

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562790

Luminaire Tested: **SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562790
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6840.7 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562790
CATALOG NUMBER: SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562790

CATALOG NUMBER: SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	73	86	79	73	69	69	65	62	61	57	55	52	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14374	14374	14374
5°	14481	14388	14335
10°	14446	14379	14338
15°	14370	14370	14356
20°	14276	14318	14318
25°	14141	14244	14200
30°	13969	14138	14076
35°	13761	13972	13875
40°	13534	13724	13586
45°	13288	13382	13174
50°	12940	12940	12733
55°	12529	12366	12181
60°	11924	11684	11498
65°	11022	10802	10706
70°	9649	9727	9690
75°	7764	8587	8637
80°	5520	7279	7359
85°	3356	6108	6108



TEST NUMBER: P562790

CATALOG NUMBER: SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	2.2
10°-20°	423.1	6.2
20°-30°	640.7	9.4
30°-40°	768.1	11.2
40°-50°	783.2	11.4
50°-60°	683.7	10.0
60°-70°	489.5	7.2
70°-80°	252.1	3.7
80°-90°	64.8	0.9
90°-100°	187.4	2.7
100°-110°	515.5	7.5
110°-120°	532.1	7.8
120°-130°	426.3	6.2
130°-140°	334.8	4.9
140°-150°	256.6	3.8
150°-160°	184.5	2.7
160°-170°	112.8	1.6
170°-180°	38.0	0.6
0°-30°	1211.2	17.7
0°-40°	1979.4	28.9
0°-60°	3446.3	50.4
0°-90°	4252.7	62.2
90°-120°	1235.0	18.1
90°-150°	2252.7	32.9
90°-180°	2588.0	37.8
0°-180°	6840.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1564	1548	1554	1549	1548	148
15°	1504	1492	1504	1504	1503	424
25°	1389	1379	1399	1395	1395	639
35°	1222	1219	1240	1232	1232	764
45°	1018	1016	1026	1012	1010	784
55°	779	769	769	757	757	694
65°	505	494	495	490	490	499
75°	218	228	241	242	242	235
85°	32	49	58	59	58	43
90°	1	3	6	8	8	3
95°	28	102	331	142	90	29
105°	92	142	568	865	807	97
115°	163	199	456	907	1030	161
125°	225	256	413	699	819	201
135°	271	301	402	566	640	209
145°	314	335	396	482	519	197
155°	355	367	393	433	446	163
165°	384	389	395	411	413	108
175°	397	398	396	401	400	38
180°	397	397	397	397	397	

TEST NUMBER: P562790

CATALOG NUMBER: SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1557.9	1557.9	1557.9	1557.9	1557.9
2.5°	1567.1	1553.5	1557.9	1554.3	1548.6
5°	1563.6	1548.1	1553.5	1549.2	1547.8
7.5°	1552.4	1536.9	1544.0	1541.1	1539.7
10°	1542.0	1526.5	1534.8	1531.9	1530.4
12.5°	1528.1	1513.7	1523.2	1520.3	1520.1
15°	1504.5	1491.8	1504.5	1504.4	1503.0
17.5°	1474.8	1463.2	1476.8	1477.6	1476.8
20°	1454.0	1441.3	1458.3	1456.9	1458.3
22.5°	1428.6	1418.2	1436.4	1432.7	1434.1
25°	1389.1	1379.2	1399.2	1394.9	1394.9
27.5°	1342.3	1335.3	1357.1	1352.4	1352.4
30°	1311.2	1304.1	1327.1	1321.3	1321.3
32.5°	1276.6	1271.8	1293.6	1286.7	1286.7
35°	1221.8	1218.9	1240.5	1231.9	1231.9
37.5°	1165.2	1162.7	1182.2	1171.8	1168.4
40°	1123.7	1122.3	1139.5	1128.0	1128.0
42.5°	1082.1	1080.7	1095.7	1081.8	1081.8
45°	1018.4	1015.6	1025.6	1012.5	1009.7
47.5°	948.8	946.0	952.3	938.1	936.7
50°	901.5	898.7	901.5	888.5	887.1
52.5°	853.1	848.0	848.5	835.5	835.2
55°	778.9	769.1	768.8	757.3	757.3
57.5°	700.5	687.5	688.6	678.8	677.4
60°	646.2	632.1	633.2	624.6	623.1
62.5°	593.1	576.8	580.2	570.3	570.1
65°	504.9	493.6	494.8	490.4	490.4
67.5°	420.0	409.6	417.2	413.7	413.4
70°	357.7	350.7	360.6	360.6	359.2
72.5°	300.0	299.7	312.1	312.2	313.0
75°	217.8	227.7	240.9	242.3	242.3
77.5°	145.4	162.9	177.4	178.0	177.7
80°	103.9	123.6	137.0	139.9	138.5
82.5°	70.4	91.3	102.4	105.3	103.9
85°	31.7	48.7	57.7	59.1	57.7
87.5°	9.4	20.1	24.3	24.5	22.3
90°	0.8	3.3	5.9	7.6	7.6
92.5°	11.7	49.8	86.4	33.2	27.2
95°	27.9	102.3	331.3	141.7	90.4
97.5°	45.5	113.4	505.6	389.6	274.9
100°	58.3	120.3	560.4	565.6	461.5
102.5°	70.5	128.5	574.6	701.8	606.2
105°	92.1	141.7	568.0	865.1	807.2
107.5°	112.8	158.0	535.7	945.1	962.2
110°	127.6	169.0	511.4	964.9	1024.5



TEST NUMBER: P562790

CATALOG NUMBER: SQ4-PC3-075U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.2	181.2	487.0	952.1	1042.7
115°	163.1	198.7	455.6	907.2	1029.5
117.5°	184.1	216.8	435.6	844.2	982.5
120°	196.9	228.4	426.9	796.9	939.9
122.5°	208.4	239.8	420.8	755.5	891.2
125°	224.8	256.2	413.3	699.2	819.1
127.5°	240.4	270.3	408.4	652.2	757.4
130°	248.5	279.1	405.7	624.3	720.2
132.5°	258.0	288.6	403.7	599.7	686.4
135°	271.3	301.1	401.5	565.5	639.9
137.5°	283.8	311.4	399.6	537.8	599.1
140°	293.3	318.9	399.0	519.4	574.8
142.5°	301.4	325.1	397.6	503.0	550.4
145°	313.6	335.1	395.6	481.8	519.0
147.5°	326.6	345.1	394.6	463.0	492.8
150°	334.7	351.3	393.9	452.7	475.9
152.5°	342.2	357.4	393.2	443.9	463.0
155°	355.0	366.6	393.0	433.1	445.5
157.5°	364.3	373.7	393.0	424.2	432.8
160°	371.1	378.5	393.0	419.4	426.0
162.5°	376.5	382.6	393.7	415.3	420.6
165°	383.7	388.7	394.7	410.9	413.3
167.5°	388.8	392.6	395.6	407.1	407.8
170°	392.2	394.7	395.6	405.7	405.7
172.5°	394.9	396.1	395.6	403.7	403.0
175°	397.3	398.1	395.6	400.6	399.8
177.5°	397.9	397.9	395.2	399.3	397.9
180°	397.3	397.3	397.3	397.3	397.3

(END OF REPORT)