

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563294

Luminaire Tested: **SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563294  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3408.2 lumens  
Efficiency: N/A  
Efficacy: 119.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 28.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563294  
CATALOG NUMBER: SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563294

CATALOG NUMBER: SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20		
RC	80					70					50					0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36
3	82	72	65	59	75	67	61	55	57	52	48	48	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6061
10°	6109	6065	6039
15°	6068	6036	6002
20°	6028	5994	5949
25°	5956	5916	5857
30°	5847	5816	5742
35°	5694	5654	5583
40°	5511	5476	5414
45°	5361	5324	5270
50°	5169	5136	5085
55°	4901	4835	4798
60°	4462	4334	4312
65°	3930	3766	3755
70°	3394	3253	3253
75°	2920	2880	2838
80°	2577	2603	2545
85°	2011	2202	2202



TEST NUMBER: P563294

CATALOG NUMBER: SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.3	1.8
10°-20°	177.8	5.2
20°-30°	266.3	7.8
30°-40°	312.3	9.2
40°-50°	313.3	9.2
50°-60°	267.3	7.8
60°-70°	174.3	5.1
70°-80°	87.5	2.6
80°-90°	25.2	0.7
90°-100°	126.6	3.7
100°-110°	343.9	10.1
110°-120°	353.6	10.4
120°-130°	282.7	8.3
130°-140°	222.2	6.5
140°-150°	170.3	5.0
150°-160°	122.5	3.6
160°-170°	74.9	2.2
170°-180°	25.2	0.7
0°-30°	506.3	14.9
0°-40°	818.6	24.0
0°-60°	1399.2	41.1
0°-90°	1686.2	49.5
90°-120°	824.1	24.2
90°-150°	1499.3	44.0
90°-180°	1722.0	50.5
0°-180°	3408.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	658	658	658	658	658	
5°	661	654	657	654	654	63
15°	635	629	632	630	628	179
25°	585	578	581	576	575	269
35°	506	500	502	496	496	316
45°	411	408	408	404	404	316
55°	305	304	301	299	298	271
65°	180	177	172	171	172	180
75°	82	82	81	80	80	89
85°	19	21	21	21	21	22
90°	1	3	6	8	8	2
95°	19	69	220	96	64	20
105°	61	95	378	576	542	65
115°	108	132	303	602	686	107
125°	149	170	274	462	544	133
135°	180	200	266	376	424	139
145°	208	223	263	319	343	130
155°	235	243	261	287	295	108
165°	254	258	262	273	274	72
175°	264	265	263	266	265	25
180°	264	264	264	264	264	

TEST NUMBER: P563294

CATALOG NUMBER: SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	658.4	658.4	658.4	658.4	658.4
2.5°	662.6	657.1	658.4	657.4	654.7
5°	660.7	654.5	656.7	654.4	654.4
7.5°	656.2	649.4	651.6	649.3	649.2
10°	652.1	645.3	647.4	645.1	644.6
12.5°	646.1	639.3	641.9	639.1	639.0
15°	635.3	629.1	631.9	629.5	628.4
17.5°	623.2	616.4	619.7	616.5	616.1
20°	614.0	607.2	610.5	605.9	605.9
22.5°	602.9	596.1	599.9	593.9	593.9
25°	585.1	578.4	581.1	575.9	575.3
27.5°	564.0	557.3	560.2	554.3	554.2
30°	548.8	542.6	545.9	539.5	539.0
32.5°	532.2	526.4	528.8	522.4	521.9
35°	505.5	500.4	502.0	496.2	495.7
37.5°	477.4	472.3	474.1	469.1	468.9
40°	457.6	454.2	454.7	450.6	449.5
42.5°	439.1	435.3	435.8	431.7	431.5
45°	410.9	408.0	408.0	403.9	403.9
47.5°	380.9	378.7	378.1	374.7	374.6
50°	360.1	358.4	357.8	354.9	354.3
52.5°	338.4	337.6	335.6	333.2	333.1
55°	304.7	303.6	300.6	298.9	298.3
57.5°	268.1	265.8	262.6	260.0	260.5
60°	241.8	239.5	234.9	233.7	233.7
62.5°	216.4	213.7	209.0	207.4	208.3
65°	180.0	176.7	172.5	171.4	172.0
67.5°	147.0	144.0	139.5	139.5	139.1
70°	125.8	124.1	120.6	120.6	120.6
72.5°	106.9	106.1	103.5	103.5	103.1
75°	81.9	81.9	80.8	80.2	79.6
77.5°	61.4	61.6	61.1	60.5	59.4
80°	48.5	49.6	49.0	48.5	47.9
82.5°	36.5	37.6	37.5	36.5	36.4
85°	19.0	20.7	20.8	20.8	20.8
87.5°	5.2	7.6	8.6	8.9	9.4
90°	0.8	3.3	5.9	7.6	7.6
92.5°	7.6	34.7	60.2	25.9	21.9
95°	18.7	69.2	220.5	96.0	64.4
97.5°	30.9	76.5	338.0	263.0	184.7
100°	39.0	81.3	374.0	379.1	306.1
102.5°	47.1	86.1	383.5	468.8	404.5
105°	61.1	95.1	378.2	575.9	541.9
107.5°	75.5	105.5	356.3	631.1	640.6
110°	85.6	113.0	340.1	642.0	682.6



TEST NUMBER: P563294

CATALOG NUMBER: SQ4-PP3-050U-050D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	94.5	120.5	323.8	633.0	694.2
115°	108.5	131.8	302.7	602.3	686.0
117.5°	121.8	144.0	289.3	558.8	653.1
120°	130.6	152.2	283.2	529.6	623.3
122.5°	138.1	159.6	279.2	500.3	590.7
125°	149.2	170.0	273.9	461.5	544.4
127.5°	159.3	179.8	271.0	432.1	503.2
130°	165.4	185.3	269.7	413.6	477.4
132.5°	171.5	191.4	268.3	397.8	454.4
135°	179.8	199.7	266.3	375.9	424.0
137.5°	188.8	206.8	265.3	356.6	397.0
140°	194.2	211.6	264.6	344.3	380.8
142.5°	199.6	215.7	263.9	334.6	365.2
145°	207.8	222.7	262.9	319.4	343.4
147.5°	216.9	229.7	262.0	307.4	326.3
150°	223.0	233.8	262.0	300.5	315.5
152.5°	227.8	237.2	261.4	294.4	306.6
155°	234.9	243.2	261.2	286.8	295.1
157.5°	241.9	248.3	261.2	281.7	288.0
160°	245.9	251.7	261.2	278.3	283.2
162.5°	250.0	254.5	261.9	275.5	279.2
165°	254.4	257.7	262.0	273.1	273.9
167.5°	259.0	260.6	262.9	270.2	270.9
170°	260.3	262.0	262.9	268.8	268.8
172.5°	261.7	262.7	262.9	267.5	267.5
175°	263.7	264.6	262.9	266.3	265.4
177.5°	264.4	264.4	262.4	265.1	263.7
180°	263.7	263.7	263.7	263.7	263.7

(END OF REPORT)