

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563486

Luminaire Tested: **SQ4-PP3-0U-050D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563486  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-0U-050D-940-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1685.2 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563486  
CATALOG NUMBER: SQ4-PP3-0U-050D-940-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563486

CATALOG NUMBER: SQ4-PP3-0U-050D-940-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6061
10°	6109	6065	6039
15°	6068	6036	6002
20°	6028	5994	5949
25°	5956	5916	5857
30°	5847	5816	5742
35°	5694	5654	5583
40°	5511	5476	5414
45°	5361	5324	5270
50°	5169	5136	5085
55°	4901	4835	4798
60°	4462	4334	4312
65°	3930	3766	3755
70°	3394	3253	3253
75°	2920	2880	2838
80°	2577	2603	2545
85°	2011	2202	2202



TEST NUMBER: P563486

CATALOG NUMBER: SQ4-PP3-0U-050D-940-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.3	3.7
10°-20°	177.8	10.5
20°-30°	266.3	15.8
30°-40°	312.3	18.5
40°-50°	313.3	18.6
50°-60°	267.3	15.9
60°-70°	174.3	10.3
70°-80°	87.5	5.2
80°-90°	24.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	506.3	30.0
0°-40°	818.6	48.6
0°-60°	1399.2	83.0
0°-90°	1685.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1685.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	658	658	658	658	658	
5°	661	654	657	654	654	63
15°	635	629	632	630	628	179
25°	585	578	581	576	575	269
35°	506	500	502	496	496	316
45°	411	408	408	404	404	316
55°	305	304	301	299	298	271
65°	180	177	172	171	172	180
75°	82	82	81	80	80	89
85°	19	21	21	21	21	23
90°	0	0	0	0	0	



TEST NUMBER: P563486

CATALOG NUMBER: SQ4-PP3-0U-050D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	658.4	658.4	658.4	658.4	658.4
2.5°	662.6	657.1	658.4	657.4	654.7
5°	660.7	654.5	656.7	654.4	654.4
7.5°	656.2	649.4	651.6	649.3	649.2
10°	652.1	645.3	647.4	645.1	644.6
12.5°	646.1	639.3	641.9	639.1	639.0
15°	635.3	629.1	631.9	629.5	628.4
17.5°	623.2	616.4	619.7	616.5	616.1
20°	614.0	607.2	610.5	605.9	605.9
22.5°	602.9	596.1	599.9	593.9	593.9
25°	585.1	578.4	581.1	575.9	575.3
27.5°	564.0	557.3	560.2	554.3	554.2
30°	548.8	542.6	545.9	539.5	539.0
32.5°	532.2	526.4	528.8	522.4	521.9
35°	505.5	500.4	502.0	496.2	495.7
37.5°	477.4	472.3	474.1	469.1	468.9
40°	457.6	454.2	454.7	450.6	449.5
42.5°	439.1	435.3	435.8	431.7	431.5
45°	410.9	408.0	408.0	403.9	403.9
47.5°	380.9	378.7	378.1	374.7	374.6
50°	360.1	358.4	357.8	354.9	354.3
52.5°	338.4	337.6	335.6	333.2	333.1
55°	304.7	303.6	300.6	298.9	298.3
57.5°	268.1	265.8	262.6	260.0	260.5
60°	241.8	239.5	234.9	233.7	233.7
62.5°	216.4	213.7	209.0	207.4	208.3
65°	180.0	176.7	172.5	171.4	172.0
67.5°	147.0	144.0	139.5	139.5	139.1
70°	125.8	124.1	120.6	120.6	120.6
72.5°	106.9	106.1	103.5	103.5	103.1
75°	81.9	81.9	80.8	80.2	79.6
77.5°	61.4	61.6	61.1	60.5	59.4
80°	48.5	49.6	49.0	48.5	47.9
82.5°	36.5	37.6	37.5	36.5	36.4
85°	19.0	20.7	20.8	20.8	20.8
87.5°	5.1	6.9	7.4	7.4	7.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)