

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563991

Luminaire Tested: **SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563991
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6288.1 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563991
CATALOG NUMBER: SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563991

CATALOG NUMBER: SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	86	83	78	76	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9112	9112	9112
5°	9195	9124	9076
10°	9166	9102	9054
15°	9125	9068	9019
20°	9079	9020	8954
25°	9015	8954	8850
30°	8918	8854	8727
35°	8786	8709	8585
40°	8586	8493	8340
45°	8236	8091	7925
50°	7620	7436	7290
55°	6651	6500	6363
60°	5605	5557	5447
65°	4846	4865	4829
70°	4453	4474	4474
75°	4275	4275	4306
80°	4024	4066	4024
85°	3239	3599	3599



TEST NUMBER: P563991

CATALOG NUMBER: SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	2.2
10°-20°	400.8	6.4
20°-30°	604.6	9.6
30°-40°	720.4	11.5
40°-50°	710.2	11.3
50°-60°	542.8	8.6
60°-70°	335.9	5.3
70°-80°	190.8	3.0
80°-90°	59.5	0.9
90°-100°	189.9	3.0
100°-110°	515.9	8.2
110°-120°	530.4	8.4
120°-130°	424.1	6.7
130°-140°	333.2	5.3
140°-150°	255.5	4.1
150°-160°	183.7	2.9
160°-170°	112.4	1.8
170°-180°	37.9	0.6
0°-30°	1145.5	18.2
0°-40°	1865.9	29.7
0°-60°	3118.9	49.6
0°-90°	3705.1	58.9
90°-120°	1236.2	19.7
90°-150°	2249.0	35.8
90°-180°	2583.0	41.1
0°-180°	6288.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1482	1482	1482	1482	1482	
5°	1489	1473	1478	1472	1470	141
15°	1433	1418	1424	1419	1416	404
25°	1328	1312	1319	1305	1304	611
35°	1170	1156	1160	1145	1143	730
45°	947	934	930	914	911	725
55°	620	610	606	596	593	556
65°	333	331	334	332	332	337
75°	180	180	180	181	181	190
85°	46	48	51	51	51	53
90°	1	5	9	11	11	4
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	

TEST NUMBER: P563991

CATALOG NUMBER: SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1481.5	1481.5	1481.5	1481.5	1481.5
2.5°	1490.7	1477.7	1481.5	1478.3	1471.3
5°	1489.2	1472.9	1477.7	1472.5	1470.0
7.5°	1477.7	1461.7	1466.4	1461.3	1459.8
10°	1467.5	1452.5	1457.3	1452.1	1449.6
12.5°	1456.2	1440.3	1446.0	1439.8	1437.3
15°	1433.0	1418.0	1424.1	1418.9	1416.4
17.5°	1407.5	1391.5	1397.5	1391.6	1388.3
20°	1387.1	1372.1	1378.1	1369.2	1367.9
22.5°	1364.6	1349.6	1355.7	1343.7	1343.4
25°	1328.4	1312.1	1319.4	1305.4	1304.1
27.5°	1285.2	1270.3	1276.3	1262.0	1260.5
30°	1255.6	1240.7	1246.7	1231.3	1228.8
32.5°	1221.9	1208.0	1213.0	1197.7	1196.2
35°	1170.1	1156.4	1159.9	1144.6	1143.3
37.5°	1111.2	1098.7	1100.7	1083.8	1082.6
40°	1069.3	1056.9	1057.8	1040.0	1038.7
42.5°	1023.4	1010.9	1009.9	992.0	990.7
45°	946.8	934.4	930.2	913.6	911.1
47.5°	859.5	847.1	839.4	825.8	824.1
50°	796.3	783.8	777.1	765.5	761.8
52.5°	727.9	715.4	709.7	699.2	695.4
55°	620.2	610.2	606.1	595.9	593.4
57.5°	517.8	511.1	509.9	499.9	498.9
60°	455.6	451.8	451.7	442.8	442.8
62.5°	402.5	399.7	401.7	395.8	394.8
65°	333.0	330.6	334.3	331.8	331.8
67.5°	278.2	278.2	280.5	279.5	279.5
70°	247.6	247.6	248.8	248.8	248.8
72.5°	220.0	219.0	222.3	222.3	221.3
75°	179.9	179.9	179.9	181.2	181.2
77.5°	140.1	140.4	141.4	141.1	140.1
80°	113.6	114.8	114.8	113.6	113.6
82.5°	87.0	88.3	88.3	88.0	87.0
85°	45.9	48.4	51.0	51.0	51.0
87.5°	13.5	18.3	22.2	22.7	21.7
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0

TEST NUMBER: P563991

CATALOG NUMBER: SQ4-PR1-050U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)