

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563558

Luminaire Tested: **SQ4-PP3-0U-125D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563558
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4211.4 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563558
CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563558

CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15181	15181	15181
5°	15292	15199	15146
10°	15267	15158	15091
15°	15166	15083	15001
20°	15065	14981	14867
25°	14886	14783	14637
30°	14610	14534	14349
35°	14229	14131	13953
40°	13773	13687	13530
45°	13398	13304	13172
50°	12917	12833	12710
55°	12247	12085	11993
60°	11149	10830	10778
65°	9822	9414	9381
70°	8481	8130	8130
75°	7301	7197	7094
80°	6434	6514	6360
85°	5039	5494	5494



TEST NUMBER: P563558

CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.6	3.7
10°-20°	444.3	10.5
20°-30°	665.5	15.8
30°-40°	780.5	18.5
40°-50°	783.0	18.6
50°-60°	668.0	15.9
60°-70°	435.6	10.3
70°-80°	218.6	5.2
80°-90°	60.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1265.3	30.0
0°-40°	2045.9	48.6
0°-60°	3496.8	83.0
0°-90°	4211.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4211.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1645	1645	1645	1645	1645	
5°	1651	1636	1641	1635	1635	157
15°	1588	1572	1579	1573	1570	448
25°	1462	1445	1452	1439	1438	672
35°	1263	1251	1255	1240	1239	789
45°	1027	1020	1020	1010	1010	791
55°	761	759	751	747	746	677
65°	450	442	431	428	430	449
75°	205	205	202	200	199	222
85°	48	52	52	52	52	58
90°	0	0	0	0	0	



TEST NUMBER: P563558

CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1645.4	1645.4	1645.4	1645.4	1645.4
2.5°	1655.8	1642.3	1645.4	1643.0	1636.2
5°	1651.2	1635.7	1641.1	1635.4	1635.4
7.5°	1640.0	1623.0	1628.4	1622.7	1622.4
10°	1629.6	1612.7	1618.0	1612.2	1610.8
12.5°	1614.6	1597.7	1604.2	1597.3	1597.0
15°	1587.8	1572.3	1579.1	1573.3	1570.5
17.5°	1557.5	1540.6	1548.8	1540.7	1539.6
20°	1534.4	1517.5	1525.8	1514.2	1514.2
22.5°	1506.7	1489.8	1499.2	1484.2	1484.2
25°	1462.3	1445.4	1452.2	1439.2	1437.8
27.5°	1409.5	1392.9	1400.0	1385.3	1385.0
30°	1371.4	1355.9	1364.2	1348.3	1346.9
32.5°	1329.9	1315.5	1321.6	1305.7	1304.2
35°	1263.3	1250.6	1254.6	1240.2	1238.8
37.5°	1193.2	1180.2	1184.8	1172.4	1171.9
40°	1143.6	1135.1	1136.4	1126.2	1123.4
42.5°	1097.4	1087.9	1089.1	1079.0	1078.4
45°	1026.8	1019.7	1019.6	1009.5	1009.5
47.5°	951.8	946.4	944.9	936.5	936.2
50°	899.9	895.6	894.1	886.9	885.5
52.5°	845.7	843.7	838.7	832.7	832.4
55°	761.4	758.6	751.3	747.0	745.6
57.5°	670.0	664.4	656.2	649.8	651.0
60°	604.2	598.6	586.9	584.1	584.1
62.5°	540.8	534.0	522.3	518.3	520.6
65°	449.9	441.5	431.2	428.3	429.7
67.5°	367.5	359.8	348.7	348.7	347.5
70°	314.4	310.2	301.4	301.4	301.4
72.5°	267.1	265.1	258.7	258.7	257.6
75°	204.8	204.8	201.9	200.4	199.0
77.5°	153.4	154.0	152.6	151.1	148.5
80°	121.1	124.0	122.6	121.1	119.7
82.5°	91.1	94.0	93.7	91.1	90.9
85°	47.6	51.8	51.9	51.9	51.9
87.5°	12.7	17.2	18.5	18.5	19.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)