

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564159

Luminaire Tested: **SQ4-PR1-0U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564159  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-0U-050D-940-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2512.8 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564159  
CATALOG NUMBER: SQ4-PR1-0U-050D-940-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564159

CATALOG NUMBER: SQ4-PR1-0U-050D-940-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93		95	92	90		91	89	87	85
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		81	78	75	72
3	92	82	74	68	90	80	73	68	78	71	66		75	70	65		72	68	64	62
4	85	73	65	58	82	72	64	58	69	63	57		67	61	56		65	60	56	54
5	78	66	57	51	76	65	57	50	63	55	50		61	54	49		59	53	49	47
6	72	59	51	45	70	58	50	44	57	49	44		55	49	44		53	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39		50	44	39		49	43	39	37
8	63	49	41	35	61	49	41	35	47	40	35		46	40	35		45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32		43	36	32		42	36	31	30
10	55	42	34	29	54	41	34	29	40	34	29		40	33	29		39	33	29	27

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6183	6183	6183
5°	6239	6190	6158
10°	6218	6175	6143
15°	6191	6153	6119
20°	6160	6120	6075
25°	6117	6075	6005
30°	6050	6008	5921
35°	5961	5909	5825
40°	5825	5763	5658
45°	5588	5490	5377
50°	5169	5046	4946
55°	4512	4410	4317
60°	3802	3770	3695
65°	3289	3301	3276
70°	3021	3036	3036
75°	2902	2902	2921
80°	2731	2759	2731
85°	2202	2442	2442



TEST NUMBER: P564159

CATALOG NUMBER: SQ4-PR1-0U-050D-940-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.1	3.8
10°-20°	272.0	10.8
20°-30°	410.2	16.3
30°-40°	488.8	19.5
40°-50°	481.9	19.2
50°-60°	368.3	14.7
60°-70°	227.9	9.1
70°-80°	129.4	5.2
80°-90°	39.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.2	30.9
0°-40°	1266.0	50.4
0°-60°	2116.1	84.2
0°-90°	2512.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2512.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	1010	999	1003	999	997	96
15°	972	962	966	963	961	274
25°	901	890	895	886	885	415
35°	794	785	787	777	776	495
45°	642	634	631	620	618	492
55°	421	414	411	404	403	377
65°	226	224	227	225	225	229
75°	122	122	122	123	123	129
85°	31	33	35	35	35	37
90°	0	0	0	0	0	



TEST NUMBER: P564159

CATALOG NUMBER: SQ4-PR1-0U-050D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1005.2	1005.2	1005.2	1005.2	1005.2
2.5°	1011.4	1002.6	1005.2	1003.0	998.2
5°	1010.4	999.4	1002.6	999.1	997.4
7.5°	1002.6	991.7	994.9	991.5	990.4
10°	995.6	985.5	988.7	985.2	983.5
12.5°	988.0	977.2	981.1	976.9	975.2
15°	972.3	962.1	966.2	962.7	961.0
17.5°	954.9	944.1	948.2	944.2	942.0
20°	941.1	930.9	935.0	929.0	928.1
22.5°	925.9	915.7	919.8	911.7	911.5
25°	901.3	890.3	895.2	885.7	884.8
27.5°	872.0	861.8	865.9	856.2	855.2
30°	851.9	841.8	845.9	835.4	833.7
32.5°	829.1	819.6	823.0	812.6	811.6
35°	793.9	784.6	787.0	776.6	775.7
37.5°	753.9	745.5	746.8	735.4	734.5
40°	725.5	717.1	717.7	705.6	704.7
42.5°	694.4	685.9	685.2	673.0	672.2
45°	642.4	633.9	631.1	619.9	618.2
47.5°	583.2	574.7	569.5	560.3	559.1
50°	540.2	531.8	527.3	519.4	516.9
52.5°	493.8	485.4	481.5	474.4	471.8
55°	420.8	414.0	411.2	404.3	402.6
57.5°	351.3	346.8	346.0	339.2	338.5
60°	309.1	306.5	306.5	300.4	300.4
62.5°	273.1	271.2	272.5	268.5	267.9
65°	226.0	224.3	226.8	225.1	225.1
67.5°	188.7	188.7	190.3	189.6	189.6
70°	168.0	168.0	168.8	168.8	168.8
72.5°	149.3	148.6	150.8	150.8	150.1
75°	122.1	122.1	122.1	122.9	122.9
77.5°	95.1	95.2	95.9	95.7	95.1
80°	77.1	77.9	77.9	77.1	77.1
82.5°	59.0	59.9	59.9	59.7	59.0
85°	31.2	32.9	34.6	34.6	34.6
87.5°	9.0	11.7	13.9	13.8	13.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)