

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564471

Luminaire Tested: **SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564471
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11517.5 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 97.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564471
CATALOG NUMBER: SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564471

CATALOG NUMBER: SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	20
4	72	61	54	48	64	55	49	44	45	40	36	34	31	29	25	23	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	19	16	15	12
8	52	40	32	27	46	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9112	9112	9112
5°	9195	9124	9076
10°	9166	9102	9054
15°	9125	9068	9019
20°	9079	9020	8954
25°	9015	8954	8850
30°	8918	8854	8727
35°	8786	8709	8585
40°	8586	8493	8340
45°	8236	8091	7925
50°	7620	7436	7290
55°	6651	6500	6363
60°	5605	5557	5447
65°	4846	4865	4829
70°	4453	4474	4474
75°	4275	4275	4306
80°	4024	4066	4024
85°	3239	3599	3599



TEST NUMBER: P564471

CATALOG NUMBER: SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	1.2
10°-20°	400.8	3.5
20°-30°	604.6	5.2
30°-40°	720.4	6.3
40°-50°	710.2	6.2
50°-60°	542.8	4.7
60°-70°	335.9	2.9
70°-80°	190.8	1.7
80°-90°	60.5	0.5
90°-100°	563.1	4.9
100°-110°	1522.4	13.2
110°-120°	1600.6	13.9
120°-130°	1300.1	11.3
130°-140°	1019.8	8.9
140°-150°	782.7	6.8
150°-160°	562.9	4.9
160°-170°	343.9	3.0
170°-180°	115.9	1.0
0°-30°	1145.5	9.9
0°-40°	1865.9	16.2
0°-60°	3118.9	27.1
0°-90°	3706.1	32.2
90°-120°	3686.0	32.0
90°-150°	6788.7	58.9
90°-180°	7811.0	67.8
0°-180°	11517.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1482	1482	1482	1482	1482	
5°	1489	1473	1478	1472	1470	141
15°	1433	1418	1424	1419	1416	404
25°	1328	1312	1319	1305	1304	611
35°	1170	1156	1160	1145	1143	730
45°	947	934	930	914	911	725
55°	620	610	606	596	593	556
65°	333	331	334	332	332	337
75°	180	180	180	181	181	190
85°	46	48	51	51	51	53
90°	3	8	17	18	17	8
95°	87	307	936	485	288	91
105°	283	437	1689	2491	2389	298
115°	498	609	1401	2712	3061	492
125°	682	782	1262	2130	2503	608
135°	818	915	1228	1720	1947	632
145°	951	1022	1212	1472	1585	595
155°	1073	1115	1201	1321	1364	495
165°	1168	1180	1206	1253	1260	329
175°	1213	1212	1208	1223	1221	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P564471

CATALOG NUMBER: SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1481.5	1481.5	1481.5	1481.5	1481.5
2.5°	1490.7	1477.7	1481.5	1478.3	1471.3
5°	1489.2	1472.9	1477.7	1472.5	1470.0
7.5°	1477.7	1461.7	1466.4	1461.3	1459.8
10°	1467.5	1452.5	1457.3	1452.1	1449.6
12.5°	1456.2	1440.3	1446.0	1439.8	1437.3
15°	1433.0	1418.0	1424.1	1418.9	1416.4
17.5°	1407.5	1391.5	1397.5	1391.6	1388.3
20°	1387.1	1372.1	1378.1	1369.2	1367.9
22.5°	1364.6	1349.6	1355.7	1343.7	1343.4
25°	1328.4	1312.1	1319.4	1305.4	1304.1
27.5°	1285.2	1270.3	1276.3	1262.0	1260.5
30°	1255.6	1240.7	1246.7	1231.3	1228.8
32.5°	1221.9	1208.0	1213.0	1197.7	1196.2
35°	1170.1	1156.4	1159.9	1144.6	1143.3
37.5°	1111.2	1098.7	1100.7	1083.8	1082.6
40°	1069.3	1056.9	1057.8	1040.0	1038.7
42.5°	1023.4	1010.9	1009.9	992.0	990.7
45°	946.8	934.4	930.2	913.6	911.1
47.5°	859.5	847.1	839.4	825.8	824.1
50°	796.3	783.8	777.1	765.5	761.8
52.5°	727.9	715.4	709.7	699.2	695.4
55°	620.2	610.2	606.1	595.9	593.4
57.5°	517.8	511.1	509.9	499.9	498.9
60°	455.6	451.8	451.7	442.8	442.8
62.5°	402.5	399.7	401.7	395.8	394.8
65°	333.0	330.6	334.3	331.8	331.8
67.5°	278.2	278.2	280.5	279.5	279.5
70°	247.6	247.6	248.8	248.8	248.8
72.5°	220.0	219.0	222.3	222.3	221.3
75°	179.9	179.9	179.9	181.2	181.2
77.5°	140.1	140.4	141.4	141.1	140.1
80°	113.6	114.8	114.8	113.6	113.6
82.5°	87.0	88.3	88.3	88.0	87.0
85°	45.9	48.4	51.0	51.0	51.0
87.5°	13.8	18.8	23.8	24.0	22.8
90°	2.6	7.7	17.0	18.2	17.0
92.5°	37.0	135.0	266.3	115.6	83.7
95°	87.4	306.7	936.4	484.6	288.2
97.5°	140.3	351.8	1459.6	1207.9	887.1
100°	180.0	370.0	1622.4	1692.0	1368.1
102.5°	216.5	395.3	1679.8	2059.0	1816.7
105°	283.0	437.3	1688.9	2491.2	2389.2
107.5°	344.6	485.3	1615.1	2760.9	2794.8
110°	392.6	520.1	1549.3	2833.3	2977.4



TEST NUMBER: P564471

CATALOG NUMBER: SQ4-PR1-150U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.3	554.7	1488.8	2818.8	3060.9
115°	498.2	609.1	1400.7	2711.5	3060.9
117.5°	559.7	663.8	1342.5	2547.4	2943.5
120°	597.3	699.3	1308.1	2429.7	2833.9
122.5°	632.8	732.8	1287.2	2303.5	2710.8
125°	682.1	781.5	1262.4	2130.3	2502.7
127.5°	727.5	825.1	1247.8	1989.0	2316.4
130°	752.5	853.2	1241.6	1901.7	2197.5
132.5°	778.6	878.3	1235.3	1822.9	2095.3
135°	817.7	914.6	1228.5	1720.1	1947.1
137.5°	857.1	948.6	1222.8	1636.7	1821.6
140°	884.2	969.7	1220.7	1583.1	1747.6
142.5°	910.3	990.6	1216.5	1534.6	1678.7
145°	950.7	1022.1	1211.6	1472.3	1584.6
147.5°	987.5	1050.8	1205.8	1415.9	1502.1
150°	1014.6	1070.7	1203.7	1385.3	1454.1
152.5°	1039.7	1088.6	1202.7	1356.8	1413.4
155°	1073.3	1115.4	1201.1	1320.8	1364.1
157.5°	1108.3	1137.6	1201.4	1295.7	1324.2
160°	1128.1	1152.3	1202.4	1279.8	1300.2
162.5°	1143.7	1163.9	1203.5	1267.2	1282.5
165°	1168.5	1180.0	1206.3	1253.4	1259.8
167.5°	1185.5	1193.4	1206.6	1241.6	1244.7
170°	1195.9	1199.7	1207.6	1236.3	1236.3
172.5°	1204.3	1205.0	1207.6	1230.1	1229.0
175°	1212.9	1211.6	1207.6	1223.2	1220.7
177.5°	1215.7	1212.7	1207.4	1217.8	1214.7
180°	1211.6	1211.6	1211.6	1211.6	1211.6

(END OF REPORT)