

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564710

Luminaire Tested: **SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564710
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5888.4 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564710
CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564710

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	94	91	97	93	90	86	84	81	78	75	73	71	67	65	64	60
2	94	86	80	74	88	82	76	71	73	69	65	66	62	59	59	56	54	50
3	85	76	68	62	81	72	65	60	65	59	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	56	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	45	68	57	49	44	52	45	41	47	42	38	42	38	35	32
6	66	54	46	40	63	51	44	38	47	40	36	42	37	33	38	34	31	28
7	61	49	41	35	58	47	39	34	42	36	32	39	33	29	35	31	27	25
8	57	44	36	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15105	15105	15105
5°	15203	15082	15016
10°	15081	14960	14878
15°	14922	14756	14701
20°	14743	14516	14488
25°	14537	14273	14229
30°	14230	14015	13923
35°	13825	13631	13550
40°	13394	13186	13134
45°	12873	12705	12647
50°	12340	12236	12153
55°	11763	11763	11578
60°	11046	11260	10859
65°	10108	10612	9857
70°	8910	9768	8678
75°	7611	8741	7404
80°	5903	7359	5977
85°	3822	5653	5039



TEST NUMBER: P564710

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.2	2.6
10°-20°	435.3	7.4
20°-30°	645.6	11.0
30°-40°	755.4	12.8
40°-50°	752.1	12.8
50°-60°	649.5	11.0
60°-70°	467.5	7.9
70°-80°	245.2	4.2
80°-90°	61.8	1.0
90°-100°	126.6	2.2
100°-110°	343.9	5.8
110°-120°	353.6	6.0
120°-130°	282.7	4.8
130°-140°	222.2	3.8
140°-150°	170.3	2.9
150°-160°	122.5	2.1
160°-170°	74.9	1.3
170°-180°	25.2	0.4
0°-30°	1235.0	21.0
0°-40°	1990.5	33.8
0°-60°	3392.0	57.6
0°-90°	4166.4	70.8
90°-120°	824.1	14.0
90°-150°	1499.3	25.5
90°-180°	1722.0	29.2
0°-180°	5888.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1642	1623	1628	1624	1621	155
15°	1562	1542	1545	1542	1539	440
25°	1428	1404	1402	1394	1398	657
35°	1228	1211	1210	1199	1203	767
45°	987	978	974	971	969	761
55°	731	730	731	721	720	653
65°	463	477	486	467	452	459
75°	214	233	245	229	208	229
85°	36	47	53	50	48	48
90°	1	3	6	8	8	3
95°	19	69	220	96	64	20
105°	61	95	378	576	542	65
115°	108	132	303	602	686	107
125°	149	170	274	462	544	133
135°	180	200	266	376	424	139
145°	208	223	263	319	343	130
155°	235	243	261	287	295	108
165°	254	258	262	273	274	72
175°	264	265	263	266	265	25
180°	264	264	264	264	264	

TEST NUMBER: P564710

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1646.4	1632.9	1637.2	1633.5	1625.6
5°	1641.5	1623.2	1628.5	1624.1	1621.3
7.5°	1624.8	1607.9	1611.8	1607.1	1605.5
10°	1609.8	1592.9	1596.8	1591.0	1588.1
12.5°	1592.5	1574.4	1578.3	1572.5	1570.8
15°	1562.2	1542.4	1544.9	1541.9	1539.1
17.5°	1527.0	1507.0	1507.4	1502.7	1502.2
20°	1501.6	1480.4	1478.5	1472.8	1475.6
22.5°	1473.9	1451.6	1449.7	1441.7	1445.6
25°	1428.0	1404.1	1402.1	1393.5	1397.7
27.5°	1374.9	1351.3	1351.3	1339.3	1343.8
30°	1335.7	1313.1	1315.5	1301.2	1306.9
32.5°	1294.2	1273.9	1275.1	1260.8	1266.5
35°	1227.5	1210.6	1210.2	1198.8	1203.0
37.5°	1159.4	1144.5	1142.1	1135.5	1136.7
40°	1112.1	1099.4	1094.8	1090.5	1090.5
42.5°	1062.5	1050.9	1046.4	1043.2	1042.0
45°	986.6	978.2	973.7	970.7	969.3
47.5°	911.6	903.7	899.8	897.8	896.3
50°	859.7	854.1	852.5	848.1	846.7
52.5°	807.8	804.4	802.9	797.4	795.9
55°	731.3	729.9	731.3	721.2	719.8
57.5°	651.7	654.0	658.6	645.0	641.6
60°	598.6	604.3	610.2	594.2	588.5
62.5°	544.4	553.4	561.7	543.3	535.4
65°	463.0	477.1	486.1	467.0	451.5
67.5°	384.6	402.0	412.8	392.2	374.7
70°	330.3	350.1	362.1	341.4	321.7
72.5°	283.0	305.0	314.7	295.3	275.5
75°	213.5	233.2	245.2	228.9	207.7
77.5°	151.5	170.1	180.0	165.8	148.3
80°	111.1	130.8	138.5	126.6	112.5
82.5°	78.8	95.1	100.4	93.3	83.7
85°	36.1	47.3	53.4	50.4	47.6
87.5°	9.4	17.8	23.1	23.5	24.6
90°	0.8	3.3	5.9	7.6	7.6
92.5°	7.6	34.7	60.2	25.9	21.9
95°	18.7	69.2	220.5	96.0	64.4
97.5°	30.9	76.5	338.0	263.0	184.7
100°	39.0	81.3	374.0	379.1	306.1
102.5°	47.1	86.1	383.5	468.8	404.5
105°	61.1	95.1	378.2	575.9	541.9
107.5°	75.5	105.5	356.3	631.1	640.6
110°	85.6	113.0	340.1	642.0	682.6



TEST NUMBER: P564710

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.5	120.5	323.8	633.0	694.2
115°	108.5	131.8	302.7	602.3	686.0
117.5°	121.8	144.0	289.3	558.8	653.1
120°	130.6	152.2	283.2	529.6	623.3
122.5°	138.1	159.6	279.2	500.3	590.7
125°	149.2	170.0	273.9	461.5	544.4
127.5°	159.3	179.8	271.0	432.1	503.2
130°	165.4	185.3	269.7	413.6	477.4
132.5°	171.5	191.4	268.3	397.8	454.4
135°	179.8	199.7	266.3	375.9	424.0
137.5°	188.8	206.8	265.3	356.6	397.0
140°	194.2	211.6	264.6	344.3	380.8
142.5°	199.6	215.7	263.9	334.6	365.2
145°	207.8	222.7	262.9	319.4	343.4
147.5°	216.9	229.7	262.0	307.4	326.3
150°	223.0	233.8	262.0	300.5	315.5
152.5°	227.8	237.2	261.4	294.4	306.6
155°	234.9	243.2	261.2	286.8	295.1
157.5°	241.9	248.3	261.2	281.7	288.0
160°	245.9	251.7	261.2	278.3	283.2
162.5°	250.0	254.5	261.9	275.5	279.2
165°	254.4	257.7	262.0	273.1	273.9
167.5°	259.0	260.6	262.9	270.2	270.9
170°	260.3	262.0	262.9	268.8	268.8
172.5°	261.7	262.7	262.9	267.5	267.5
175°	263.7	264.6	262.9	266.3	265.4
177.5°	264.4	264.4	262.4	265.1	263.7
180°	263.7	263.7	263.7	263.7	263.7

(END OF REPORT)