

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564711

Luminaire Tested: **SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564711
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8832.6 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 87.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564711
CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564711

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	94	91	97	93	90	86	84	81	78	75	73	71	67	65	64	60
2	94	86	80	74	88	82	76	71	73	69	65	66	62	59	59	56	54	50
3	85	76	68	62	81	72	65	60	65	59	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	56	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	45	68	57	49	44	52	45	41	47	42	38	42	38	35	32
6	66	54	46	40	63	51	44	38	47	40	36	42	37	33	38	34	31	28
7	61	49	41	35	58	47	39	34	42	36	32	39	33	29	35	31	27	25
8	57	44	36	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15105	15105	15105
5°	15203	15083	15016
10°	15081	14960	14878
15°	14922	14756	14701
20°	14743	14517	14488
25°	14537	14273	14229
30°	14230	14015	13923
35°	13826	13631	13550
40°	13394	13186	13134
45°	12874	12704	12648
50°	12340	12236	12154
55°	11764	11764	11578
60°	11046	11258	10860
65°	10108	10613	9856
70°	8911	9767	8677
75°	7610	8741	7405
80°	5901	7357	5979
85°	3818	5653	5039



TEST NUMBER: P564711

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.3	2.6
10°-20°	652.9	7.4
20°-30°	968.4	11.0
30°-40°	1133.2	12.8
40°-50°	1128.1	12.8
50°-60°	974.2	11.0
60°-70°	701.2	7.9
70°-80°	367.7	4.2
80°-90°	92.7	1.0
90°-100°	189.9	2.1
100°-110°	515.9	5.8
110°-120°	530.4	6.0
120°-130°	424.1	4.8
130°-140°	333.2	3.8
140°-150°	255.5	2.9
150°-160°	183.7	2.1
160°-170°	112.4	1.3
170°-180°	37.9	0.4
0°-30°	1852.6	21.0
0°-40°	2985.7	33.8
0°-60°	5088.0	57.6
0°-90°	6249.7	70.8
90°-120°	1236.2	14.0
90°-150°	2249.0	25.5
90°-180°	2583.0	29.2
0°-180°	8832.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2456	2456	2456	2456	2456	
5°	2462	2435	2443	2436	2432	233
15°	2343	2314	2317	2313	2309	660
25°	2142	2106	2103	2090	2097	985
35°	1841	1816	1815	1798	1804	1151
45°	1480	1467	1460	1456	1454	1142
55°	1097	1095	1097	1082	1080	979
65°	694	716	729	700	677	688
75°	320	350	368	343	312	343
85°	54	71	80	76	71	71
90°	1	5	9	11	11	4
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	

TEST NUMBER: P564711

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2455.8	2455.8	2455.8	2455.8	2455.8
2.5°	2469.6	2449.3	2455.8	2450.3	2438.5
5°	2462.3	2434.8	2442.8	2436.2	2432.0
7.5°	2437.2	2411.8	2417.7	2410.7	2408.2
10°	2414.7	2389.3	2395.2	2386.4	2382.2
12.5°	2388.7	2361.6	2367.5	2358.8	2356.2
15°	2343.3	2313.6	2317.3	2312.9	2308.6
17.5°	2290.5	2260.4	2261.0	2254.1	2253.3
20°	2252.4	2220.7	2217.8	2209.2	2213.4
22.5°	2210.9	2177.4	2174.5	2162.5	2168.4
25°	2142.0	2106.1	2103.1	2090.3	2096.6
27.5°	2062.4	2026.9	2026.9	2008.9	2015.7
30°	2003.6	1969.7	1973.3	1951.8	1960.3
32.5°	1941.3	1910.8	1912.7	1891.3	1899.7
35°	1841.3	1815.9	1815.3	1798.2	1804.5
37.5°	1739.2	1716.7	1713.2	1703.3	1705.0
40°	1668.2	1649.2	1642.2	1635.7	1635.7
42.5°	1593.8	1576.4	1569.5	1564.7	1563.0
45°	1480.0	1467.3	1460.5	1456.1	1454.0
47.5°	1367.4	1355.6	1349.7	1346.6	1344.5
50°	1289.6	1281.1	1278.7	1272.2	1270.1
52.5°	1211.7	1206.6	1204.3	1196.0	1193.9
55°	1097.0	1094.9	1097.0	1081.8	1079.7
57.5°	977.6	980.9	987.9	967.5	962.4
60°	897.9	906.4	915.2	891.2	882.8
62.5°	816.6	830.1	842.5	815.0	803.2
65°	694.5	715.7	729.2	700.5	677.2
67.5°	576.8	603.1	619.2	588.4	562.1
70°	495.5	525.1	543.1	512.1	482.5
72.5°	424.5	457.5	472.1	442.9	413.3
75°	320.2	349.8	367.8	343.3	311.6
77.5°	227.2	255.1	270.0	248.7	222.4
80°	166.6	196.2	207.7	189.9	168.8
82.5°	118.1	142.7	150.6	139.9	125.5
85°	54.1	71.0	80.1	75.6	71.4
87.5°	14.1	26.7	34.7	35.2	36.9
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0

TEST NUMBER: P564711

CATALOG NUMBER: SQ4-PW1-050U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)