

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P564902

Luminaire Tested: **SQ4-PW1-0U-125D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564902  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4165.4 lumens  
Efficiency: N/A  
Efficacy: 95.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 43.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564902  
CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564902

CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15105	15105	15105
5°	15203	15082	15016
10°	15081	14960	14878
15°	14922	14756	14701
20°	14743	14516	14488
25°	14537	14273	14229
30°	14230	14015	13923
35°	13825	13631	13550
40°	13394	13186	13134
45°	12873	12705	12647
50°	12340	12236	12153
55°	11763	11763	11578
60°	11046	11260	10859
65°	10108	10612	9857
70°	8910	9768	8678
75°	7611	8741	7404
80°	5903	7359	5977
85°	3822	5653	5039



TEST NUMBER: P564902

CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.2	3.7
10°-20°	435.3	10.4
20°-30°	645.6	15.5
30°-40°	755.4	18.1
40°-50°	752.1	18.1
50°-60°	649.5	15.6
60°-70°	467.5	11.2
70°-80°	245.2	5.9
80°-90°	60.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1235.0	29.6
0°-40°	1990.5	47.8
0°-60°	3392.0	81.4
0°-90°	4165.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4165.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1642	1623	1628	1624	1621	155
15°	1562	1542	1545	1542	1539	440
25°	1428	1404	1402	1394	1398	657
35°	1228	1211	1210	1199	1203	767
45°	987	978	974	971	969	761
55°	731	730	731	721	720	653
65°	463	477	486	467	452	459
75°	214	233	245	229	208	229
85°	36	47	53	50	48	49
90°	0	0	0	0	0	



TEST NUMBER: P564902

CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1646.4	1632.9	1637.2	1633.5	1625.6
5°	1641.5	1623.2	1628.5	1624.1	1621.3
7.5°	1624.8	1607.9	1611.8	1607.1	1605.5
10°	1609.8	1592.9	1596.8	1591.0	1588.1
12.5°	1592.5	1574.4	1578.3	1572.5	1570.8
15°	1562.2	1542.4	1544.9	1541.9	1539.1
17.5°	1527.0	1507.0	1507.4	1502.7	1502.2
20°	1501.6	1480.4	1478.5	1472.8	1475.6
22.5°	1473.9	1451.6	1449.7	1441.7	1445.6
25°	1428.0	1404.1	1402.1	1393.5	1397.7
27.5°	1374.9	1351.3	1351.3	1339.3	1343.8
30°	1335.7	1313.1	1315.5	1301.2	1306.9
32.5°	1294.2	1273.9	1275.1	1260.8	1266.5
35°	1227.5	1210.6	1210.2	1198.8	1203.0
37.5°	1159.4	1144.5	1142.1	1135.5	1136.7
40°	1112.1	1099.4	1094.8	1090.5	1090.5
42.5°	1062.5	1050.9	1046.4	1043.2	1042.0
45°	986.6	978.2	973.7	970.7	969.3
47.5°	911.6	903.7	899.8	897.8	896.3
50°	859.7	854.1	852.5	848.1	846.7
52.5°	807.8	804.4	802.9	797.4	795.9
55°	731.3	729.9	731.3	721.2	719.8
57.5°	651.7	654.0	658.6	645.0	641.6
60°	598.6	604.3	610.2	594.2	588.5
62.5°	544.4	553.4	561.7	543.3	535.4
65°	463.0	477.1	486.1	467.0	451.5
67.5°	384.6	402.0	412.8	392.2	374.7
70°	330.3	350.1	362.1	341.4	321.7
72.5°	283.0	305.0	314.7	295.3	275.5
75°	213.5	233.2	245.2	228.9	207.7
77.5°	151.5	170.1	180.0	165.8	148.3
80°	111.1	130.8	138.5	126.6	112.5
82.5°	78.8	95.1	100.4	93.3	83.7
85°	36.1	47.3	53.4	50.4	47.6
87.5°	9.2	17.1	21.9	22.0	23.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)