

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564926

Luminaire Tested: **SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564926
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5139.9 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 41.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564926
CATALOG NUMBER: SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564926

CATALOG NUMBER: SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34	27
2	86	78	72	67	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	35	33	28	26	24	20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	35	31	31	27	24	22	20	18	15
6	60	48	41	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6044	6044	6044
5°	6083	6035	6009
10°	6034	5986	5954
15°	5971	5905	5883
20°	5899	5809	5798
25°	5817	5711	5694
30°	5694	5608	5571
35°	5532	5455	5422
40°	5360	5276	5256
45°	5151	5083	5061
50°	4938	4896	4863
55°	4707	4707	4633
60°	4419	4504	4346
65°	4045	4246	3945
70°	3566	3909	3472
75°	3044	3497	2962
80°	2359	2943	2391
85°	1524	2265	2011



TEST NUMBER: P564926

CATALOG NUMBER: SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	1.2
10°-20°	174.2	3.4
20°-30°	258.3	5.0
30°-40°	302.3	5.9
40°-50°	300.9	5.9
50°-60°	259.9	5.1
60°-70°	187.1	3.6
70°-80°	98.1	1.9
80°-90°	25.4	0.5
90°-100°	250.2	4.9
100°-110°	690.9	13.4
110°-120°	712.5	13.9
120°-130°	572.6	11.1
130°-140°	450.0	8.8
140°-150°	345.1	6.7
150°-160°	248.0	4.8
160°-170°	151.7	3.0
170°-180°	51.1	1.0
0°-30°	494.2	9.6
0°-40°	796.5	15.5
0°-60°	1357.3	26.4
0°-90°	1667.9	32.4
90°-120°	1653.6	32.2
90°-150°	3021.2	58.8
90°-180°	3472.0	67.5
0°-180°	5139.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	657	650	652	650	649	62
15°	625	617	618	617	616	176
25°	571	562	561	558	559	263
35°	491	484	484	480	481	307
45°	395	391	390	388	388	305
55°	293	292	293	289	288	261
65°	185	191	194	187	181	184
75°	85	93	98	92	83	92
85°	14	19	21	20	19	19
90°	2	3	7	8	8	3
95°	37	135	454	187	121	39
105°	123	190	760	1160	1093	131
115°	221	267	612	1212	1378	217
125°	303	344	555	939	1102	269
135°	364	404	540	761	858	282
145°	422	452	533	648	697	264
155°	476	492	528	581	599	219
165°	516	522	531	552	556	145
175°	534	535	532	540	538	51
180°	534	534	534	534	534	

TEST NUMBER: P564926

CATALOG NUMBER: SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	655.1	655.1	655.1	655.1	655.1
2.5°	658.8	653.4	655.1	653.6	650.5
5°	656.8	649.5	651.6	649.9	648.8
7.5°	650.1	643.4	644.9	643.1	642.4
10°	644.1	637.4	638.9	636.6	635.5
12.5°	637.2	630.0	631.6	629.2	628.6
15°	625.1	617.2	618.2	617.0	615.9
17.5°	611.0	603.0	603.2	601.3	601.1
20°	600.8	592.4	591.6	589.3	590.5
22.5°	589.8	580.9	580.1	576.9	578.5
25°	571.4	561.8	561.0	557.6	559.3
27.5°	550.2	540.7	540.7	535.9	537.7
30°	534.5	525.4	526.4	520.7	522.9
32.5°	517.9	509.7	510.2	504.5	506.8
35°	491.2	484.4	484.3	479.7	481.4
37.5°	463.9	458.0	457.0	454.4	454.8
40°	445.0	439.9	438.1	436.4	436.4
42.5°	425.2	420.5	418.7	417.4	417.0
45°	394.8	391.4	389.6	388.4	387.9
47.5°	364.8	361.6	360.0	359.2	358.7
50°	344.0	341.7	341.1	339.4	338.8
52.5°	323.2	321.9	321.3	319.1	318.5
55°	292.6	292.1	292.6	288.6	288.0
57.5°	260.8	261.7	263.5	258.1	256.7
60°	239.5	241.8	244.1	237.7	235.5
62.5°	217.8	221.4	224.8	217.4	214.3
65°	185.3	190.9	194.5	186.9	180.7
67.5°	153.9	160.9	165.2	157.0	150.0
70°	132.2	140.1	144.9	136.6	128.7
72.5°	113.2	122.0	125.9	118.1	110.2
75°	85.4	93.3	98.1	91.6	83.1
77.5°	60.6	68.1	72.0	66.3	59.3
80°	44.4	52.3	55.4	50.7	45.0
82.5°	31.5	38.1	40.2	37.3	33.5
85°	14.4	18.9	21.4	20.2	19.0
87.5°	4.0	7.5	10.1	10.3	10.9
90°	1.7	3.4	6.8	7.7	8.5
92.5°	15.4	63.9	114.2	41.7	32.5
95°	36.8	135.4	454.0	186.6	121.4
97.5°	60.9	151.7	672.5	517.8	375.0
100°	78.7	161.4	753.2	758.6	616.4
102.5°	95.8	172.5	769.0	937.3	802.5
105°	123.1	190.0	760.1	1160.4	1092.7
107.5°	152.2	211.7	717.7	1268.0	1292.7
110°	172.7	226.2	684.8	1291.1	1371.4



TEST NUMBER: P564926

CATALOG NUMBER: SQ4-PW1-100U-050D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	191.2	242.7	654.1	1272.9	1391.2
115°	220.6	266.6	612.2	1211.9	1378.2
117.5°	246.2	292.0	584.6	1126.0	1315.3
120°	263.3	308.5	573.7	1067.9	1258.5
122.5°	279.8	322.9	564.8	1013.7	1194.2
125°	302.7	344.5	554.9	939.1	1102.1
127.5°	322.2	364.0	549.1	876.0	1016.6
130°	335.2	377.0	546.3	837.4	965.3
132.5°	347.5	387.3	543.6	805.0	920.8
135°	364.2	403.5	539.5	760.6	857.6
137.5°	383.0	418.8	537.4	723.3	806.1
140°	393.3	428.4	536.1	698.5	771.2
142.5°	404.9	437.4	534.7	676.4	740.4
145°	422.4	451.6	532.7	647.5	696.8
147.5°	439.1	464.7	530.8	623.1	661.4
150°	451.4	472.3	530.1	608.6	639.5
152.5°	461.0	480.6	529.4	596.2	621.7
155°	476.2	492.1	528.4	581.0	599.3
157.5°	490.2	502.5	528.6	569.9	582.4
160°	498.5	509.3	529.2	563.6	572.8
162.5°	505.3	514.8	529.9	558.1	565.3
165°	515.6	522.2	530.9	551.6	555.7
167.5°	523.4	527.4	531.8	547.6	548.9
170°	527.5	530.9	531.8	545.5	545.5
172.5°	530.9	533.0	531.8	542.7	542.1
175°	534.4	535.2	531.8	539.5	537.8
177.5°	535.7	535.1	531.6	536.4	535.0
180°	534.4	534.4	534.4	534.4	534.4

(END OF REPORT)