

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564735

Luminaire Tested: **SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564735
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6383.8 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 54.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564735
CATALOG NUMBER: SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564735

CATALOG NUMBER: SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28				
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24				
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20				
5	67	55	47	41	60	50	44	38	42	36	32	33	30	27	26	23	21	18				
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	16				
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14				
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12				
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11				
10	45	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6044	6044	6044
5°	6084	6035	6008
10°	6035	5986	5953
15°	5970	5904	5883
20°	5900	5809	5797
25°	5817	5711	5693
30°	5694	5608	5571
35°	5532	5454	5422
40°	5360	5276	5255
45°	5151	5083	5061
50°	4938	4896	4863
55°	4707	4707	4633
60°	4420	4505	4345
65°	4045	4247	3944
70°	3566	3908	3473
75°	3044	3498	2963
80°	2363	2943	2391
85°	1524	2258	2018



TEST NUMBER: P564735

CATALOG NUMBER: SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	1.4
10°-20°	261.2	4.1
20°-30°	387.5	6.1
30°-40°	453.4	7.1
40°-50°	451.4	7.1
50°-60°	389.8	6.1
60°-70°	280.6	4.4
70°-80°	147.1	2.3
80°-90°	38.0	0.6
90°-100°	281.1	4.4
100°-110°	773.3	12.1
110°-120°	798.1	12.5
120°-130°	639.5	10.0
130°-140°	502.3	7.9
140°-150°	384.9	6.0
150°-160°	276.7	4.3
160°-170°	169.2	2.7
170°-180°	57.0	0.9
0°-30°	741.3	11.6
0°-40°	1194.7	18.7
0°-60°	2035.9	31.9
0°-90°	2501.6	39.2
90°-120°	1852.5	29.0
90°-150°	3379.1	52.9
90°-180°	3882.0	60.8
0°-180°	6383.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	983	983	983	983	983	
5°	985	974	978	975	973	93
15°	938	926	927	926	924	264
25°	857	843	842	836	839	394
35°	737	727	726	720	722	461
45°	592	587	584	583	582	457
55°	439	438	439	433	432	392
65°	278	286	292	280	271	275
75°	128	140	147	137	125	137
85°	22	28	32	30	29	29
90°	1	5	9	11	11	4
95°	42	153	497	212	136	44
105°	138	213	852	1298	1211	146
115°	245	298	683	1361	1544	241
125°	337	384	620	1049	1229	301
135°	407	452	602	848	960	314
145°	470	503	593	723	778	295
155°	532	550	590	650	668	245
165°	576	583	592	616	620	162
175°	596	597	593	601	600	57
180°	596	596	596	596	596	



TEST NUMBER: P564735

CATALOG NUMBER: SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.7	982.7	982.7	982.7	982.7
2.5°	988.2	980.1	982.7	980.5	975.7
5°	985.3	974.2	977.5	974.8	973.1
7.5°	975.2	965.1	967.4	964.6	963.6
10°	966.2	956.0	958.4	954.9	953.2
12.5°	955.8	945.0	947.3	943.8	942.8
15°	937.6	925.8	927.2	925.5	923.8
17.5°	916.5	904.5	904.7	902.0	901.6
20°	901.3	888.6	887.4	884.0	885.7
22.5°	884.7	871.3	870.1	865.3	867.7
25°	857.1	842.7	841.5	836.4	838.9
27.5°	825.3	811.0	811.1	803.8	806.6
30°	801.7	788.2	789.6	781.0	784.4
32.5°	776.8	764.6	765.3	756.8	760.2
35°	736.8	726.6	726.4	719.5	722.1
37.5°	695.9	686.9	685.5	681.6	682.2
40°	667.5	659.9	657.1	654.5	654.5
42.5°	637.7	630.8	628.0	626.1	625.4
45°	592.2	587.1	584.4	582.6	581.8
47.5°	547.2	542.4	540.1	538.8	538.0
50°	516.0	512.6	511.7	509.1	508.2
52.5°	484.8	482.8	481.9	478.6	477.7
55°	438.9	438.1	438.9	432.9	432.0
57.5°	391.2	392.5	395.3	387.1	385.1
60°	359.3	362.7	366.2	356.6	353.2
62.5°	326.7	332.2	337.1	326.1	321.4
65°	277.9	286.4	291.8	280.3	271.0
67.5°	230.8	241.3	247.8	235.4	224.9
70°	198.3	210.1	217.3	204.9	193.1
72.5°	169.9	183.1	188.9	177.2	165.4
75°	128.1	140.0	147.2	137.4	124.7
77.5°	90.9	102.1	108.0	99.5	89.0
80°	66.7	78.5	83.1	76.0	67.5
82.5°	47.3	57.1	60.3	56.0	50.2
85°	21.6	28.4	32.0	30.3	28.6
87.5°	5.8	11.3	14.9	15.5	16.1
90°	1.3	5.0	8.9	11.4	11.4
92.5°	17.5	74.8	129.6	49.8	40.8
95°	41.8	153.4	497.0	212.5	135.7
97.5°	68.2	170.1	758.5	584.4	412.3
100°	87.5	180.5	840.6	848.5	692.3
102.5°	105.7	192.8	861.9	1052.6	909.3
105°	138.2	212.6	852.0	1297.6	1210.8
107.5°	169.1	237.1	803.6	1417.6	1443.4
110°	191.5	253.4	767.1	1447.4	1536.7



TEST NUMBER: P564735

CATALOG NUMBER: SQ4-PW1-075U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.7	271.7	730.6	1428.2	1564.1
115°	244.7	298.0	683.4	1360.8	1544.3
117.5°	276.1	325.2	653.5	1266.3	1473.8
120°	295.4	342.5	640.3	1195.4	1409.9
122.5°	312.7	359.8	631.2	1133.3	1336.9
125°	337.3	384.4	620.0	1048.8	1228.6
127.5°	360.6	405.5	612.6	978.3	1136.0
130°	372.8	418.6	608.6	936.4	1080.2
132.5°	387.0	432.8	605.5	899.6	1029.5
135°	407.0	451.6	602.2	848.2	959.8
137.5°	425.8	467.2	599.5	806.7	898.7
140°	440.0	478.4	598.4	779.1	862.2
142.5°	452.1	487.6	596.4	754.5	825.6
145°	470.4	502.6	593.4	722.7	778.5
147.5°	489.9	517.7	591.9	694.5	739.2
150°	502.1	526.9	590.8	679.1	713.8
152.5°	513.2	536.1	589.8	665.8	694.5
155°	532.5	549.9	589.6	649.6	668.2
157.5°	546.5	560.6	589.6	636.3	649.2
160°	556.6	567.8	589.6	629.1	639.0
162.5°	564.7	573.9	590.6	623.0	630.9
165°	575.6	583.1	592.1	616.3	620.0
167.5°	583.2	588.9	593.4	610.6	611.6
170°	588.3	592.0	593.4	608.6	608.6
172.5°	592.4	594.1	593.4	605.5	604.5
175°	595.9	597.1	593.4	601.0	599.7
177.5°	596.9	596.9	592.9	598.9	596.9
180°	595.9	595.9	595.9	595.9	595.9

(END OF REPORT)