

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565142

Luminaire Tested: **SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565142
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7665.9 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 63.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565142
CATALOG NUMBER: SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P565142

CATALOG NUMBER: SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	34	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	26	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	22	21	17
5	65	54	46	40	59	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	55	44	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8908	8908	8908
5°	8966	8895	8856
10°	8894	8822	8775
15°	8800	8703	8670
20°	8695	8562	8545
25°	8574	8418	8391
30°	8393	8265	8211
35°	8153	8038	7991
40°	7900	7777	7745
45°	7593	7492	7459
50°	7277	7217	7168
55°	6938	6938	6828
60°	6514	6639	6405
65°	5962	6259	5814
70°	5255	5759	5117
75°	4488	5155	4367
80°	3480	4341	3528
85°	2255	3335	2975



TEST NUMBER: P565142

CATALOG NUMBER: SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.2
10°-20°	256.7	3.3
20°-30°	380.8	5.0
30°-40°	445.5	5.8
40°-50°	443.5	5.8
50°-60°	383.0	5.0
60°-70°	275.7	3.6
70°-80°	144.6	1.9
80°-90°	37.5	0.5
90°-100°	375.4	4.9
100°-110°	1014.9	13.2
110°-120°	1067.1	13.9
120°-130°	866.7	11.3
130°-140°	679.9	8.9
140°-150°	521.8	6.8
150°-160°	375.3	4.9
160°-170°	229.3	3.0
170°-180°	77.3	1.0
0°-30°	728.4	9.5
0°-40°	1173.9	15.3
0°-60°	2000.5	26.1
0°-90°	2458.3	32.1
90°-120°	2457.4	32.1
90°-150°	4525.8	59.0
90°-180°	5208.0	67.9
0°-180°	7665.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	966	966	966	966	966	
5°	968	957	960	958	956	92
15°	921	910	911	909	908	260
25°	842	828	827	822	824	387
35°	724	714	714	707	710	453
45°	582	577	574	572	572	449
55°	431	430	431	425	424	385
65°	273	281	287	275	266	271
75°	126	138	145	135	122	135
85°	21	28	32	30	28	28
90°	2	5	11	12	11	5
95°	58	204	624	323	192	61
105°	189	292	1126	1661	1593	199
115°	332	406	934	1808	2041	328
125°	455	521	842	1420	1668	405
135°	545	610	819	1147	1298	421
145°	634	681	808	982	1056	397
155°	716	744	801	880	909	330
165°	779	787	804	836	840	219
175°	809	808	805	816	814	77
180°	808	808	808	808	808	

TEST NUMBER: P565142

CATALOG NUMBER: SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	965.5	965.5	965.5	965.5	965.5
2.5°	971.0	963.0	965.5	963.4	958.7
5°	968.1	957.3	960.4	957.9	956.2
7.5°	958.2	948.3	950.6	947.8	946.8
10°	949.4	939.4	941.7	938.3	936.6
12.5°	939.2	928.5	930.8	927.4	926.4
15°	921.3	909.7	911.1	909.4	907.7
17.5°	900.6	888.7	889.0	886.3	885.9
20°	885.6	873.1	872.0	868.6	870.3
22.5°	869.2	856.1	855.0	850.2	852.6
25°	842.2	828.1	826.9	821.8	824.3
27.5°	810.9	796.9	796.9	789.9	792.5
30°	787.8	774.4	775.8	767.4	770.7
32.5°	763.3	751.3	752.0	743.6	746.9
35°	723.9	714.0	713.7	707.0	709.5
37.5°	683.8	675.0	673.6	669.7	670.4
40°	655.9	648.4	645.7	643.1	643.1
42.5°	626.6	619.8	617.1	615.2	614.5
45°	581.9	576.9	574.2	572.5	571.7
47.5°	537.6	533.0	530.7	529.5	528.6
50°	507.0	503.7	502.8	500.2	499.4
52.5°	476.4	474.4	473.5	470.2	469.4
55°	431.3	430.5	431.3	425.3	424.5
57.5°	384.3	385.7	388.4	380.4	378.4
60°	353.0	356.4	359.8	350.4	347.1
62.5°	321.1	326.4	331.3	320.4	315.8
65°	273.1	281.4	286.7	275.4	266.3
67.5°	226.8	237.1	243.5	231.3	221.0
70°	194.8	206.5	213.5	201.4	189.7
72.5°	166.9	179.9	185.6	174.1	162.5
75°	125.9	137.5	144.6	135.0	122.5
77.5°	89.3	100.3	106.2	97.8	87.5
80°	65.5	77.1	81.7	74.7	66.4
82.5°	46.4	56.1	59.2	55.0	49.3
85°	21.3	27.9	31.5	29.7	28.1
87.5°	5.8	11.1	15.2	15.4	15.9
90°	1.7	5.1	11.3	12.2	11.3
92.5°	24.7	90.0	177.5	77.1	55.8
95°	58.3	204.5	624.3	323.1	192.1
97.5°	93.6	234.5	973.1	805.3	591.4
100°	120.0	246.6	1081.6	1128.0	912.0
102.5°	144.3	263.5	1119.8	1372.6	1211.1
105°	188.7	291.5	1125.9	1660.8	1592.8
107.5°	229.7	323.6	1076.7	1840.6	1863.2
110°	261.7	346.7	1032.9	1888.9	1984.9



TEST NUMBER: P565142

CATALOG NUMBER: SQ4-PW1-150U-075D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.2	369.8	992.6	1879.2	2040.6
115°	332.1	406.1	933.8	1807.6	2040.6
117.5°	373.2	442.5	895.0	1698.3	1962.3
120°	398.2	466.2	872.0	1619.8	1889.3
122.5°	421.9	488.5	858.1	1535.7	1807.2
125°	454.7	521.0	841.6	1420.2	1668.5
127.5°	485.0	550.1	831.9	1326.0	1544.3
130°	501.7	568.8	827.7	1267.8	1465.0
132.5°	519.1	585.5	823.5	1215.3	1396.8
135°	545.1	609.7	819.0	1146.7	1298.1
137.5°	571.4	632.4	815.2	1091.2	1214.4
140°	589.5	646.4	813.8	1055.4	1165.0
142.5°	606.9	660.4	811.0	1023.1	1119.1
145°	633.8	681.4	807.7	981.6	1056.4
147.5°	658.3	700.5	803.9	944.0	1001.4
150°	676.4	713.8	802.5	923.5	969.4
152.5°	693.1	725.8	801.8	904.6	942.3
155°	715.5	743.6	800.8	880.5	909.4
157.5°	738.8	758.4	800.9	863.8	882.8
160°	752.1	768.2	801.6	853.2	866.8
162.5°	762.5	775.9	802.3	844.8	855.0
165°	779.0	786.7	804.2	835.6	839.9
167.5°	790.3	795.6	804.4	827.8	829.8
170°	797.3	799.8	805.1	824.2	824.2
172.5°	802.8	803.3	805.1	820.0	819.4
175°	808.6	807.7	805.1	815.5	813.8
177.5°	810.5	808.4	804.9	811.8	809.8
180°	807.7	807.7	807.7	807.7	807.7

(END OF REPORT)