

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P565071

Luminaire Tested: **SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565071
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11381.2 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 102.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565071
CATALOG NUMBER: SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P565071

CATALOG NUMBER: SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	69	64	61	57	54	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	49	46	44	41	38	34	32	30	26
4	73	63	55	49	67	58	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	14
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11837	11837	11837
5°	11913	11819	11766
10°	11818	11723	11659
15°	11693	11563	11520
20°	11553	11376	11353
25°	11391	11184	11150
30°	11151	10982	10910
35°	10834	10681	10617
40°	10496	10333	10292
45°	10088	9955	9911
50°	9669	9588	9524
55°	9218	9218	9073
60°	8655	8823	8510
65°	7922	8316	7724
70°	6983	7654	6800
75°	5963	6849	5803
80°	4626	5767	4683
85°	2992	4425	3952



TEST NUMBER: P565071

CATALOG NUMBER: SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.2	1.6
10°-20°	511.6	4.5
20°-30°	758.9	6.7
30°-40°	888.0	7.8
40°-50°	884.0	7.8
50°-60°	763.4	6.7
60°-70°	549.5	4.8
70°-80°	288.2	2.5
80°-90°	73.8	0.6
90°-100°	469.8	4.1
100°-110°	1265.4	11.1
110°-120°	1328.0	11.7
120°-130°	1077.7	9.5
130°-140°	845.2	7.4
140°-150°	648.9	5.7
150°-160°	466.6	4.1
160°-170°	285.0	2.5
170°-180°	96.1	0.8
0°-30°	1451.7	12.8
0°-40°	2339.7	20.6
0°-60°	3987.1	35.0
0°-90°	4898.5	43.0
90°-120°	3063.3	26.9
90°-150°	5635.0	49.5
90°-180°	6483.0	57.0
0°-180°	11381.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1924	1924	1924	1924	1924	
5°	1930	1908	1914	1909	1906	183
15°	1836	1813	1816	1812	1809	518
25°	1678	1650	1648	1638	1643	772
35°	1443	1423	1422	1409	1414	902
45°	1160	1150	1144	1141	1139	895
55°	860	858	860	848	846	767
65°	544	561	571	549	531	539
75°	251	274	288	269	244	269
85°	42	56	63	59	56	56
90°	3	8	15	17	17	7
95°	72	256	770	394	272	75
105°	234	364	1400	2094	1965	246
115°	413	506	1165	2252	2547	407
125°	564	648	1046	1769	2081	504
135°	679	758	1017	1427	1616	524
145°	786	847	1004	1220	1310	493
155°	892	924	995	1094	1130	410
165°	967	978	999	1039	1044	273
175°	1006	1004	1000	1014	1012	96
180°	1004	1004	1004	1004	1004	



TEST NUMBER: P565071

CATALOG NUMBER: SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1924.4	1924.4	1924.4	1924.4	1924.4
2.5°	1935.2	1919.3	1924.4	1920.1	1910.8
5°	1929.5	1907.9	1914.2	1909.1	1905.7
7.5°	1909.8	1889.9	1894.5	1889.1	1887.1
10°	1892.2	1872.3	1876.9	1870.1	1866.7
12.5°	1871.8	1850.6	1855.2	1848.4	1846.4
15°	1836.2	1813.0	1815.9	1812.4	1809.1
17.5°	1794.9	1771.3	1771.8	1766.4	1765.7
20°	1765.0	1740.1	1737.9	1731.2	1734.5
22.5°	1732.5	1706.3	1704.0	1694.6	1699.2
25°	1678.5	1650.4	1648.0	1638.0	1642.9
27.5°	1616.1	1588.3	1588.3	1574.2	1579.5
30°	1570.0	1543.5	1546.3	1529.5	1536.1
32.5°	1521.2	1497.3	1498.8	1482.0	1488.6
35°	1442.9	1423.0	1422.5	1409.1	1414.0
37.5°	1362.8	1345.3	1342.5	1334.7	1336.1
40°	1307.2	1292.3	1286.9	1281.8	1281.8
42.5°	1248.9	1235.3	1229.9	1226.2	1224.8
45°	1159.7	1149.8	1144.5	1141.0	1139.4
47.5°	1071.6	1062.3	1057.7	1055.2	1053.6
50°	1010.5	1003.9	1002.0	996.9	995.3
52.5°	949.5	945.5	943.7	937.2	935.6
55°	859.6	858.0	859.6	847.7	846.1
57.5°	766.0	768.7	774.2	758.1	754.2
60°	703.6	710.3	717.2	698.4	691.8
62.5°	639.9	650.5	660.2	638.7	629.4
65°	544.3	560.8	571.4	548.9	530.7
67.5°	452.0	472.6	485.3	461.0	440.5
70°	388.3	411.5	425.6	401.3	378.1
72.5°	332.7	358.5	370.0	347.0	323.8
75°	250.9	274.1	288.2	269.0	244.2
77.5°	178.0	199.9	211.6	194.9	174.3
80°	130.6	153.8	162.8	148.8	132.2
82.5°	92.6	111.8	118.0	109.6	98.3
85°	42.4	55.7	62.7	59.3	56.0
87.5°	11.4	21.6	28.8	29.1	30.5
90°	2.6	7.6	15.4	16.6	16.6
92.5°	31.2	110.3	218.0	104.9	72.9
95°	71.6	255.5	770.1	393.8	272.5
97.5°	114.4	292.5	1207.9	1009.1	760.9
100°	147.1	307.2	1347.0	1409.4	1169.2
102.5°	178.8	327.9	1393.1	1709.2	1512.1
105°	234.1	364.2	1399.5	2093.7	1964.9
107.5°	286.3	402.4	1339.9	2291.4	2324.6
110°	321.1	431.2	1285.6	2352.7	2474.1



TEST NUMBER: P565071

CATALOG NUMBER: SQ4-PW1-125U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.9	460.0	1233.4	2339.1	2538.5
115°	413.2	505.8	1165.4	2251.8	2547.0
117.5°	463.6	550.4	1112.7	2112.3	2441.0
120°	496.3	580.2	1086.1	2012.2	2350.0
122.5°	525.0	607.8	1066.6	1909.9	2246.6
125°	564.1	648.0	1046.4	1768.6	2081.3
127.5°	601.8	684.3	1033.6	1644.0	1923.2
130°	624.3	706.8	1028.5	1572.6	1817.8
132.5°	646.8	728.3	1023.4	1509.8	1734.9
135°	679.3	758.1	1017.0	1426.8	1615.7
137.5°	710.2	785.8	1013.7	1356.5	1511.6
140°	731.7	804.3	1010.6	1313.1	1453.2
142.5°	754.2	821.8	1008.6	1272.7	1390.8
145°	785.5	846.7	1004.2	1219.9	1309.9
147.5°	819.2	872.5	999.9	1175.4	1246.2
150°	841.7	888.0	997.8	1147.5	1206.3
152.5°	862.2	902.5	996.8	1124.8	1172.6
155°	891.6	924.2	995.2	1094.5	1129.6
157.5°	917.5	942.7	995.5	1073.3	1096.8
160°	933.8	955.1	996.5	1060.9	1078.4
162.5°	948.2	965.4	997.6	1050.5	1063.0
165°	967.1	978.4	999.1	1038.9	1043.9
167.5°	982.5	989.0	1000.4	1029.8	1031.8
170°	992.7	995.2	1000.4	1024.7	1024.7
172.5°	998.8	999.3	1001.4	1019.6	1019.6
175°	1005.5	1004.2	1000.4	1014.4	1011.9
177.5°	1008.3	1006.3	1001.1	1009.3	1007.3
180°	1004.2	1004.2	1004.2	1004.2	1004.2

(END OF REPORT)