

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P565119

Luminaire Tested: **SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P565119
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10314.0 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P565119
CATALOG NUMBER: SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P565119

CATALOG NUMBER: SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	27	21				21
2	84	77	71	66	74	68	64	59	53	50	47	39	37	35	25	24	23	17				17
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	22	21	20	15				15
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13				13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11				11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10				10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	9				9
8	50	38	31	26	45	35	28	24	27	22	19	20	17	15	14	12	10	8				8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7				7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6				6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6044	6044	6044
5°	6084	6035	6008
10°	6035	5986	5953
15°	5970	5904	5883
20°	5900	5809	5797
25°	5817	5711	5693
30°	5694	5608	5571
35°	5532	5454	5422
40°	5360	5276	5255
45°	5151	5083	5061
50°	4938	4896	4863
55°	4707	4707	4633
60°	4420	4505	4345
65°	4045	4247	3944
70°	3566	3908	3473
75°	3044	3498	2963
80°	2363	2943	2391
85°	1524	2258	2018



TEST NUMBER: P565119

CATALOG NUMBER: SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	0.9
10°-20°	261.2	2.5
20°-30°	387.5	3.8
30°-40°	453.4	4.4
40°-50°	451.4	4.4
50°-60°	389.8	3.8
60°-70°	280.6	2.7
70°-80°	147.1	1.4
80°-90°	39.0	0.4
90°-100°	563.1	5.5
100°-110°	1522.4	14.8
110°-120°	1600.6	15.5
120°-130°	1300.1	12.6
130°-140°	1019.8	9.9
140°-150°	782.7	7.6
150°-160°	562.9	5.5
160°-170°	343.9	3.3
170°-180°	115.9	1.1
0°-30°	741.3	7.2
0°-40°	1194.7	11.6
0°-60°	2035.9	19.7
0°-90°	2502.7	24.3
90°-120°	3686.0	35.7
90°-150°	6788.7	65.8
90°-180°	7811.0	75.7
0°-180°	10314.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	983	983	983	983	983	
5°	985	974	978	975	973	93
15°	938	926	927	926	924	264
25°	857	843	842	836	839	394
35°	737	727	726	720	722	461
45°	592	587	584	583	582	457
55°	439	438	439	433	432	392
65°	278	286	292	280	271	275
75°	128	140	147	137	125	137
85°	22	28	32	30	29	29
90°	3	8	17	18	17	7
95°	87	307	936	485	288	91
105°	283	437	1689	2491	2389	298
115°	498	609	1401	2712	3061	492
125°	682	782	1262	2130	2503	608
135°	818	915	1228	1720	1947	632
145°	951	1022	1212	1472	1585	595
155°	1073	1115	1201	1321	1364	495
165°	1168	1180	1206	1253	1260	329
175°	1213	1212	1208	1223	1221	115
180°	1212	1212	1212	1212	1212	

TEST NUMBER: P565119

CATALOG NUMBER: SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	982.7	982.7	982.7	982.7	982.7
2.5°	988.2	980.1	982.7	980.5	975.7
5°	985.3	974.2	977.5	974.8	973.1
7.5°	975.2	965.1	967.4	964.6	963.6
10°	966.2	956.0	958.4	954.9	953.2
12.5°	955.8	945.0	947.3	943.8	942.8
15°	937.6	925.8	927.2	925.5	923.8
17.5°	916.5	904.5	904.7	902.0	901.6
20°	901.3	888.6	887.4	884.0	885.7
22.5°	884.7	871.3	870.1	865.3	867.7
25°	857.1	842.7	841.5	836.4	838.9
27.5°	825.3	811.0	811.1	803.8	806.6
30°	801.7	788.2	789.6	781.0	784.4
32.5°	776.8	764.6	765.3	756.8	760.2
35°	736.8	726.6	726.4	719.5	722.1
37.5°	695.9	686.9	685.5	681.6	682.2
40°	667.5	659.9	657.1	654.5	654.5
42.5°	637.7	630.8	628.0	626.1	625.4
45°	592.2	587.1	584.4	582.6	581.8
47.5°	547.2	542.4	540.1	538.8	538.0
50°	516.0	512.6	511.7	509.1	508.2
52.5°	484.8	482.8	481.9	478.6	477.7
55°	438.9	438.1	438.9	432.9	432.0
57.5°	391.2	392.5	395.3	387.1	385.1
60°	359.3	362.7	366.2	356.6	353.2
62.5°	326.7	332.2	337.1	326.1	321.4
65°	277.9	286.4	291.8	280.3	271.0
67.5°	230.8	241.3	247.8	235.4	224.9
70°	198.3	210.1	217.3	204.9	193.1
72.5°	169.9	183.1	188.9	177.2	165.4
75°	128.1	140.0	147.2	137.4	124.7
77.5°	90.9	102.1	108.0	99.5	89.0
80°	66.7	78.5	83.1	76.0	67.5
82.5°	47.3	57.1	60.3	56.0	50.2
85°	21.6	28.4	32.0	30.3	28.6
87.5°	6.1	11.8	16.6	16.8	17.2
90°	2.6	7.7	17.0	18.2	17.0
92.5°	37.0	135.0	266.3	115.6	83.7
95°	87.4	306.7	936.4	484.6	288.2
97.5°	140.3	351.8	1459.6	1207.9	887.1
100°	180.0	370.0	1622.4	1692.0	1368.1
102.5°	216.5	395.3	1679.8	2059.0	1816.7
105°	283.0	437.3	1688.9	2491.2	2389.2
107.5°	344.6	485.3	1615.1	2760.9	2794.8
110°	392.6	520.1	1549.3	2833.3	2977.4



TEST NUMBER: P565119

CATALOG NUMBER: SQ4-PW1-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.3	554.7	1488.8	2818.8	3060.9
115°	498.2	609.1	1400.7	2711.5	3060.9
117.5°	559.7	663.8	1342.5	2547.4	2943.5
120°	597.3	699.3	1308.1	2429.7	2833.9
122.5°	632.8	732.8	1287.2	2303.5	2710.8
125°	682.1	781.5	1262.4	2130.3	2502.7
127.5°	727.5	825.1	1247.8	1989.0	2316.4
130°	752.5	853.2	1241.6	1901.7	2197.5
132.5°	778.6	878.3	1235.3	1822.9	2095.3
135°	817.7	914.6	1228.5	1720.1	1947.1
137.5°	857.1	948.6	1222.8	1636.7	1821.6
140°	884.2	969.7	1220.7	1583.1	1747.6
142.5°	910.3	990.6	1216.5	1534.6	1678.7
145°	950.7	1022.1	1211.6	1472.3	1584.6
147.5°	987.5	1050.8	1205.8	1415.9	1502.1
150°	1014.6	1070.7	1203.7	1385.3	1454.1
152.5°	1039.7	1088.6	1202.7	1356.8	1413.4
155°	1073.3	1115.4	1201.1	1320.8	1364.1
157.5°	1108.3	1137.6	1201.4	1295.7	1324.2
160°	1128.1	1152.3	1202.4	1279.8	1300.2
162.5°	1143.7	1163.9	1203.5	1267.2	1282.5
165°	1168.5	1180.0	1206.3	1253.4	1259.8
167.5°	1185.5	1193.4	1206.6	1241.6	1244.7
170°	1195.9	1199.7	1207.6	1236.3	1236.3
172.5°	1204.3	1205.0	1207.6	1230.1	1229.0
175°	1212.9	1211.6	1207.6	1223.2	1220.7
177.5°	1215.7	1212.7	1207.4	1217.8	1214.7
180°	1211.6	1211.6	1211.6	1211.6	1211.6

(END OF REPORT)