

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519544

Luminaire Tested: **SQ4-WB-125U-125D-940-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519544
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-125D-940-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7872.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519544
CATALOG NUMBER: SQ4-WB-125U-125D-940-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519544

CATALOG NUMBER: SQ4-WB-125U-125D-940-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	46	46	40
2	90	83	78	73	82	77	72	68	64	61	58	53	51	49	43	41	40	35
3	83	74	67	62	76	68	63	58	58	54	50	48	45	43	39	37	35	31
4	76	66	59	54	70	61	55	50	52	47	44	44	40	38	36	33	31	28
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25
6	65	54	46	41	60	50	44	39	43	38	34	36	33	30	30	27	25	23
7	61	49	42	36	56	46	39	34	39	34	31	33	30	27	28	25	23	20
8	56	45	38	33	52	42	35	31	36	31	28	31	27	24	26	23	21	19
9	53	41	34	29	49	39	32	28	33	28	25	29	25	22	24	21	19	17
10	49	38	31	27	46	36	29	25	31	26	23	27	23	20	22	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22469	22469	22469
5°	22188	22109	22238
10°	20963	21153	21644
15°	19352	19801	20689
20°	17574	18235	19441
25°	15763	16622	18112
30°	14094	15016	16735
35°	12324	13215	15105
40°	10373	11197	13076
45°	8561	9299	10917
50°	7148	7791	9096
55°	6067	6687	7512
60°	5185	5798	5993
65°	4128	4875	3873
70°	3661	3806	2363
75°	3390	3087	1447
80°	3124	2837	1249
85°	2826	2604	1016



TEST NUMBER: P519544

CATALOG NUMBER: SQ4-WB-125U-125D-940-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.4	2.8
10°-20°	581.0	7.4
20°-30°	752.6	9.6
30°-40°	737.0	9.4
40°-50°	564.1	7.2
50°-60°	375.9	4.8
60°-70°	205.1	2.6
70°-80°	85.5	1.1
80°-90°	25.8	0.3
90°-100°	313.2	4.0
100°-110°	843.6	10.7
110°-120°	885.4	11.2
120°-130°	718.5	9.1
130°-140°	563.5	7.2
140°-150°	432.6	5.5
150°-160°	311.0	4.0
160°-170°	190.0	2.4
170°-180°	64.1	0.8
0°-30°	1556.9	19.8
0°-40°	2293.9	29.1
0°-60°	3233.9	41.1
0°-90°	3550.2	45.1
90°-120°	2042.2	25.9
90°-150°	3756.7	47.7
90°-180°	4322.0	54.9
0°-180°	7872.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2435	2435	2435	2435	2435	
5°	2396	2372	2387	2393	2401	223
15°	2026	2019	2073	2129	2166	566
25°	1548	1552	1633	1704	1779	712
35°	1094	1099	1173	1252	1341	680
45°	656	669	713	767	837	512
55°	377	393	416	431	467	342
65°	189	205	223	195	177	197
75°	95	95	87	59	41	102
85°	27	27	25	16	10	29
90°	2	5	10	11	11	5
95°	48	170	513	262	182	50
105°	156	243	933	1396	1310	164
115°	276	337	777	1501	1698	271
125°	376	432	698	1179	1388	336
135°	453	505	678	951	1077	350
145°	524	564	670	813	873	328
155°	594	616	664	730	753	274
165°	645	652	666	693	696	182
175°	670	670	667	676	675	64
180°	670	670	670	670	670	



TEST NUMBER: P519544

CATALOG NUMBER: SQ4-WB-125U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2435.3	2435.3	2435.3	2435.3	2435.3
2.5°	2441.3	2419.5	2425.0	2424.9	2418.2
5°	2395.7	2371.7	2387.2	2392.7	2401.1
7.5°	2306.8	2288.7	2316.9	2337.8	2354.7
10°	2237.6	2221.9	2257.9	2288.3	2310.3
12.5°	2157.2	2144.1	2188.7	2229.5	2258.1
15°	2026.0	2018.7	2073.0	2129.4	2166.0
17.5°	1885.6	1882.1	1944.4	2010.2	2057.0
20°	1789.9	1788.8	1857.2	1925.7	1980.1
22.5°	1693.3	1695.6	1767.4	1838.7	1900.6
25°	1548.4	1552.5	1632.8	1703.9	1779.2
27.5°	1414.4	1416.2	1499.2	1574.3	1654.6
30°	1322.9	1328.1	1409.5	1487.2	1570.8
32.5°	1231.4	1237.5	1317.1	1397.5	1482.8
35°	1094.2	1099.4	1173.3	1252.3	1341.1
37.5°	952.7	959.8	1025.4	1100.1	1187.4
40°	861.3	871.7	929.7	1000.0	1085.7
42.5°	773.2	786.2	839.9	906.6	983.9
45°	656.1	668.6	712.7	766.7	836.7
47.5°	555.2	569.7	603.5	650.0	709.7
50°	498.0	511.5	542.8	577.2	633.7
52.5°	447.5	461.1	489.0	515.5	563.6
55°	377.2	392.9	415.7	431.4	467.0
57.5°	319.5	334.5	352.6	359.7	381.3
60°	281.0	297.8	314.2	313.4	324.8
62.5°	246.0	260.2	276.5	265.2	265.9
65°	189.1	204.8	223.3	195.1	177.4
67.5°	152.8	156.1	175.2	136.1	115.0
70°	135.7	135.7	141.1	105.4	87.6
72.5°	119.5	119.5	114.6	85.7	67.1
75°	95.1	95.1	86.6	59.4	40.6
77.5°	73.3	72.5	66.3	44.3	29.5
80°	58.8	58.8	53.4	35.0	23.5
82.5°	45.9	45.9	41.5	27.3	17.5
85°	26.7	26.7	24.6	15.9	9.6
87.5°	9.7	10.4	10.6	7.3	6.5
90°	1.7	5.0	10.2	11.1	11.1
92.5°	20.8	73.5	145.3	70.0	48.6
95°	47.8	170.3	513.4	262.5	181.7
97.5°	76.2	195.0	805.2	672.7	507.3
100°	98.1	204.8	898.0	939.6	779.5
102.5°	119.2	218.6	928.7	1139.5	1008.0
105°	156.1	242.8	933.0	1395.8	1309.9
107.5°	190.9	268.2	893.3	1527.6	1549.8
110°	214.1	287.4	857.1	1568.5	1649.4

TEST NUMBER: P519544

CATALOG NUMBER: SQ4-WB-125U-125D-940-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	238.6	306.7	822.3	1559.4	1692.4
115°	275.5	337.2	776.9	1501.2	1698.0
117.5°	309.1	366.9	741.8	1408.2	1627.4
120°	330.9	386.8	724.1	1341.5	1566.6
122.5°	350.0	405.2	711.1	1273.3	1497.7
125°	376.1	432.0	697.6	1179.1	1387.6
127.5°	401.2	456.2	689.1	1096.0	1282.1
130°	416.2	471.2	685.7	1048.4	1211.9
132.5°	431.2	485.6	682.3	1006.5	1156.6
135°	452.9	505.4	678.0	951.2	1077.1
137.5°	473.5	523.9	675.8	904.3	1007.7
140°	487.8	536.2	673.7	875.4	968.8
142.5°	502.8	547.9	672.4	848.5	927.2
145°	523.6	564.5	669.5	813.3	873.3
147.5°	546.2	581.7	666.6	783.6	830.8
150°	561.2	592.0	665.2	765.0	804.2
152.5°	574.8	601.7	664.5	749.8	781.7
155°	594.4	616.1	663.5	729.7	753.0
157.5°	611.6	628.5	663.7	715.5	731.2
160°	622.6	636.7	664.4	707.3	718.9
162.5°	632.1	643.6	665.0	700.4	708.7
165°	644.7	652.2	666.1	692.6	695.9
167.5°	655.0	659.3	666.9	686.6	687.9
170°	661.8	663.5	666.9	683.1	683.1
172.5°	665.9	666.2	667.6	679.7	679.7
175°	670.3	669.5	666.9	676.3	674.6
177.5°	672.2	670.9	667.4	672.9	671.5
180°	669.5	669.5	669.5	669.5	669.5

(END OF REPORT)