

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519665

Luminaire Tested: **SQ4-025U-0D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519665  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-025U-0D-940-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1265.1 lumens  
Efficiency: N/A  
Efficacy: 154.3 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Indirect

Input Watts (W): 8.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519665  
CATALOG NUMBER: SQ4-025U-0D-940-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P519665

CATALOG NUMBER: SQ4-025U-0D-940-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	882	11567	4065
100°	1020	9574	7534
105°	1069	6571	9306
110°	1126	4455	9001
115°	1166	3224	7338
120°	1185	2555	5618
125°	1195	2160	4307
130°	1173	1892	3364
135°	1153	1698	2710
140°	1155	1557	2251
145°	1156	1447	1897
150°	1164	1369	1653
155°	1180	1308	1477
160°	1187	1261	1360
165°	1195	1227	1291
170°	1204	1211	1242
175°	1205	1197	1213



TEST NUMBER: P519665

CATALOG NUMBER: SQ4-025U-0D-940-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	95.1	7.5
100°-110°	250.1	19.8
110°-120°	259.3	20.5
120°-130°	208.0	16.4
130°-140°	163.2	12.9
140°-150°	125.3	9.9
150°-160°	90.2	7.1
160°-170°	55.2	4.4
170°-180°	18.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	604.6	47.8
90°-150°	1101.1	87.0
90°-180°	1265.0	100.0
0°-180°	1265.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	4	10	5	5	
95°	12	49	164	84	58	15
105°	45	68	276	420	392	48
115°	80	97	222	442	504	79
125°	111	125	201	340	402	99
135°	133	146	195	275	312	103
145°	154	164	193	234	253	96
155°	174	179	193	212	218	80
165°	188	190	193	200	203	53
175°	195	195	194	196	196	19
180°	195	195	195	195	195	



TEST NUMBER: P519665

CATALOG NUMBER: SQ4-025U-0D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.3	3.7	10.0	5.0	5.0
92.5°	5.3	25.3	56.1	24.8	16.0
95°	12.5	49.2	163.9	84.5	57.6
97.5°	21.8	54.1	245.2	195.0	143.6
100°	28.8	58.1	270.3	273.9	212.7
102.5°	34.8	62.2	277.3	341.1	288.8
105°	45.0	68.3	276.5	419.8	391.6
107.5°	55.6	77.1	260.8	460.6	467.5
110°	62.6	82.1	247.7	471.1	500.5
112.5°	69.6	88.2	235.7	464.5	509.5
115°	80.1	97.2	221.5	441.8	504.2
117.5°	90.3	106.0	211.7	410.5	479.7
120°	96.3	111.0	207.7	389.4	456.7
122.5°	102.3	117.0	204.7	368.4	434.7
125°	111.4	124.8	201.4	340.5	401.6
127.5°	118.6	132.3	198.7	318.0	369.6
130°	122.6	137.3	197.7	303.9	351.6
132.5°	126.6	141.3	196.7	291.8	334.6
135°	132.6	146.1	195.2	274.8	311.6
137.5°	138.9	152.1	194.9	262.2	292.3
140°	143.9	156.1	193.9	252.1	280.3
142.5°	147.9	159.1	193.9	245.0	269.3
145°	153.9	163.7	192.7	234.4	252.7
147.5°	159.9	169.4	192.7	225.6	240.7
150°	163.9	172.5	192.7	220.5	232.7
152.5°	167.9	174.5	192.7	216.4	225.7
155°	173.9	178.8	192.7	211.6	217.7
157.5°	178.4	183.1	192.7	207.3	211.7
160°	181.4	185.1	192.7	205.3	207.7
162.5°	184.4	187.1	192.7	203.3	205.7
165°	187.7	190.1	192.7	200.2	202.7
167.5°	190.7	191.9	193.9	199.0	199.9
170°	192.7	193.9	193.9	198.9	198.9
172.5°	193.7	193.9	193.9	197.9	196.9
175°	195.2	195.2	193.9	196.4	196.4
177.5°	195.2	195.2	194.2	196.2	195.2
180°	195.2	195.2	195.2	195.2	195.2

(END OF REPORT)