

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519713

Luminaire Tested: **SQ4-075U-0D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519713
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3882.1 lumens
Efficiency: N/A
Efficacy: 140.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Indirect

Input Watts (W): 27.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519713
CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519713

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2950	35075	9577
100°	3099	29775	24522
105°	3284	20248	28775
110°	3444	13795	27636
115°	3561	9946	22476
120°	3634	7877	17344
125°	3617	6649	13175
130°	3567	5824	10336
135°	3540	5238	8349
140°	3533	4805	6923
145°	3532	4456	5846
150°	3566	4196	5070
155°	3614	4001	4535
160°	3643	3859	4183
165°	3665	3770	3948
170°	3674	3706	3801
175°	3679	3664	3703



TEST NUMBER: P519713

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	281.1	7.2
100°-110°	773.3	19.9
110°-120°	798.1	20.6
120°-130°	639.5	16.5
130°-140°	502.3	12.9
140°-150°	384.9	9.9
150°-160°	276.7	7.1
160°-170°	169.2	4.4
170°-180°	57.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1852.5	47.7
90°-150°	3379.1	87.0
90°-180°	3882.0	100.0
0°-180°	3882.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	5	9	11	11	
95°	42	153	497	212	136	47
105°	138	213	852	1298	1211	146
115°	245	298	683	1361	1544	241
125°	337	384	620	1049	1229	301
135°	407	452	602	848	960	314
145°	470	503	593	723	778	295
155°	532	550	590	650	668	245
165°	576	583	592	616	620	162
175°	596	597	593	601	600	57
180°	596	596	596	596	596	



TEST NUMBER: P519713

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.3	5.0	8.9	11.4	11.4
92.5°	17.5	74.8	129.6	49.8	40.8
95°	41.8	153.4	497.0	212.5	135.7
97.5°	68.2	170.1	758.5	584.4	412.3
100°	87.5	180.5	840.6	848.5	692.3
102.5°	105.7	192.8	861.9	1052.6	909.3
105°	138.2	212.6	852.0	1297.6	1210.8
107.5°	169.1	237.1	803.6	1417.6	1443.4
110°	191.5	253.4	767.1	1447.4	1536.7
112.5°	211.7	271.7	730.6	1428.2	1564.1
115°	244.7	298.0	683.4	1360.8	1544.3
117.5°	276.1	325.2	653.5	1266.3	1473.8
120°	295.4	342.5	640.3	1195.4	1409.9
122.5°	312.7	359.8	631.2	1133.3	1336.9
125°	337.3	384.4	620.0	1048.8	1228.6
127.5°	360.6	405.5	612.6	978.3	1136.0
130°	372.8	418.6	608.6	936.4	1080.2
132.5°	387.0	432.8	605.5	899.6	1029.5
135°	407.0	451.6	602.2	848.2	959.8
137.5°	425.8	467.2	599.5	806.7	898.7
140°	440.0	478.4	598.4	779.1	862.2
142.5°	452.1	487.6	596.4	754.5	825.6
145°	470.4	502.6	593.4	722.7	778.5
147.5°	489.9	517.7	591.9	694.5	739.2
150°	502.1	526.9	590.8	679.1	713.8
152.5°	513.2	536.1	589.8	665.8	694.5
155°	532.5	549.9	589.6	649.6	668.2
157.5°	546.5	560.6	589.6	636.3	649.2
160°	556.6	567.8	589.6	629.1	639.0
162.5°	564.7	573.9	590.6	623.0	630.9
165°	575.6	583.1	592.1	616.3	620.0
167.5°	583.2	588.9	593.4	610.6	611.6
170°	588.3	592.0	593.4	608.6	608.6
172.5°	592.4	594.1	593.4	605.5	604.5
175°	595.9	597.1	593.4	601.0	599.7
177.5°	596.9	596.9	592.9	598.9	596.9
180°	595.9	595.9	595.9	595.9	595.9

(END OF REPORT)