

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519497

Luminaire Tested: **SQ4-WB-125U-075D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519497
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-125U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9718.3 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 87.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519497
CATALOG NUMBER: SQ4-WB-125U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519497

CATALOG NUMBER: SQ4-WB-125U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				
1	95	91	87	84	85	82	79	77	66	64	62	51	50	49	37	36	36	30				
2	87	80	75	70	78	73	68	64	59	55	53	46	44	42	34	32	31	26				
3	80	71	65	59	72	65	59	54	52	48	45	41	38	36	31	29	28	23				
4	73	63	56	51	66	58	52	47	47	43	39	37	34	32	28	26	25	21				
5	68	57	49	44	61	52	45	41	42	38	34	34	31	28	26	24	22	18				
6	62	51	44	38	56	47	40	36	39	34	30	31	27	25	23	21	20	17				
7	58	46	39	34	52	43	36	32	35	30	27	28	25	22	22	19	18	15				
8	54	42	35	30	49	39	33	28	32	27	24	26	23	20	20	18	16	14				
9	50	39	32	27	45	36	29	25	30	25	22	24	21	18	19	16	15	13				
10	47	36	29	24	43	33	27	23	27	23	20	22	19	17	17	15	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13647	13647	13647
5°	13477	13429	13508
10°	12733	12849	13147
15°	11754	12027	12567
20°	10674	11076	11809
25°	9574	10097	11001
30°	8560	9121	10165
35°	7486	8027	9175
40°	6301	6801	7943
45°	5200	5649	6631
50°	4341	4733	5524
55°	3686	4061	4563
60°	3150	3521	3641
65°	2508	2962	2352
70°	2223	2311	1435
75°	2060	1875	879
80°	1895	1725	758
85°	1715	1581	621



TEST NUMBER: P519497

CATALOG NUMBER: SQ4-WB-125U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.5	2.1
10°-20°	529.4	5.4
20°-30°	685.7	7.1
30°-40°	671.5	6.9
40°-50°	513.9	5.3
50°-60°	342.5	3.5
60°-70°	186.9	1.9
70°-80°	77.9	0.8
80°-90°	24.4	0.3
90°-100°	469.8	4.8
100°-110°	1265.4	13.0
110°-120°	1328.0	13.7
120°-130°	1077.7	11.1
130°-140°	845.2	8.7
140°-150°	648.9	6.7
150°-160°	466.6	4.8
160°-170°	285.0	2.9
170°-180°	96.1	1.0
0°-30°	1418.6	14.6
0°-40°	2090.0	21.5
0°-60°	2946.4	30.3
0°-90°	3235.6	33.3
90°-120°	3063.3	31.5
90°-150°	5635.0	58.0
90°-180°	6483.0	66.7
0°-180°	9718.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2219	2219	2219	2219	2219	
5°	2183	2161	2175	2180	2188	203
15°	1846	1839	1889	1940	1974	515
25°	1411	1415	1488	1552	1621	649
35°	997	1002	1069	1141	1222	620
45°	598	609	649	698	762	466
55°	344	358	379	393	426	312
65°	172	187	204	178	162	179
75°	87	87	79	54	37	92
85°	24	24	22	14	9	27
90°	3	8	15	17	17	6
95°	72	256	770	394	272	75
105°	234	364	1400	2094	1965	246
115°	413	506	1165	2252	2547	407
125°	564	648	1046	1769	2081	504
135°	679	758	1017	1427	1616	524
145°	786	847	1004	1220	1310	493
155°	892	924	995	1094	1130	410
165°	967	978	999	1039	1044	273
175°	1006	1004	1000	1014	1012	96
180°	1004	1004	1004	1004	1004	

TEST NUMBER: P519497

CATALOG NUMBER: SQ4-WB-125U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2218.8	2218.8	2218.8	2218.8	2218.8
2.5°	2224.3	2204.5	2209.5	2209.4	2203.3
5°	2182.8	2160.9	2175.0	2180.1	2187.7
7.5°	2101.8	2085.2	2111.0	2130.0	2145.4
10°	2038.7	2024.4	2057.2	2084.9	2104.9
12.5°	1965.5	1953.5	1994.1	2031.3	2057.4
15°	1845.9	1839.3	1888.8	1940.2	1973.5
17.5°	1718.0	1714.8	1771.6	1831.5	1874.2
20°	1630.8	1629.8	1692.1	1754.6	1804.1
22.5°	1542.8	1544.9	1610.3	1675.3	1731.6
25°	1410.7	1414.6	1487.7	1552.5	1621.0
27.5°	1288.7	1290.4	1366.0	1434.4	1507.5
30°	1205.3	1210.1	1284.2	1355.0	1431.2
32.5°	1122.0	1127.5	1200.1	1273.3	1351.0
35°	997.0	1001.7	1069.0	1141.0	1221.9
37.5°	868.1	874.5	934.3	1002.3	1081.9
40°	784.7	794.2	847.0	911.1	989.2
42.5°	704.5	716.3	765.3	826.0	896.5
45°	597.8	609.2	649.4	698.5	762.3
47.5°	505.9	519.0	549.9	592.2	646.7
50°	453.7	466.1	494.6	525.9	577.3
52.5°	407.7	420.1	445.5	469.7	513.5
55°	343.7	358.0	378.7	393.1	425.5
57.5°	291.1	304.8	321.3	327.8	347.4
60°	256.1	271.3	286.2	285.5	296.0
62.5°	224.1	237.1	252.0	241.7	242.2
65°	172.3	186.6	203.5	177.8	161.6
67.5°	139.2	142.3	159.7	124.0	104.8
70°	123.6	123.6	128.5	96.0	79.8
72.5°	108.8	108.8	104.4	78.1	61.1
75°	86.7	86.7	78.9	54.1	37.0
77.5°	66.8	66.0	60.4	40.4	26.9
80°	53.5	53.5	48.7	31.9	21.4
82.5°	41.9	41.9	37.8	24.9	16.0
85°	24.3	24.3	22.4	14.5	8.8
87.5°	9.1	10.1	10.9	8.0	7.2
90°	2.6	7.6	15.4	16.6	16.6
92.5°	31.2	110.3	218.0	104.9	72.9
95°	71.6	255.5	770.1	393.8	272.5
97.5°	114.4	292.5	1207.9	1009.1	760.9
100°	147.1	307.2	1347.0	1409.4	1169.2
102.5°	178.8	327.9	1393.1	1709.2	1512.1
105°	234.1	364.2	1399.5	2093.7	1964.9
107.5°	286.3	402.4	1339.9	2291.4	2324.6
110°	321.1	431.2	1285.6	2352.7	2474.1



TEST NUMBER: P519497

CATALOG NUMBER: SQ4-WB-125U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.9	460.0	1233.4	2339.1	2538.5
115°	413.2	505.8	1165.4	2251.8	2547.0
117.5°	463.6	550.4	1112.7	2112.3	2441.0
120°	496.3	580.2	1086.1	2012.2	2350.0
122.5°	525.0	607.8	1066.6	1909.9	2246.6
125°	564.1	648.0	1046.4	1768.6	2081.3
127.5°	601.8	684.3	1033.6	1644.0	1923.2
130°	624.3	706.8	1028.5	1572.6	1817.8
132.5°	646.8	728.3	1023.4	1509.8	1734.9
135°	679.3	758.1	1017.0	1426.8	1615.7
137.5°	710.2	785.8	1013.7	1356.5	1511.6
140°	731.7	804.3	1010.6	1313.1	1453.2
142.5°	754.2	821.8	1008.6	1272.7	1390.8
145°	785.5	846.7	1004.2	1219.9	1309.9
147.5°	819.2	872.5	999.9	1175.4	1246.2
150°	841.7	888.0	997.8	1147.5	1206.3
152.5°	862.2	902.5	996.8	1124.8	1172.6
155°	891.6	924.2	995.2	1094.5	1129.6
157.5°	917.5	942.7	995.5	1073.3	1096.8
160°	933.8	955.1	996.5	1060.9	1078.4
162.5°	948.2	965.4	997.6	1050.5	1063.0
165°	967.1	978.4	999.1	1038.9	1043.9
167.5°	982.5	989.0	1000.4	1029.8	1031.8
170°	992.7	995.2	1000.4	1024.7	1024.7
172.5°	998.8	999.3	1001.4	1019.6	1019.6
175°	1005.5	1004.2	1000.4	1014.4	1011.9
177.5°	1008.3	1006.3	1001.1	1009.3	1007.3
180°	1004.2	1004.2	1004.2	1004.2	1004.2

(END OF REPORT)