

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562744

Luminaire Tested: **SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562744
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10193.1 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 91
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562744
CATALOG NUMBER: SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562744

CATALOG NUMBER: SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47				42	
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40				35	
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34				29	
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29				25	
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25				22	
6	63	51	42	37	58	47	40	34	40	34	30	34	29	26	28	25	22				19	
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20				17	
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16				14	
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8477	8477	8477
5°	8540	8485	8454
10°	8520	8480	8456
15°	8475	8475	8467
20°	8419	8444	8444
25°	8340	8401	8375
30°	8238	8338	8302
35°	8116	8240	8183
40°	7982	8094	8012
45°	7837	7892	7770
50°	7632	7632	7510
55°	7390	7293	7184
60°	7032	6891	6781
65°	6500	6370	6315
70°	5691	5738	5713
75°	4579	5064	5094
80°	3254	4293	4338
85°	1980	3604	3604



TEST NUMBER: P562744

CATALOG NUMBER: SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	1.7
10°-20°	499.0	4.9
20°-30°	755.7	7.4
30°-40°	906.0	8.9
40°-50°	923.9	9.1
50°-60°	806.4	7.9
60°-70°	577.3	5.7
70°-80°	297.4	2.9
80°-90°	77.2	0.8
90°-100°	374.7	3.7
100°-110°	1031.0	10.1
110°-120°	1064.2	10.4
120°-130°	852.6	8.4
130°-140°	669.7	6.6
140°-150°	513.2	5.0
150°-160°	369.0	3.6
160°-170°	225.6	2.2
170°-180°	76.1	0.7
0°-30°	1428.7	14.0
0°-40°	2334.7	22.9
0°-60°	4065.0	39.9
0°-90°	5017.0	49.2
90°-120°	2470.0	24.2
90°-150°	4505.5	44.2
90°-180°	5176.0	50.8
0°-180°	10193.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1838	1838	1838	1838	1838	
5°	1844	1826	1832	1827	1826	175
15°	1775	1760	1775	1774	1773	500
25°	1638	1627	1650	1645	1645	754
35°	1441	1438	1463	1453	1453	901
45°	1201	1198	1210	1194	1191	925
55°	919	907	907	893	893	819
65°	596	582	584	578	578	589
75°	257	269	284	286	286	278
85°	37	57	68	70	68	51
90°	2	7	12	15	15	5
95°	56	205	663	283	181	59
105°	184	283	1136	1730	1614	194
115°	326	397	911	1814	2059	322
125°	450	512	827	1398	1638	401
135°	543	602	803	1131	1280	419
145°	627	670	791	964	1038	393
155°	710	733	786	866	891	326
165°	768	777	790	822	827	216
175°	794	796	791	801	800	75
180°	794	794	794	794	794	

TEST NUMBER: P562744

CATALOG NUMBER: SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1837.5	1837.5	1837.5	1837.5	1837.5
2.5°	1848.4	1832.4	1837.5	1833.3	1826.6
5°	1844.3	1826.0	1832.4	1827.3	1825.6
7.5°	1831.1	1812.8	1821.2	1817.7	1816.1
10°	1818.8	1800.5	1810.3	1806.9	1805.2
12.5°	1802.5	1785.5	1796.7	1793.3	1792.9
15°	1774.6	1759.6	1774.6	1774.5	1772.9
17.5°	1739.5	1725.9	1741.9	1742.9	1741.9
20°	1715.0	1700.0	1720.1	1718.5	1720.1
22.5°	1685.1	1672.8	1694.3	1689.9	1691.5
25°	1638.5	1626.8	1650.4	1645.3	1645.3
27.5°	1583.3	1575.0	1600.7	1595.2	1595.2
30°	1546.6	1538.3	1565.3	1558.5	1558.5
32.5°	1505.7	1500.1	1525.8	1517.7	1517.7
35°	1441.1	1437.8	1463.2	1453.0	1453.0
37.5°	1374.4	1371.4	1394.5	1382.1	1378.1
40°	1325.4	1323.7	1344.1	1330.5	1330.5
42.5°	1276.4	1274.7	1292.4	1276.1	1276.1
45°	1201.2	1197.9	1209.7	1194.3	1191.0
47.5°	1119.2	1115.9	1123.3	1106.6	1104.9
50°	1063.4	1060.1	1063.4	1048.0	1046.4
52.5°	1006.2	1000.2	1000.8	985.4	985.1
55°	918.8	907.1	906.8	893.2	893.2
57.5°	826.2	810.9	812.3	800.6	799.0
60°	762.2	745.6	746.9	736.7	735.0
62.5°	699.6	680.3	684.3	672.7	672.4
65°	595.5	582.2	583.6	578.5	578.5
67.5°	495.4	483.1	492.0	488.0	487.6
70°	421.9	413.6	425.4	425.3	423.6
72.5°	353.9	353.6	368.2	368.2	369.2
75°	256.9	268.6	284.1	285.8	285.8
77.5°	171.5	192.1	209.3	209.9	209.6
80°	122.5	145.8	161.6	165.0	163.3
82.5°	83.0	107.6	120.8	124.2	122.5
85°	37.4	57.4	68.1	69.7	68.1
87.5°	11.2	24.2	29.6	30.2	27.5
90°	1.7	6.6	11.8	15.2	15.2
92.5°	23.3	99.7	172.8	66.3	54.4
95°	55.8	204.6	662.7	283.4	180.9
97.5°	90.9	226.8	1011.3	779.2	549.8
100°	116.6	240.6	1120.8	1131.3	923.0
102.5°	141.0	257.0	1149.2	1403.5	1212.4
105°	184.3	283.4	1136.0	1730.2	1614.4
107.5°	225.5	316.1	1071.5	1890.1	1924.5
110°	255.3	337.9	1022.8	1929.9	2048.9



TEST NUMBER: P562744

CATALOG NUMBER: SQ4-PC3-075U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.3	362.3	974.1	1904.3	2085.4
115°	326.3	397.3	911.2	1814.4	2059.1
117.5°	368.2	433.7	871.3	1688.4	1965.1
120°	393.9	456.7	853.7	1593.9	1879.9
122.5°	416.9	479.7	841.5	1511.1	1782.5
125°	449.7	512.5	826.7	1398.4	1638.1
127.5°	480.8	540.6	816.9	1304.4	1514.7
130°	497.0	558.2	811.4	1248.6	1440.3
132.5°	515.9	577.1	807.4	1199.5	1372.7
135°	542.7	602.2	803.0	1131.0	1279.7
137.5°	567.7	622.9	799.3	1075.6	1198.2
140°	586.6	637.9	797.9	1038.8	1149.6
142.5°	602.8	650.1	795.2	1006.0	1100.9
145°	627.2	670.2	791.2	963.6	1038.0
147.5°	653.2	690.2	789.1	926.1	985.6
150°	669.4	702.5	787.8	905.5	951.8
152.5°	684.3	714.7	786.4	887.7	926.1
155°	710.0	733.2	786.1	866.1	890.9
157.5°	728.6	747.5	786.1	848.4	865.5
160°	742.1	757.0	786.1	838.8	852.0
162.5°	753.0	765.2	787.4	830.6	841.2
165°	767.5	777.4	789.5	821.7	826.7
167.5°	777.6	785.2	791.2	814.2	815.5
170°	784.4	789.4	791.2	811.4	811.4
172.5°	789.8	792.1	791.2	807.4	806.0
175°	794.5	796.2	791.2	801.3	799.6
177.5°	795.9	795.9	790.5	798.5	795.9
180°	794.5	794.5	794.5	794.5	794.5

(END OF REPORT)