

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562840

Luminaire Tested: **SQ4-PC3-0U-075D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5014.9 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562840
CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562840

CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8477	8477	8477
5°	8540	8485	8454
10°	8520	8480	8456
15°	8475	8475	8467
20°	8419	8444	8444
25°	8340	8401	8375
30°	8238	8338	8302
35°	8116	8240	8183
40°	7982	8094	8012
45°	7837	7892	7770
50°	7632	7632	7510
55°	7390	7293	7184
60°	7032	6891	6781
65°	6500	6370	6315
70°	5691	5738	5713
75°	4579	5064	5094
80°	3254	4293	4338
85°	1980	3604	3604



TEST NUMBER: P562840

CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	3.5
10°-20°	499.0	10.0
20°-30°	755.7	15.1
30°-40°	906.0	18.1
40°-50°	923.9	18.4
50°-60°	806.4	16.1
60°-70°	577.3	11.5
70°-80°	297.4	5.9
80°-90°	75.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1428.7	28.5
0°-40°	2334.7	46.6
0°-60°	4065.0	81.1
0°-90°	5014.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5014.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1838	1838	1838	1838	1838	
5°	1844	1826	1832	1827	1826	175
15°	1775	1760	1775	1774	1773	500
25°	1638	1627	1650	1645	1645	754
35°	1441	1438	1463	1453	1453	901
45°	1201	1198	1210	1194	1191	925
55°	919	907	907	893	893	819
65°	596	582	584	578	578	589
75°	257	269	284	286	286	278
85°	37	57	68	70	68	52
90°	0	0	0	0	0	



TEST NUMBER: P562840

CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1837.5	1837.5	1837.5	1837.5	1837.5
2.5°	1848.4	1832.4	1837.5	1833.3	1826.6
5°	1844.3	1826.0	1832.4	1827.3	1825.6
7.5°	1831.1	1812.8	1821.2	1817.7	1816.1
10°	1818.8	1800.5	1810.3	1806.9	1805.2
12.5°	1802.5	1785.5	1796.7	1793.3	1792.9
15°	1774.6	1759.6	1774.6	1774.5	1772.9
17.5°	1739.5	1725.9	1741.9	1742.9	1741.9
20°	1715.0	1700.0	1720.1	1718.5	1720.1
22.5°	1685.1	1672.8	1694.3	1689.9	1691.5
25°	1638.5	1626.8	1650.4	1645.3	1645.3
27.5°	1583.3	1575.0	1600.7	1595.2	1595.2
30°	1546.6	1538.3	1565.3	1558.5	1558.5
32.5°	1505.7	1500.1	1525.8	1517.7	1517.7
35°	1441.1	1437.8	1463.2	1453.0	1453.0
37.5°	1374.4	1371.4	1394.5	1382.1	1378.1
40°	1325.4	1323.7	1344.1	1330.5	1330.5
42.5°	1276.4	1274.7	1292.4	1276.1	1276.1
45°	1201.2	1197.9	1209.7	1194.3	1191.0
47.5°	1119.2	1115.9	1123.3	1106.6	1104.9
50°	1063.4	1060.1	1063.4	1048.0	1046.4
52.5°	1006.2	1000.2	1000.8	985.4	985.1
55°	918.8	907.1	906.8	893.2	893.2
57.5°	826.2	810.9	812.3	800.6	799.0
60°	762.2	745.6	746.9	736.7	735.0
62.5°	699.6	680.3	684.3	672.7	672.4
65°	595.5	582.2	583.6	578.5	578.5
67.5°	495.4	483.1	492.0	488.0	487.6
70°	421.9	413.6	425.4	425.3	423.6
72.5°	353.9	353.6	368.2	368.2	369.2
75°	256.9	268.6	284.1	285.8	285.8
77.5°	171.5	192.1	209.3	209.9	209.6
80°	122.5	145.8	161.6	165.0	163.3
82.5°	83.0	107.6	120.8	124.2	122.5
85°	37.4	57.4	68.1	69.7	68.1
87.5°	10.9	22.9	27.2	27.2	24.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)