

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562864

Luminaire Tested: **SQ4-PC3-0U-100D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562864
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6663.3 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562864
CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562864

CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11274	11233
10°	11320	11267	11236
15°	11261	11261	11250
20°	11187	11220	11220
25°	11081	11161	11127
30°	10946	11079	11031
35°	10783	10949	10872
40°	10605	10755	10646
45°	10412	10486	10324
50°	10140	10140	9978
55°	9819	9691	9545
60°	9344	9156	9010
65°	8636	8464	8390
70°	7561	7623	7592
75°	6085	6728	6769
80°	4325	5706	5765
85°	2631	4785	4785



TEST NUMBER: P562864

CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.1	3.5
10°-20°	663.1	10.0
20°-30°	1004.2	15.1
30°-40°	1203.9	18.1
40°-50°	1227.5	18.4
50°-60°	1071.5	16.1
60°-70°	767.1	11.5
70°-80°	395.1	5.9
80°-90°	99.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1898.3	28.5
0°-40°	3102.2	46.6
0°-60°	5401.2	81.1
0°-90°	6663.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6663.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2442	2442	2442	2442	2442	
5°	2451	2426	2435	2428	2426	233
15°	2358	2338	2358	2358	2356	665
25°	2177	2162	2193	2186	2186	1002
35°	1915	1910	1944	1931	1931	1198
45°	1596	1592	1607	1587	1582	1229
55°	1221	1205	1205	1187	1187	1088
65°	791	774	775	769	769	783
75°	341	357	378	380	380	369
85°	50	76	90	93	90	70
90°	0	0	0	0	0	



TEST NUMBER: P562864

CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2441.5	2441.5	2441.5	2441.5	2441.5
2.5°	2456.0	2434.8	2441.5	2435.9	2427.0
5°	2450.6	2426.2	2434.7	2427.9	2425.7
7.5°	2432.9	2408.6	2419.8	2415.2	2413.0
10°	2416.6	2392.3	2405.3	2400.8	2398.6
12.5°	2394.9	2372.4	2387.3	2382.7	2382.3
15°	2357.9	2338.0	2357.9	2357.8	2355.6
17.5°	2311.3	2293.2	2314.5	2315.8	2314.5
20°	2278.7	2258.9	2285.5	2283.3	2285.5
22.5°	2239.0	2222.6	2251.2	2245.3	2247.6
25°	2177.0	2161.5	2192.8	2186.1	2186.1
27.5°	2103.8	2092.7	2126.8	2119.6	2119.6
30°	2054.9	2043.9	2079.8	2070.8	2070.8
32.5°	2000.7	1993.2	2027.4	2016.5	2016.5
35°	1914.8	1910.4	1944.2	1930.6	1930.6
37.5°	1826.2	1822.2	1852.8	1836.4	1831.1
40°	1761.1	1758.8	1785.9	1767.8	1767.8
42.5°	1695.9	1693.7	1717.2	1695.5	1695.5
45°	1596.0	1591.6	1607.3	1586.9	1582.5
47.5°	1487.1	1482.6	1492.5	1470.3	1468.1
50°	1412.9	1408.5	1412.9	1392.5	1390.3
52.5°	1337.0	1329.0	1329.7	1309.4	1308.9
55°	1220.8	1205.3	1204.9	1186.8	1186.8
57.5°	1097.8	1077.4	1079.2	1063.8	1061.6
60°	1012.8	990.7	992.4	978.8	976.6
62.5°	929.6	903.9	909.2	893.9	893.4
65°	791.2	773.5	775.4	768.6	768.6
67.5°	658.3	641.9	653.8	648.3	647.9
70°	560.6	549.6	565.2	565.1	562.9
72.5°	470.2	469.8	489.2	489.2	490.6
75°	341.4	356.8	377.5	379.8	379.8
77.5°	227.9	255.3	278.1	279.0	278.5
80°	162.8	193.7	214.8	219.2	217.0
82.5°	110.3	143.0	160.5	165.0	162.8
85°	49.7	76.3	90.4	92.6	90.4
87.5°	14.5	30.4	36.2	36.1	32.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)