

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937975

Luminaire Tested: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937975
REPORT IS A COMBINATION OF REPORTS P933606 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9870.0 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 83.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937975
CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P937975

CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10						0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																								
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	40	40	40	40	40	40	33
1	94	89	85	82	84	80	77	74	64	62	60	49	47	46	35	34	33	33	33	33	33	33	33	27
2	85	77	71	66	76	70	65	60	55	52	49	42	40	38	30	29	27	27	27	27	27	27	27	22
3	77	68	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23	23	23	23	23	23	23	18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	26	23	21	19	19	19	19	19	19	19	15
5	64	53	45	39	57	48	41	35	38	33	29	29	25	23	21	18	16	16	16	16	16	16	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	14	14	14	14	14	14	11
7	54	42	34	29	49	38	31	26	31	25	22	23	20	17	17	14	12	12	12	12	12	12	12	10
8	50	38	30	25	45	34	28	23	28	23	19	21	18	15	15	13	11	11	11	11	11	11	11	8
9	47	34	27	22	42	31	25	20	25	20	17	19	16	13	14	12	10	10	10	10	10	10	10	7
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9	9	9	9	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2563	2563	2563
5°	2503	2961	3444
10°	2269	4315	5711
15°	1928	5637	6896
20°	1569	6531	7028
25°	1308	6832	6885
30°	1102	6874	6872
35°	974	6758	7050
40°	849	6607	7233
45°	768	6497	7262
50°	704	6396	7141
55°	673	6251	6825
60°	689	5974	6325
65°	715	5554	5638
70°	761	4840	4763
75°	839	3942	3717
80°	911	2731	2505
85°	793	1446	1281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7262 cd/sqm



TEST NUMBER: P937975

CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	0.5
10°-20°	237.5	2.4
20°-30°	415.4	4.2
30°-40°	534.8	5.4
40°-50°	597.3	6.1
50°-60°	572.1	5.8
60°-70°	453.4	4.6
70°-80°	266.6	2.7
80°-90°	78.0	0.8
90°-100°	500.9	5.1
100°-110°	1316.9	13.3
110°-120°	1365.4	13.8
120°-130°	1095.3	11.1
130°-140°	859.4	8.7
140°-150°	659.6	6.7
150°-160°	475.0	4.8
160°-170°	290.7	2.9
170°-180°	98.2	1.0
0°-30°	706.5	7.2
0°-40°	1241.3	12.6
0°-60°	2410.7	24.4
0°-90°	3208.6	32.5
90°-120°	3183.2	32.3
90°-150°	5797.5	58.7
90°-180°	6661.0	67.5
0°-180°	9870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	414	414	414	414	414	
5°	404	433	488	551	571	37
15°	302	558	940	1140	1176	84
25°	193	633	1120	1170	1171	89
35°	130	605	1055	1115	1159	81
45°	89	482	932	1068	1116	69
55°	64	306	791	919	944	58
65°	51	162	587	661	670	50
75°	37	100	322	354	356	39
85°	13	31	80	88	89	14
90°	7	19	52	26	26	7
95°	66	259	863	445	303	74
105°	237	359	1456	2210	2062	252
115°	421	512	1166	2326	2655	416
125°	586	657	1061	1792	2114	520
135°	699	769	1028	1447	1641	541
145°	810	862	1014	1234	1331	508
155°	916	941	1014	1114	1146	421
165°	988	1001	1014	1054	1068	279
175°	1028	1028	1021	1034	1034	98
180°	1028	1028	1028	1028	1028	



TEST NUMBER: P937975
 CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3
2.5°	414.3	414.3	416.9	418.2	420.9	422.2	424.9	427.6	435.6	436.9	439.6
5°	403.6	408.9	426.2	432.9	451.5	476.9	487.5	504.8	540.8	551.4	558.1
7.5°	387.6	399.6	442.2	452.9	499.5	566.1	594.1	631.4	688.6	716.6	739.3
10°	362.3	387.6	463.5	488.8	564.8	666.0	717.9	769.9	856.5	895.1	909.8
12.5°	334.3	375.6	486.2	520.8	630.0	777.9	840.5	897.8	996.3	1048.4	1056.4
15°	302.4	358.3	507.5	558.1	699.3	871.1	940.4	1011.1	1103.0	1140.3	1149.6
17.5°	274.4	345.0	527.5	580.8	752.6	955.0	1025.7	1084.3	1158.9	1184.2	1190.9
20°	239.8	323.7	540.8	610.1	808.5	1016.4	1084.3	1129.6	1180.2	1196.2	1198.9
22.5°	214.5	301.0	548.8	620.7	845.8	1053.7	1111.0	1146.9	1181.6	1186.9	1188.2
25°	193.1	275.7	547.5	632.7	877.8	1076.3	1120.3	1146.9	1166.9	1169.6	1169.6
27.5°	173.2	247.8	542.1	635.4	901.8	1081.7	1116.3	1135.0	1144.3	1149.6	1149.6
30°	155.8	221.1	528.8	630.0	912.4	1076.3	1104.3	1113.6	1123.0	1131.0	1135.0
32.5°	142.5	195.8	508.8	619.4	913.8	1063.0	1083.0	1088.3	1101.7	1120.3	1127.0
35°	130.5	170.5	486.2	604.7	905.8	1041.7	1055.0	1060.4	1087.0	1115.0	1124.3
37.5°	118.5	151.8	456.9	579.4	893.8	1016.4	1025.7	1035.1	1076.3	1109.6	1120.3
40°	106.6	135.9	422.2	551.4	875.1	985.7	993.7	1008.3	1063.0	1101.7	1112.3
42.5°	97.2	122.5	384.9	522.1	851.1	951.0	963.0	984.3	1047.0	1088.3	1100.3
45°	89.2	109.2	345.0	482.2	820.5	915.1	932.4	961.7	1028.4	1068.4	1079.0
47.5°	81.3	99.9	303.7	440.9	787.2	879.1	901.8	935.1	1003.0	1041.7	1051.0
50°	74.6	90.6	262.4	396.9	751.2	840.5	867.1	901.8	971.0	1007.0	1019.1
52.5°	69.3	82.6	223.8	353.0	710.0	800.5	831.2	867.1	932.4	967.0	975.0
55°	63.9	75.9	190.5	306.4	667.3	757.9	791.2	825.8	889.8	919.1	924.4
57.5°	61.3	70.6	162.5	262.4	622.0	710.0	747.3	779.2	839.2	861.8	867.1
60°	57.3	66.6	141.2	225.1	572.8	664.7	696.6	728.6	779.2	797.9	801.9
62.5°	53.3	63.9	125.2	189.1	522.1	611.4	643.4	672.7	715.3	728.6	733.9
65°	50.6	61.3	113.2	162.5	470.2	555.4	587.4	612.7	647.4	660.7	663.3
67.5°	48.0	58.6	103.9	139.9	418.2	499.5	523.5	547.5	574.1	587.4	588.7
70°	44.0	55.9	95.9	123.9	365.0	435.6	455.5	480.9	502.2	508.8	512.8
72.5°	41.3	51.9	90.6	111.9	310.4	374.3	392.9	407.6	426.2	432.9	432.9
75°	37.3	46.6	85.2	99.9	254.4	306.4	322.3	337.0	351.6	354.3	350.3
77.5°	33.3	41.3	73.3	83.9	198.5	242.4	255.7	263.7	275.7	278.4	279.7
80°	28.0	36.0	57.3	65.3	143.9	178.5	187.8	194.5	205.1	205.1	207.8
82.5°	21.3	28.0	41.3	46.6	97.2	122.5	130.5	134.5	141.2	141.2	141.2
85°	13.3	17.3	26.6	30.6	58.6	74.6	79.9	81.3	86.6	87.9	87.9
87.5°	6.7	9.3	17.3	18.6	30.6	38.6	38.6	41.3	41.3	40.0	38.6
90°	6.9	12.4	17.9	19.3	30.3	45.0	52.4	46.5	34.9	26.2	26.2
92.5°	27.6	74.5	121.4	133.1	187.1	259.1	295.2	258.7	185.8	131.1	125.8
95°	66.2	152.0	237.8	259.3	460.4	728.7	862.8	769.9	584.1	444.8	429.0
97.5°	114.5	190.1	265.9	284.8	620.2	1067.5	1291.1	1232.4	1115.0	1026.9	996.9
100°	151.8	220.4	289.0	306.2	678.3	1174.6	1422.8	1427.0	1435.6	1442.0	1406.2
102.5°	183.5	247.5	311.6	327.6	705.1	1208.3	1460.0	1534.7	1684.4	1796.5	1765.9
105°	237.3	291.5	345.7	359.3	724.8	1212.2	1455.9	1623.5	1958.8	2210.3	2193.8
107.5°	292.4	342.9	393.6	406.2	728.5	1158.2	1373.1	1607.0	2074.7	2425.5	2429.5
110°	329.6	375.3	420.9	432.4	722.9	1110.4	1304.1	1565.5	2088.5	2480.7	2497.9



TEST NUMBER: P937975

CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	366.2	409.7	453.2	464.2	723.2	1068.6	1241.3	1508.9	2044.1	2445.5	2471.8
115°	421.4	461.5	501.7	511.8	729.9	1020.8	1166.2	1424.0	1939.6	2326.2	2362.8
117.5°	475.9	512.4	548.8	557.9	743.4	990.7	1114.4	1347.1	1812.4	2161.4	2201.9
120°	507.6	541.9	576.2	584.8	754.4	980.6	1093.7	1306.3	1731.4	2050.3	2089.7
122.5°	538.7	573.3	607.9	616.5	770.3	975.4	1077.9	1269.4	1652.2	1939.3	1978.1
125°	586.2	617.8	649.3	657.2	791.7	971.0	1060.7	1223.3	1548.5	1792.4	1828.2
127.5°	624.8	656.7	688.6	696.5	813.1	968.5	1046.2	1185.8	1465.1	1674.5	1704.7
130°	645.5	679.9	714.1	722.7	828.7	970.0	1040.6	1165.0	1413.5	1600.0	1627.9
132.5°	666.9	701.3	735.5	744.1	841.4	971.0	1035.9	1147.1	1369.7	1536.5	1561.5
135°	698.6	729.8	761.1	768.9	855.1	970.1	1027.6	1120.7	1307.1	1446.9	1468.4
137.5°	731.0	762.0	793.0	800.7	875.8	976.1	1026.2	1104.9	1262.5	1380.7	1398.2
140°	757.9	786.4	814.9	822.0	888.4	977.1	1021.4	1089.4	1225.5	1327.6	1344.1
142.5°	778.6	805.0	831.3	837.9	899.1	980.6	1021.4	1081.1	1200.7	1290.4	1304.6
145°	810.3	833.3	856.3	862.1	912.9	980.6	1014.5	1063.4	1161.1	1234.5	1245.2
147.5°	842.1	864.5	886.8	892.4	933.1	987.4	1014.5	1052.9	1129.9	1187.6	1196.5
150°	862.8	883.0	903.2	908.2	943.7	990.8	1014.5	1047.0	1112.0	1160.7	1167.9
152.5°	884.1	899.5	914.8	918.6	950.6	993.1	1014.5	1042.2	1097.7	1139.3	1144.7
155°	915.9	927.2	938.5	941.4	965.7	998.2	1014.5	1036.6	1080.7	1113.8	1117.5
157.5°	939.3	950.3	961.3	964.1	980.9	1003.3	1014.5	1031.6	1066.0	1091.7	1094.2
160°	955.1	963.7	972.4	974.5	987.8	1005.6	1014.5	1029.2	1058.6	1080.7	1082.1
162.5°	971.0	977.4	983.9	985.5	995.2	1008.1	1014.5	1026.9	1051.7	1070.3	1071.7
165°	988.3	994.1	1000.0	1001.4	1005.7	1011.5	1014.5	1023.3	1041.2	1054.5	1055.9
167.5°	1004.2	1006.9	1009.7	1010.4	1014.0	1018.9	1021.4	1027.2	1038.9	1047.6	1048.2
170°	1014.5	1017.2	1020.0	1020.7	1020.9	1021.2	1021.4	1027.2	1038.9	1047.6	1047.6
172.5°	1020.0	1020.6	1021.2	1021.4	1021.4	1021.4	1021.4	1026.0	1035.1	1042.1	1041.5
175°	1027.6	1027.6	1027.6	1027.6	1025.6	1022.8	1021.4	1024.3	1030.2	1034.5	1034.5
177.5°	1027.6	1027.6	1027.6	1027.6	1026.0	1023.8	1022.7	1025.0	1029.6	1033.1	1032.5
180°	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6	1027.6



TEST NUMBER: P937975

CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	414.3	414.3
2.5°	442.2	439.6
5°	568.8	571.4
7.5°	765.9	764.6
10°	952.4	964.4
12.5°	1088.3	1091.0
15°	1170.9	1176.2
17.5°	1202.9	1204.2
20°	1204.2	1201.6
22.5°	1189.6	1186.9
25°	1172.2	1170.9
27.5°	1156.3	1157.6
30°	1149.6	1153.6
32.5°	1149.6	1156.3
35°	1152.3	1158.9
37.5°	1150.9	1158.9
40°	1145.6	1154.9
42.5°	1131.0	1137.6
45°	1108.3	1116.3
47.5°	1079.0	1084.3
50°	1041.7	1047.0
52.5°	995.0	996.3
55°	939.1	944.4
57.5°	879.1	880.5
60°	812.5	816.5
62.5°	741.9	741.9
65°	667.3	670.0
67.5°	590.1	596.7
70°	511.5	512.8
72.5°	434.2	434.2
75°	354.3	355.6
77.5°	278.4	278.4
80°	206.5	207.8
82.5°	142.5	145.2
85°	89.2	89.2
87.5°	41.3	37.3
90°	26.2	26.2
92.5°	105.0	84.1
95°	365.9	302.7
97.5°	876.7	756.6
100°	1263.2	1120.0
102.5°	1643.2	1520.7
105°	2127.9	2062.0
107.5°	2445.4	2461.4
110°	2566.5	2635.1



TEST NUMBER: P937975

CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2577.2	2682.7
115°	2509.0	2655.1
117.5°	2364.0	2526.2
120°	2247.3	2404.8
122.5°	2133.5	2288.9
125°	1971.4	2114.5
127.5°	1825.5	1946.2
130°	1739.5	1851.0
132.5°	1661.4	1761.3
135°	1554.5	1640.7
137.5°	1468.8	1539.3
140°	1410.0	1475.9
142.5°	1361.2	1418.0
145°	1288.1	1331.0
147.5°	1232.1	1267.6
150°	1196.8	1225.5
152.5°	1166.5	1188.2
155°	1131.8	1146.2
157.5°	1104.3	1114.4
160°	1088.0	1093.7
162.5°	1077.2	1082.7
165°	1061.8	1067.6
167.5°	1050.6	1053.1
170°	1047.6	1047.6
172.5°	1039.4	1037.3
175°	1034.5	1034.5
177.5°	1030.1	1027.6
180°	1027.6	1027.6



TEST NUMBER: P937975
 CATALOG NUMBER: SQ4-FB-125U-075D-940-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.41	3.15	3.50	4.24	5.74	15.57	16.32	16.66	17.41	18.91
	3H	3.10	3.77	4.20	4.87	6.39	17.40	18.07	18.49	19.17	20.68
	4H	3.40	4.03	4.50	5.13	6.65	18.03	18.67	19.14	19.77	21.29
	6H	3.64	4.23	4.76	5.33	6.86	18.45	19.04	19.57	20.14	21.68
	8H	3.71	4.26	4.83	5.38	6.91	18.57	19.13	19.69	20.25	21.77
	12H	3.72	4.25	4.84	5.36	6.91	18.63	19.16	19.76	20.27	21.82
4H	2H	9.60	10.24	10.71	11.34	12.86	15.83	16.47	16.95	17.57	19.09
	3H	11.16	11.69	12.28	12.82	14.35	17.86	18.39	18.98	19.52	21.06
	4H	11.25	11.74	12.37	12.85	14.41	18.62	19.11	19.75	20.23	21.78
	6H	11.25	11.67	12.38	12.81	14.36	19.15	19.57	20.28	20.71	22.25
	8H	11.23	11.62	12.36	12.75	14.31	19.31	19.70	20.44	20.83	22.39
	12H	11.18	11.53	12.33	12.67	14.24	19.39	19.75	20.54	20.89	22.46
8H	4H	12.68	13.07	13.81	14.20	15.76	18.67	19.06	19.80	20.19	21.76
	6H	12.92	13.24	14.07	14.41	15.97	19.29	19.62	20.44	20.79	22.35
	8H	12.93	13.22	14.09	14.37	15.95	19.51	19.79	20.67	20.94	22.52
	12H	12.89	13.14	14.06	14.29	15.91	19.64	19.89	20.81	21.04	22.66
12H	4H	12.81	13.17	13.96	14.31	15.88	18.62	18.97	19.77	20.12	21.69
	6H	13.17	13.46	14.33	14.61	16.19	19.27	19.56	20.43	20.71	22.29
	8H	13.23	13.48	14.40	14.63	16.25	19.49	19.74	20.66	20.89	22.51