

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562599

Luminaire Tested: **SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562599
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7643.7 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 77.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562599
CATALOG NUMBER: SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562599

CATALOG NUMBER: SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	83									83																			
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71									71																			
2	96	88	82	76	92	85	79	74	79	74	70	73	69	66	68	65	62	59									59																			
3	88	78	70	64	84	75	68	62	69	64	59	65	60	56	60	56	53	50									50																			
4	80	69	60	54	77	66	59	53	62	55	50	58	52	48	54	49	45	43									43																			
5	74	61	53	46	71	59	51	45	55	49	43	52	46	41	48	43	40	37									37																			
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	32									32																			
7	63	50	42	36	60	48	41	35	45	39	34	43	37	32	40	35	31	29									29																			
8	59	46	37	32	56	44	36	31	42	35	30	39	33	29	37	32	28	26									26																			
9	55	42	34	28	53	41	33	28	38	32	27	36	30	26	34	29	25	23									23																			
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	21									21																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14373	14373	14373
5°	14481	14388	14334
10°	14446	14379	14338
15°	14370	14370	14357
20°	14276	14318	14318
25°	14141	14244	14200
30°	13969	14138	14076
35°	13761	13972	13875
40°	13533	13724	13586
45°	13288	13382	13175
50°	12940	12940	12733
55°	12529	12366	12181
60°	11924	11685	11498
65°	11022	10801	10707
70°	9650	9727	9690
75°	7764	8586	8639
80°	5519	7279	7357
85°	3359	6105	6105



TEST NUMBER: P562599

CATALOG NUMBER: SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.2	2.9
10°-20°	634.6	8.3
20°-30°	961.1	12.6
30°-40°	1152.2	15.1
40°-50°	1174.9	15.4
50°-60°	1025.6	13.4
60°-70°	734.2	9.6
70°-80°	378.2	4.9
80°-90°	96.7	1.3
90°-100°	95.1	1.2
100°-110°	250.1	3.3
110°-120°	259.3	3.4
120°-130°	208.0	2.7
130°-140°	163.2	2.1
140°-150°	125.3	1.6
150°-160°	90.2	1.2
160°-170°	55.2	0.7
170°-180°	18.6	0.2
0°-30°	1816.9	23.8
0°-40°	2969.1	38.8
0°-60°	5169.5	67.6
0°-90°	6378.5	83.4
90°-120°	604.6	7.9
90°-150°	1101.1	14.4
90°-180°	1265.0	16.5
0°-180°	7643.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2345	2322	2330	2324	2322	223
15°	2257	2238	2257	2257	2255	636
25°	2084	2069	2099	2092	2092	959
35°	1833	1828	1861	1848	1848	1146
45°	1528	1523	1538	1519	1515	1176
55°	1168	1154	1153	1136	1136	1042
65°	757	740	742	736	736	749
75°	327	342	361	364	364	353
85°	48	73	86	89	86	65
90°	1	4	10	5	5	3
95°	12	49	164	84	58	14
105°	45	68	276	420	392	48
115°	80	97	222	442	504	79
125°	111	125	201	340	402	99
135°	133	146	195	275	312	103
145°	154	164	193	234	253	96
155°	174	179	193	212	218	80
165°	188	190	193	200	203	53
175°	195	195	194	196	196	19
180°	195	195	195	195	195	

TEST NUMBER: P562599

CATALOG NUMBER: SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.8	2336.8	2336.8	2336.8	2336.8
2.5°	2350.6	2330.3	2336.8	2331.4	2322.9
5°	2345.4	2322.2	2330.3	2323.7	2321.6
7.5°	2328.6	2305.3	2316.0	2311.6	2309.5
10°	2313.0	2289.7	2302.2	2297.8	2295.7
12.5°	2292.2	2270.6	2284.8	2280.5	2280.1
15°	2256.7	2237.7	2256.7	2256.7	2254.6
17.5°	2212.1	2194.8	2215.2	2216.4	2215.2
20°	2181.0	2161.9	2187.5	2185.4	2187.5
22.5°	2142.9	2127.3	2154.6	2149.0	2151.1
25°	2083.6	2068.8	2098.8	2092.3	2092.3
27.5°	2013.5	2002.9	2035.6	2028.7	2028.7
30°	1966.8	1956.2	1990.6	1981.9	1981.9
32.5°	1914.9	1907.7	1940.4	1930.0	1930.0
35°	1832.6	1828.4	1860.8	1847.8	1847.8
37.5°	1747.8	1744.0	1773.4	1757.7	1752.6
40°	1685.5	1683.4	1709.3	1692.0	1692.0
42.5°	1623.2	1621.1	1643.5	1622.8	1622.8
45°	1527.6	1523.3	1538.4	1518.8	1514.6
47.5°	1423.3	1419.0	1428.5	1407.2	1405.1
50°	1352.3	1348.1	1352.3	1332.8	1330.7
52.5°	1279.6	1272.0	1272.7	1253.2	1252.8
55°	1168.4	1153.6	1153.2	1135.9	1135.9
57.5°	1050.7	1031.2	1032.9	1018.2	1016.1
60°	969.3	948.2	949.9	936.8	934.7
62.5°	889.7	865.2	870.2	855.5	855.1
65°	757.3	740.4	742.1	735.7	735.7
67.5°	630.1	614.4	625.7	620.5	620.1
70°	536.6	526.0	540.9	540.9	538.8
72.5°	450.0	449.6	468.2	468.2	469.5
75°	326.7	341.5	361.3	363.5	363.5
77.5°	218.1	244.3	266.1	267.0	266.6
80°	155.8	185.4	205.5	209.8	207.7
82.5°	105.6	136.9	153.6	157.9	155.8
85°	47.6	73.0	86.5	88.7	86.5
87.5°	14.1	29.8	36.6	35.5	32.2
90°	1.3	3.7	10.0	5.0	5.0
92.5°	5.3	25.3	56.1	24.8	16.0
95°	12.5	49.2	163.9	84.5	57.6
97.5°	21.8	54.1	245.2	195.0	143.6
100°	28.8	58.1	270.3	273.9	212.7
102.5°	34.8	62.2	277.3	341.1	288.8
105°	45.0	68.3	276.5	419.8	391.6
107.5°	55.6	77.1	260.8	460.6	467.5
110°	62.6	82.1	247.7	471.1	500.5



TEST NUMBER: P562599

CATALOG NUMBER: SQ4-PC3-025U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.6	88.2	235.7	464.5	509.5
115°	80.1	97.2	221.5	441.8	504.2
117.5°	90.3	106.0	211.7	410.5	479.7
120°	96.3	111.0	207.7	389.4	456.7
122.5°	102.3	117.0	204.7	368.4	434.7
125°	111.4	124.8	201.4	340.5	401.6
127.5°	118.6	132.3	198.7	318.0	369.6
130°	122.6	137.3	197.7	303.9	351.6
132.5°	126.6	141.3	196.7	291.8	334.6
135°	132.6	146.1	195.2	274.8	311.6
137.5°	138.9	152.1	194.9	262.2	292.3
140°	143.9	156.1	193.9	252.1	280.3
142.5°	147.9	159.1	193.9	245.0	269.3
145°	153.9	163.7	192.7	234.4	252.7
147.5°	159.9	169.4	192.7	225.6	240.7
150°	163.9	172.5	192.7	220.5	232.7
152.5°	167.9	174.5	192.7	216.4	225.7
155°	173.9	178.8	192.7	211.6	217.7
157.5°	178.4	183.1	192.7	207.3	211.7
160°	181.4	185.1	192.7	205.3	207.7
162.5°	184.4	187.1	192.7	203.3	205.7
165°	187.7	190.1	192.7	200.2	202.7
167.5°	190.7	191.9	193.9	199.0	199.9
170°	192.7	193.9	193.9	198.9	198.9
172.5°	193.7	193.9	193.9	197.9	196.9
175°	195.2	195.2	193.9	196.4	196.4
177.5°	195.2	195.2	194.2	196.2	195.2
180°	195.2	195.2	195.2	195.2	195.2

(END OF REPORT)