

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563176

Luminaire Tested: **SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563176
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18921.9 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 167.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563176
CATALOG NUMBER: SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563176

CATALOG NUMBER: SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	89	85	88	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	80	74	69	65	62	58	55	51	48	46	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14373	14373	14373
5°	14481	14388	14334
10°	14446	14378	14338
15°	14370	14370	14357
20°	14276	14318	14318
25°	14141	14244	14200
30°	13969	14138	14076
35°	13761	13972	13874
40°	13533	13725	13586
45°	13287	13382	13174
50°	12940	12940	12733
55°	12530	12367	12181
60°	11924	11685	11499
65°	11021	10801	10707
70°	9651	9727	9688
75°	7764	8587	8639
80°	5518	7282	7359
85°	3361	6108	6108



TEST NUMBER: P563176

CATALOG NUMBER: SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.9	1.6
10°-20°	846.2	4.5
20°-30°	1281.4	6.8
30°-40°	1536.3	8.1
40°-50°	1566.5	8.3
50°-60°	1367.4	7.2
60°-70°	979.0	5.2
70°-80°	504.2	2.7
80°-90°	130.9	0.7
90°-100°	750.7	4.0
100°-110°	2029.9	10.7
110°-120°	2134.1	11.3
120°-130°	1733.5	9.2
130°-140°	1359.8	7.2
140°-150°	1043.6	5.5
150°-160°	750.6	4.0
160°-170°	458.5	2.4
170°-180°	154.6	0.8
0°-30°	2422.5	12.8
0°-40°	3958.8	20.9
0°-60°	6892.7	36.4
0°-90°	8506.7	45.0
90°-120°	4914.7	26.0
90°-150°	9051.5	47.8
90°-180°	10415.0	55.0
0°-180°	18921.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3127	3096	3107	3098	3096	297
15°	3009	2984	3009	3009	3006	848
25°	2778	2758	2798	2790	2790	1279
35°	2444	2438	2481	2464	2464	1528
45°	2037	2031	2051	2025	2019	1568
55°	1558	1538	1538	1515	1515	1389
65°	1010	987	990	981	981	999
75°	436	455	482	485	485	471
85°	64	97	115	118	115	86
90°	4	10	23	24	23	10
95°	116	409	1248	646	384	122
105°	377	583	2252	3322	3186	397
115°	664	812	1868	3615	4081	656
125°	909	1042	1683	2840	3337	811
135°	1090	1220	1638	2294	2596	843
145°	1268	1363	1615	1963	2113	793
155°	1431	1487	1602	1761	1819	660
165°	1558	1573	1608	1671	1680	439
175°	1617	1616	1610	1631	1628	154
180°	1615	1615	1615	1615	1615	

TEST NUMBER: P563176

CATALOG NUMBER: SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3115.7	3115.7	3115.7	3115.7	3115.7
2.5°	3134.2	3107.1	3115.7	3108.5	3097.2
5°	3127.2	3096.2	3107.0	3098.3	3095.5
7.5°	3104.7	3073.7	3088.0	3082.2	3079.4
10°	3084.0	3052.9	3069.5	3063.7	3060.9
12.5°	3056.3	3027.5	3046.5	3040.7	3040.1
15°	3009.0	2983.6	3009.0	3008.9	3006.1
17.5°	2949.5	2926.4	2953.6	2955.3	2953.6
20°	2908.0	2882.6	2916.6	2913.8	2916.6
22.5°	2857.2	2836.3	2872.8	2865.4	2868.2
25°	2778.2	2758.4	2798.4	2789.7	2789.7
27.5°	2684.7	2670.6	2714.1	2704.9	2704.9
30°	2622.4	2608.3	2654.1	2642.6	2642.6
32.5°	2553.1	2543.6	2587.2	2573.3	2573.3
35°	2443.5	2437.9	2481.0	2463.7	2463.7
37.5°	2330.4	2325.4	2364.5	2343.5	2336.8
40°	2247.3	2244.5	2279.1	2256.0	2256.0
42.5°	2164.3	2161.4	2191.4	2163.7	2163.7
45°	2036.7	2031.1	2051.2	2025.1	2019.4
47.5°	1897.7	1892.1	1904.6	1876.3	1873.5
50°	1803.1	1797.4	1803.1	1777.0	1774.2
52.5°	1706.1	1696.0	1696.9	1670.9	1670.4
55°	1557.9	1538.1	1537.7	1514.6	1514.6
57.5°	1400.9	1375.0	1377.3	1357.6	1354.8
60°	1292.4	1264.2	1266.5	1249.1	1246.3
62.5°	1186.3	1153.6	1160.3	1140.7	1140.1
65°	1009.7	987.2	989.5	980.9	980.9
67.5°	840.1	819.2	834.3	827.4	826.8
70°	715.5	701.4	721.2	721.2	718.3
72.5°	600.1	599.5	624.3	624.3	626.0
75°	435.6	455.4	481.8	484.7	484.7
77.5°	290.8	325.8	354.8	356.0	355.4
80°	207.7	247.2	274.1	279.8	277.0
82.5°	140.8	182.5	204.8	210.5	207.7
85°	63.5	97.3	115.4	118.2	115.4
87.5°	19.2	40.8	50.7	50.9	46.1
90°	3.5	10.3	22.6	24.3	22.6
92.5°	49.4	180.0	355.1	154.1	111.6
95°	116.5	408.9	1248.5	646.1	384.3
97.5°	187.1	469.0	1946.1	1610.6	1182.8
100°	240.0	493.3	2163.2	2255.9	1824.1
102.5°	288.7	527.0	2239.7	2745.3	2422.3
105°	377.3	583.1	2251.8	3321.6	3185.6
107.5°	459.4	647.1	2153.4	3681.2	3726.4
110°	523.4	693.4	2065.8	3777.7	3969.9



TEST NUMBER: P563176

CATALOG NUMBER: SQ4-PC3-150U-125D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	580.4	739.6	1985.1	3758.4	4081.1
115°	664.3	812.2	1867.6	3615.3	4081.1
117.5°	746.3	885.1	1790.0	3396.5	3924.6
120°	796.4	932.4	1744.1	3239.6	3778.6
122.5°	843.7	977.0	1716.3	3071.4	3614.4
125°	909.4	1042.1	1683.2	2840.4	3336.9
127.5°	969.9	1100.2	1663.8	2652.0	3088.6
130°	1003.3	1137.6	1655.4	2535.6	2930.0
132.5°	1038.1	1171.1	1647.1	2430.5	2793.7
135°	1090.3	1219.5	1638.0	2293.5	2596.1
137.5°	1142.8	1264.9	1630.4	2182.3	2428.9
140°	1179.0	1292.9	1627.6	2110.8	2330.1
142.5°	1213.7	1320.8	1622.0	2046.2	2238.3
145°	1267.6	1362.9	1615.4	1963.1	2112.7
147.5°	1316.7	1401.0	1607.8	1887.9	2002.8
150°	1352.8	1427.7	1605.0	1847.0	1938.8
152.5°	1386.2	1451.5	1603.6	1809.1	1884.6
155°	1431.1	1487.2	1601.5	1761.1	1818.9
157.5°	1477.7	1516.8	1601.9	1727.6	1765.7
160°	1504.1	1536.4	1603.2	1706.5	1733.7
162.5°	1525.0	1551.9	1604.6	1689.6	1710.0
165°	1558.0	1573.3	1608.5	1671.3	1679.8
167.5°	1580.6	1591.2	1608.8	1655.5	1659.6
170°	1594.5	1599.6	1610.2	1648.5	1648.5
172.5°	1605.7	1606.7	1610.2	1640.1	1638.7
175°	1617.2	1615.5	1610.2	1631.0	1627.6
177.5°	1621.0	1616.9	1609.9	1623.7	1619.6
180°	1615.4	1615.4	1615.4	1615.4	1615.4

(END OF REPORT)