

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562647

Luminaire Tested: **SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562647  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6345.7 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 58.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562647  
CATALOG NUMBER: SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562647

CATALOG NUMBER: SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16
10	48	36	28	23	45	34	27	22	30	24	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8476	8476	8476
5°	8540	8485	8454
10°	8520	8480	8456
15°	8475	8475	8467
20°	8420	8444	8444
25°	8339	8401	8374
30°	8238	8338	8302
35°	8115	8240	8183
40°	7981	8094	8012
45°	7837	7892	7770
50°	7631	7631	7510
55°	7390	7293	7184
60°	7033	6891	6782
65°	6500	6370	6315
70°	5692	5737	5713
75°	4579	5064	5095
80°	3255	4293	4339
85°	1983	3599	3599



TEST NUMBER: P562647

CATALOG NUMBER: SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.4	2.1
10°-20°	374.3	5.9
20°-30°	566.8	8.9
30°-40°	679.5	10.7
40°-50°	692.9	10.9
50°-60°	604.8	9.5
60°-70°	433.0	6.8
70°-80°	223.0	3.5
80°-90°	57.9	0.9
90°-100°	189.9	3.0
100°-110°	515.9	8.1
110°-120°	530.4	8.4
120°-130°	424.1	6.7
130°-140°	333.2	5.3
140°-150°	255.5	4.0
150°-160°	183.7	2.9
160°-170°	112.4	1.8
170°-180°	37.9	0.6
0°-30°	1071.5	16.9
0°-40°	1751.0	27.6
0°-60°	3048.8	48.0
0°-90°	3762.7	59.3
90°-120°	1236.2	19.5
90°-150°	2249.0	35.4
90°-180°	2583.0	40.7
0°-180°	6345.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1378	1378	1378	1378	1378	
5°	1383	1370	1374	1370	1369	131
15°	1331	1320	1331	1331	1330	375
25°	1229	1220	1238	1234	1234	566
35°	1081	1078	1097	1090	1090	676
45°	901	898	907	896	893	693
55°	689	680	680	670	670	614
65°	447	437	438	434	434	442
75°	193	201	213	214	214	208
85°	28	43	51	52	51	38
90°	1	5	9	11	11	3
95°	28	104	331	144	97	30
105°	92	143	567	864	813	97
115°	163	198	454	903	1029	161
125°	224	255	411	692	817	200
135°	270	300	399	564	636	209
145°	312	334	394	479	515	196
155°	352	365	392	430	443	162
165°	382	387	393	410	411	108
175°	396	397	394	399	398	38
180°	396	396	396	396	396	

TEST NUMBER: P562647

CATALOG NUMBER: SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1378.1	1378.1	1378.1	1378.1	1378.1
2.5°	1386.3	1374.3	1378.1	1375.0	1370.0
5°	1383.2	1369.5	1374.3	1370.5	1369.2
7.5°	1373.3	1359.6	1365.9	1363.3	1362.1
10°	1364.1	1350.4	1357.7	1355.1	1353.9
12.5°	1351.9	1339.1	1347.5	1345.0	1344.7
15°	1330.9	1319.7	1330.9	1330.9	1329.6
17.5°	1304.6	1294.4	1306.4	1307.2	1306.4
20°	1286.3	1275.0	1290.1	1288.8	1290.1
22.5°	1263.8	1254.6	1270.7	1267.4	1268.7
25°	1228.8	1220.1	1237.8	1233.9	1233.9
27.5°	1187.5	1181.3	1200.5	1196.4	1196.4
30°	1159.9	1153.7	1174.0	1168.9	1168.9
32.5°	1129.3	1125.1	1144.4	1138.2	1138.2
35°	1080.8	1078.3	1097.4	1089.8	1089.8
37.5°	1030.8	1028.6	1045.9	1036.6	1033.6
40°	994.0	992.8	1008.1	997.9	997.9
42.5°	957.3	956.0	969.3	957.0	957.0
45°	900.9	898.4	907.3	895.7	893.2
47.5°	839.4	836.9	842.5	829.9	828.7
50°	797.5	795.0	797.5	786.0	784.8
52.5°	754.7	750.2	750.6	739.1	738.8
55°	689.1	680.3	680.1	669.9	669.9
57.5°	619.7	608.2	609.2	600.5	599.2
60°	571.7	559.2	560.2	552.5	551.3
62.5°	524.7	510.2	513.2	504.5	504.3
65°	446.6	436.6	437.7	433.9	433.9
67.5°	371.6	362.4	369.0	366.0	365.7
70°	316.5	310.2	319.0	319.0	317.7
72.5°	265.4	265.2	276.1	276.2	276.9
75°	192.7	201.4	213.1	214.4	214.4
77.5°	128.6	144.1	157.0	157.5	157.2
80°	91.9	109.3	121.2	123.7	122.5
82.5°	62.3	80.7	90.6	93.1	91.9
85°	28.1	43.0	51.0	52.3	51.0
87.5°	8.4	18.2	22.2	22.7	20.7
90°	1.3	5.0	8.9	11.4	11.4
92.5°	11.4	52.0	90.3	38.8	32.8
95°	28.0	103.9	330.7	143.9	96.7
97.5°	46.3	114.7	507.0	394.5	277.0
100°	58.5	121.9	561.0	568.6	459.2
102.5°	70.7	129.2	575.2	703.3	606.8
105°	91.6	142.6	567.3	863.8	812.8
107.5°	113.2	158.2	534.5	946.7	960.9
110°	128.5	169.5	510.1	963.0	1024.0

TEST NUMBER: P562647

CATALOG NUMBER: SQ4-PC3-050U-075D-940-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	141.7	180.8	485.7	949.5	1041.3
115°	162.8	197.6	454.1	903.4	1029.1
117.5°	182.7	216.0	434.0	838.2	979.7
120°	195.9	228.2	424.9	794.4	934.9
122.5°	207.1	239.4	418.7	750.5	886.1
125°	223.9	255.0	410.9	692.3	816.6
127.5°	238.9	269.7	406.5	648.1	754.8
130°	248.0	277.9	404.5	620.4	716.1
132.5°	257.2	287.1	402.5	596.7	681.5
135°	269.7	299.5	399.4	563.9	636.0
137.5°	283.2	310.3	397.9	534.9	595.6
140°	291.3	317.4	396.9	516.4	571.1
142.5°	299.4	323.6	395.9	502.0	547.7
145°	311.6	334.0	394.3	479.1	515.2
147.5°	325.4	344.5	393.1	461.1	489.5
150°	334.5	350.7	393.1	450.8	473.2
152.5°	341.7	355.8	392.0	441.6	460.0
155°	352.3	364.8	391.8	430.2	442.7
157.5°	362.8	372.5	391.8	422.5	432.0
160°	368.9	377.6	391.8	417.4	424.9
162.5°	375.0	381.7	392.8	413.3	418.7
165°	381.6	386.6	393.1	409.6	410.9
167.5°	388.5	391.0	394.3	405.3	406.3
170°	390.5	393.0	394.3	403.2	403.2
172.5°	392.5	394.0	394.3	401.2	401.2
175°	395.6	396.8	394.3	399.4	398.1
177.5°	396.6	396.6	393.6	397.6	395.6
180°	395.6	395.6	395.6	395.6	395.6

(END OF REPORT)