

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563368

Luminaire Tested: **SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563368
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11868.9 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 114.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563368
CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563368

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	43
4	79	68	59	53	74	64	57	51	58	52	48	53	48	44	47	44	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15181	15181	15181
5°	15292	15199	15146
10°	15267	15159	15091
15°	15166	15083	15000
20°	15065	14980	14867
25°	14886	14783	14637
30°	14611	14534	14350
35°	14229	14131	13952
40°	13773	13687	13530
45°	13398	13303	13172
50°	12917	12833	12709
55°	12248	12086	11992
60°	11150	10831	10777
65°	9823	9414	9382
70°	8481	8130	8130
75°	7301	7197	7094
80°	6437	6514	6360
85°	5039	5494	5494



TEST NUMBER: P563368

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.2	2.6
10°-20°	888.5	7.5
20°-30°	1330.9	11.2
30°-40°	1561.1	13.2
40°-50°	1566.0	13.2
50°-60°	1335.9	11.3
60°-70°	871.2	7.3
70°-80°	437.1	3.7
80°-90°	123.0	1.0
90°-100°	253.2	2.1
100°-110°	687.8	5.8
110°-120°	707.2	6.0
120°-130°	565.4	4.8
130°-140°	444.3	3.7
140°-150°	340.7	2.9
150°-160°	245.0	2.1
160°-170°	149.8	1.3
170°-180°	50.5	0.4
0°-30°	2530.6	21.3
0°-40°	4091.7	34.5
0°-60°	6993.6	58.9
0°-90°	8424.9	71.0
90°-120°	1648.3	13.9
90°-150°	2998.6	25.3
90°-180°	3444.0	29.0
0°-180°	11868.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3291	3291	3291	3291	3291	
5°	3302	3271	3282	3271	3271	314
15°	3176	3144	3158	3147	3141	896
25°	2925	2891	2904	2878	2876	1345
35°	2527	2501	2509	2480	2478	1578
45°	2054	2040	2039	2019	2019	1581
55°	1523	1517	1503	1494	1491	1353
65°	900	883	862	857	860	898
75°	410	410	404	401	398	444
85°	95	104	104	104	104	112
90°	2	7	12	15	15	6
95°	37	138	441	192	129	40
105°	122	190	756	1152	1084	130
115°	217	264	606	1205	1372	214
125°	298	340	548	923	1089	266
135°	360	399	532	752	848	278
145°	416	445	526	639	687	261
155°	470	486	522	574	590	217
165°	509	515	524	546	548	144
175°	528	529	526	532	531	50
180°	528	528	528	528	528	

TEST NUMBER: P563368

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3290.9	3290.9	3290.9	3290.9	3290.9
2.5°	3311.7	3284.6	3290.9	3286.0	3272.4
5°	3302.4	3271.4	3282.2	3270.7	3270.7
7.5°	3279.9	3246.1	3256.9	3245.3	3244.8
10°	3259.2	3225.3	3236.1	3224.5	3221.7
12.5°	3229.2	3195.3	3208.4	3194.6	3194.0
15°	3175.5	3144.5	3158.2	3146.6	3140.9
17.5°	3115.0	3081.1	3097.7	3081.5	3079.2
20°	3068.8	3035.0	3051.5	3028.4	3028.4
22.5°	3013.4	2979.6	2998.4	2968.4	2968.4
25°	2924.6	2890.8	2904.4	2878.4	2875.6
27.5°	2819.0	2785.8	2800.0	2770.6	2770.0
30°	2742.9	2711.9	2728.5	2696.7	2693.9
32.5°	2659.8	2631.1	2643.1	2611.3	2608.5
35°	2526.6	2501.2	2509.3	2480.4	2477.5
37.5°	2386.4	2360.5	2369.7	2344.8	2343.7
40°	2287.2	2270.3	2272.8	2252.5	2246.8
42.5°	2194.9	2175.7	2178.2	2158.0	2156.8
45°	2053.6	2039.5	2039.1	2019.0	2019.0
47.5°	1903.6	1892.9	1889.7	1873.0	1872.4
50°	1799.8	1791.3	1788.2	1773.7	1770.9
52.5°	1691.3	1687.4	1677.5	1665.3	1664.8
55°	1522.9	1517.2	1502.7	1494.0	1491.1
57.5°	1340.0	1328.7	1312.3	1299.7	1301.9
60°	1208.5	1197.2	1173.9	1168.1	1168.1
62.5°	1081.6	1068.0	1044.7	1036.7	1041.2
65°	899.9	883.0	862.4	856.7	859.5
67.5°	734.9	719.7	697.4	697.4	695.1
70°	628.8	620.3	602.8	602.8	602.8
72.5°	534.2	530.2	517.4	517.4	515.1
75°	409.6	409.6	403.8	400.8	398.0
77.5°	306.9	308.0	305.2	302.2	297.1
80°	242.3	247.9	245.2	242.2	239.4
82.5°	182.3	187.9	187.5	182.3	181.7
85°	95.2	103.6	103.8	103.8	103.8
87.5°	25.7	35.7	39.3	40.0	42.3
90°	1.7	6.7	11.9	15.3	15.3
92.5°	15.3	69.3	120.4	51.7	43.8
95°	37.3	138.5	441.0	191.9	128.9
97.5°	61.7	152.9	676.0	525.9	369.4
100°	78.0	162.6	747.9	758.2	612.3
102.5°	94.3	172.2	766.9	937.7	809.0
105°	122.1	190.1	756.4	1151.7	1083.8
107.5°	150.9	211.0	712.7	1262.3	1281.2
110°	171.3	226.0	680.1	1284.0	1365.3



TEST NUMBER: P563368

CATALOG NUMBER: SQ4-PP3-050U-125D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.9	241.0	647.5	1266.0	1388.4
115°	217.1	263.5	605.5	1204.6	1372.1
117.5°	243.5	288.0	578.7	1117.6	1306.3
120°	261.2	304.3	566.5	1059.2	1246.6
122.5°	276.1	319.2	558.3	1000.7	1181.4
125°	298.5	340.0	547.8	923.0	1088.8
127.5°	318.5	359.6	542.0	864.1	1006.4
130°	330.7	370.5	539.3	827.2	954.9
132.5°	342.9	382.7	536.6	795.6	908.7
135°	359.6	399.4	532.5	751.8	848.0
137.5°	377.5	413.7	530.5	713.1	794.1
140°	388.4	423.2	529.2	688.5	761.5
142.5°	399.2	431.4	527.8	669.3	730.3
145°	415.5	445.4	525.8	638.8	686.9
147.5°	433.8	459.4	524.1	614.8	652.6
150°	446.1	467.6	524.1	601.1	630.9
152.5°	455.6	474.5	522.7	588.7	613.3
155°	469.8	486.4	522.4	573.6	590.2
157.5°	483.7	496.6	522.4	563.4	576.0
160°	491.8	503.5	522.4	556.5	566.5
162.5°	500.0	508.9	523.7	551.0	558.3
165°	508.8	515.4	524.1	546.2	547.8
167.5°	518.0	521.3	525.8	540.4	541.7
170°	520.7	524.0	525.8	537.6	537.6
172.5°	523.4	525.4	525.8	534.9	534.9
175°	527.5	529.1	525.8	532.5	530.9
177.5°	528.8	528.8	524.7	530.1	527.5
180°	527.5	527.5	527.5	527.5	527.5

(END OF REPORT)