

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562767

Luminaire Tested: **SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562767
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8881.1 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562767
CATALOG NUMBER: SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P562767

CATALOG NUMBER: SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	54	52	48				
2	90	83	77	72	84	77	72	67	67	63	59	57	54	52	48	46	44	40				
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34				
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29				
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25				
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	28	25	22				
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11274	11233
10°	11320	11267	11235
15°	11261	11261	11250
20°	11187	11220	11220
25°	11081	11161	11127
30°	10946	11079	11031
35°	10783	10948	10873
40°	10605	10754	10646
45°	10412	10486	10323
50°	10140	10140	9978
55°	9819	9691	9545
60°	9344	9156	9011
65°	8636	8465	8390
70°	7562	7623	7593
75°	6084	6728	6768
80°	4325	5706	5767
85°	2632	4785	4785



TEST NUMBER: P562767

CATALOG NUMBER: SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.3	2.0
10°-20°	497.3	5.6
20°-30°	753.1	8.5
30°-40°	902.9	10.2
40°-50°	920.6	10.4
50°-60°	803.7	9.0
60°-70°	575.4	6.5
70°-80°	296.3	3.3
80°-90°	76.5	0.9
90°-100°	281.1	3.2
100°-110°	773.3	8.7
110°-120°	798.1	9.0
120°-130°	639.5	7.2
130°-140°	502.3	5.7
140°-150°	384.9	4.3
150°-160°	276.7	3.1
160°-170°	169.2	1.9
170°-180°	57.0	0.6
0°-30°	1423.7	16.0
0°-40°	2326.6	26.2
0°-60°	4050.9	45.6
0°-90°	4999.0	56.3
90°-120°	1852.5	20.9
90°-150°	3379.1	38.0
90°-180°	3882.0	43.7
0°-180°	8881.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1831	1831	1831	1831	1831	
5°	1838	1820	1826	1821	1819	174
15°	1768	1754	1768	1768	1767	499
25°	1633	1621	1645	1640	1640	751
35°	1436	1433	1458	1448	1448	898
45°	1197	1194	1206	1190	1187	921
55°	916	904	904	890	890	816
65°	593	580	582	576	576	587
75°	256	268	283	285	285	277
85°	37	57	68	70	68	51
90°	1	5	9	11	11	4
95°	42	153	497	212	136	44
105°	138	213	852	1298	1211	146
115°	245	298	683	1361	1544	241
125°	337	384	620	1049	1229	301
135°	407	452	602	848	960	314
145°	470	503	593	723	778	295
155°	532	550	590	650	668	245
165°	576	583	592	616	620	162
175°	596	597	593	601	600	57
180°	596	596	596	596	596	

TEST NUMBER: P562767

CATALOG NUMBER: SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1831.1	1831.1	1831.1	1831.1	1831.1
2.5°	1842.0	1826.1	1831.1	1826.9	1820.3
5°	1837.9	1819.7	1826.0	1820.9	1819.3
7.5°	1824.7	1806.5	1814.9	1811.4	1809.8
10°	1812.5	1794.2	1804.0	1800.6	1798.9
12.5°	1796.2	1779.3	1790.4	1787.0	1786.7
15°	1768.4	1753.5	1768.4	1768.4	1766.7
17.5°	1733.5	1719.9	1735.8	1736.8	1735.8
20°	1709.1	1694.1	1714.1	1712.5	1714.1
22.5°	1679.2	1667.0	1688.4	1684.0	1685.7
25°	1632.8	1621.2	1644.6	1639.5	1639.5
27.5°	1577.8	1569.5	1595.1	1589.7	1589.7
30°	1541.2	1532.9	1559.9	1553.1	1553.1
32.5°	1500.5	1494.9	1520.5	1512.4	1512.4
35°	1436.1	1432.8	1458.1	1448.0	1448.0
37.5°	1369.6	1366.6	1389.6	1377.3	1373.4
40°	1320.8	1319.1	1339.4	1325.9	1325.9
42.5°	1272.0	1270.3	1287.9	1271.6	1271.6
45°	1197.0	1193.7	1205.5	1190.2	1186.8
47.5°	1115.3	1112.0	1119.4	1102.7	1101.1
50°	1059.7	1056.4	1059.7	1044.4	1042.7
52.5°	1002.7	996.7	997.3	982.0	981.7
55°	915.6	904.0	903.7	890.1	890.1
57.5°	823.3	808.1	809.4	797.9	796.2
60°	759.6	743.0	744.3	734.1	732.5
62.5°	697.2	678.0	681.9	670.4	670.1
65°	593.4	580.2	581.6	576.5	576.5
67.5°	493.7	481.5	490.3	486.3	485.9
70°	420.5	412.2	423.9	423.8	422.2
72.5°	352.7	352.3	366.9	366.9	367.9
75°	256.0	267.6	283.1	284.8	284.8
77.5°	170.9	191.5	208.5	209.2	208.9
80°	122.1	145.3	161.1	164.4	162.8
82.5°	82.7	107.3	120.4	123.7	122.1
85°	37.3	57.2	67.8	69.5	67.8
87.5°	11.1	23.8	28.9	29.3	26.7
90°	1.3	5.0	8.9	11.4	11.4
92.5°	17.5	74.8	129.6	49.8	40.8
95°	41.8	153.4	497.0	212.5	135.7
97.5°	68.2	170.1	758.5	584.4	412.3
100°	87.5	180.5	840.6	848.5	692.3
102.5°	105.7	192.8	861.9	1052.6	909.3
105°	138.2	212.6	852.0	1297.6	1210.8
107.5°	169.1	237.1	803.6	1417.6	1443.4
110°	191.5	253.4	767.1	1447.4	1536.7



TEST NUMBER: P562767

CATALOG NUMBER: SQ4-PC3-075U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.7	271.7	730.6	1428.2	1564.1
115°	244.7	298.0	683.4	1360.8	1544.3
117.5°	276.1	325.2	653.5	1266.3	1473.8
120°	295.4	342.5	640.3	1195.4	1409.9
122.5°	312.7	359.8	631.2	1133.3	1336.9
125°	337.3	384.4	620.0	1048.8	1228.6
127.5°	360.6	405.5	612.6	978.3	1136.0
130°	372.8	418.6	608.6	936.4	1080.2
132.5°	387.0	432.8	605.5	899.6	1029.5
135°	407.0	451.6	602.2	848.2	959.8
137.5°	425.8	467.2	599.5	806.7	898.7
140°	440.0	478.4	598.4	779.1	862.2
142.5°	452.1	487.6	596.4	754.5	825.6
145°	470.4	502.6	593.4	722.7	778.5
147.5°	489.9	517.7	591.9	694.5	739.2
150°	502.1	526.9	590.8	679.1	713.8
152.5°	513.2	536.1	589.8	665.8	694.5
155°	532.5	549.9	589.6	649.6	668.2
157.5°	546.5	560.6	589.6	636.3	649.2
160°	556.6	567.8	589.6	629.1	639.0
162.5°	564.7	573.9	590.6	623.0	630.9
165°	575.6	583.1	592.1	616.3	620.0
167.5°	583.2	588.9	593.4	610.6	611.6
170°	588.3	592.0	593.4	608.6	608.6
172.5°	592.4	594.1	593.4	605.5	604.5
175°	595.9	597.1	593.4	601.0	599.7
177.5°	596.9	596.9	592.9	598.9	596.9
180°	595.9	595.9	595.9	595.9	595.9

(END OF REPORT)