

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563632

Luminaire Tested: **SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563632  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13546.6 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 121.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563632  
CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563632

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	38	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11896	11896	11896
5°	11983	11910	11869
10°	11963	11879	11826
15°	11884	11819	11755
20°	11806	11739	11650
25°	11665	11584	11469
30°	11449	11389	11245
35°	11150	11073	10933
40°	10793	10725	10602
45°	10498	10425	10321
50°	10121	10057	9959
55°	9597	9470	9398
60°	8737	8487	8446
65°	7698	7377	7352
70°	6645	6372	6372
75°	5720	5639	5559
80°	5045	5103	4984
85°	3949	4308	4308



TEST NUMBER: P563632

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	243.8	1.8
10°-20°	696.3	5.1
20°-30°	1042.9	7.7
30°-40°	1223.3	9.0
40°-50°	1227.1	9.1
50°-60°	1046.8	7.7
60°-70°	682.7	5.0
70°-80°	342.5	2.5
80°-90°	97.0	0.7
90°-100°	500.5	3.7
100°-110°	1381.7	10.2
110°-120°	1425.0	10.5
120°-130°	1145.1	8.5
130°-140°	899.9	6.6
140°-150°	690.2	5.1
150°-160°	496.0	3.7
160°-170°	303.4	2.2
170°-180°	102.3	0.8
0°-30°	1983.0	14.6
0°-40°	3206.4	23.7
0°-60°	5480.3	40.5
0°-90°	6602.6	48.7
90°-120°	3307.2	24.4
90°-150°	6042.4	44.6
90°-180°	6944.0	51.3
0°-180°	13546.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2579	2579	2579	2579	2579	
5°	2588	2564	2572	2563	2563	246
15°	2488	2464	2475	2466	2461	702
25°	2292	2265	2276	2256	2253	1054
35°	1980	1960	1966	1944	1941	1237
45°	1609	1598	1598	1582	1582	1239
55°	1193	1189	1178	1171	1168	1061
65°	705	692	676	671	674	704
75°	321	321	316	314	312	348
85°	75	81	81	81	81	88
90°	3	7	14	15	17	8
95°	74	271	908	373	243	79
105°	246	380	1520	2321	2185	262
115°	441	533	1224	2424	2756	434
125°	605	689	1110	1878	2204	539
135°	728	807	1079	1521	1715	564
145°	845	903	1065	1295	1394	529
155°	952	984	1057	1162	1199	439
165°	1031	1044	1062	1103	1112	291
175°	1069	1070	1064	1079	1076	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P563632

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2578.8	2578.8	2578.8	2578.8	2578.8
2.5°	2595.1	2573.9	2578.8	2574.9	2564.3
5°	2587.8	2563.5	2572.0	2563.0	2563.0
7.5°	2570.2	2543.7	2552.1	2543.1	2542.6
10°	2553.9	2527.4	2535.9	2526.8	2524.6
12.5°	2530.4	2503.9	2514.2	2503.3	2502.9
15°	2488.4	2464.1	2474.8	2465.7	2461.3
17.5°	2440.9	2414.4	2427.4	2414.7	2412.9
20°	2404.8	2378.3	2391.2	2373.1	2373.1
22.5°	2361.4	2334.9	2349.6	2326.1	2326.1
25°	2291.8	2265.2	2275.9	2255.6	2253.3
27.5°	2209.0	2183.0	2194.1	2171.1	2170.6
30°	2149.4	2125.1	2138.1	2113.2	2111.0
32.5°	2084.3	2061.7	2071.2	2046.3	2044.1
35°	1979.9	1960.0	1966.3	1943.7	1941.4
37.5°	1870.0	1849.7	1856.9	1837.5	1836.6
40°	1792.3	1779.0	1781.0	1765.1	1760.6
42.5°	1720.0	1704.9	1706.8	1691.0	1690.1
45°	1609.2	1598.2	1597.9	1582.1	1582.1
47.5°	1491.7	1483.3	1480.8	1467.7	1467.3
50°	1410.3	1403.7	1401.3	1389.9	1387.7
52.5°	1325.3	1322.2	1314.5	1305.0	1304.5
55°	1193.3	1188.9	1177.5	1170.7	1168.5
57.5°	1050.1	1041.2	1028.4	1018.5	1020.2
60°	947.0	938.2	919.9	915.4	915.4
62.5°	847.5	836.9	818.6	812.4	815.9
65°	705.2	691.9	675.8	671.3	673.5
67.5°	575.9	563.9	546.5	546.5	544.7
70°	492.7	486.1	472.4	472.4	472.4
72.5°	418.6	415.5	405.5	405.4	403.7
75°	320.9	320.9	316.4	314.1	311.9
77.5°	240.5	241.4	239.1	236.8	232.8
80°	189.9	194.3	192.1	189.8	187.6
82.5°	142.8	147.3	146.9	142.8	142.4
85°	74.6	81.2	81.4	81.4	81.4
87.5°	20.6	28.3	31.7	32.1	34.2
90°	3.4	6.8	13.7	15.4	17.1
92.5°	30.8	127.8	228.5	83.4	65.0
95°	73.5	270.8	908.0	373.2	242.8
97.5°	121.7	303.3	1345.1	1035.6	750.0
100°	157.3	322.8	1506.5	1517.1	1232.9
102.5°	191.5	345.0	1537.9	1874.5	1605.0
105°	246.2	380.0	1520.2	2320.8	2185.3
107.5°	304.4	423.4	1435.3	2536.0	2585.5
110°	345.4	452.4	1369.7	2582.3	2742.8



TEST NUMBER: P563632

CATALOG NUMBER: SQ4-PP3-100U-100D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	382.3	485.3	1308.1	2545.7	2782.5
115°	441.2	533.1	1224.3	2423.8	2756.5
117.5°	492.5	584.1	1169.3	2252.1	2630.6
120°	526.7	617.0	1147.4	2135.9	2517.1
122.5°	559.5	645.8	1129.6	2027.3	2388.5
125°	605.3	688.9	1109.8	1878.1	2204.2
127.5°	644.3	727.9	1098.1	1751.9	2033.2
130°	670.3	753.9	1092.7	1674.7	1930.6
132.5°	694.9	774.5	1087.2	1609.9	1841.6
135°	728.4	807.0	1079.0	1521.2	1715.1
137.5°	766.1	837.6	1074.9	1446.6	1612.2
140°	786.6	856.8	1072.2	1396.9	1542.4
142.5°	809.8	874.7	1069.4	1352.8	1480.8
145°	844.7	903.2	1065.3	1295.0	1393.6
147.5°	878.2	929.4	1061.5	1246.3	1322.8
150°	902.9	944.7	1060.2	1217.2	1279.1
152.5°	922.0	961.1	1058.8	1192.3	1243.5
155°	952.5	984.2	1056.8	1161.9	1198.7
157.5°	980.5	1004.9	1057.1	1139.8	1164.8
160°	996.9	1018.6	1058.5	1127.3	1145.7
162.5°	1010.6	1029.7	1059.8	1116.3	1130.6
165°	1031.1	1044.5	1061.9	1103.1	1111.5
167.5°	1046.8	1054.9	1063.6	1095.1	1097.8
170°	1055.1	1061.7	1063.6	1091.0	1091.0
172.5°	1061.9	1065.9	1063.6	1085.5	1084.1
175°	1068.7	1070.4	1063.6	1078.9	1075.6
177.5°	1071.5	1070.1	1063.3	1072.8	1070.1
180°	1068.7	1068.7	1068.7	1068.7	1068.7

(END OF REPORT)