

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563079

Luminaire Tested: **SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563079
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12862.6 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563079
CATALOG NUMBER: SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563079

CATALOG NUMBER: SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	50	48	43	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14373	14373	14373
5°	14481	14388	14334
10°	14446	14379	14338
15°	14370	14370	14357
20°	14276	14318	14318
25°	14141	14244	14200
30°	13969	14138	14076
35°	13761	13972	13875
40°	13533	13724	13586
45°	13288	13382	13175
50°	12940	12940	12733
55°	12529	12366	12181
60°	11924	11685	11498
65°	11022	10801	10707
70°	9650	9727	9690
75°	7764	8586	8639
80°	5519	7279	7357
85°	3359	6105	6105



TEST NUMBER: P563079

CATALOG NUMBER: SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.2	1.7
10°-20°	634.6	4.9
20°-30°	961.1	7.5
30°-40°	1152.2	9.0
40°-50°	1174.9	9.1
50°-60°	1025.6	8.0
60°-70°	734.2	5.7
70°-80°	378.2	2.9
80°-90°	98.0	0.8
90°-100°	469.8	3.7
100°-110°	1265.4	9.8
110°-120°	1328.0	10.3
120°-130°	1077.7	8.4
130°-140°	845.2	6.6
140°-150°	648.9	5.0
150°-160°	466.6	3.6
160°-170°	285.0	2.2
170°-180°	96.1	0.7
0°-30°	1816.9	14.1
0°-40°	2969.1	23.1
0°-60°	5169.5	40.2
0°-90°	6379.9	49.6
90°-120°	3063.3	23.8
90°-150°	5635.0	43.8
90°-180°	6483.0	50.4
0°-180°	12862.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2345	2322	2330	2324	2322	223
15°	2257	2238	2257	2257	2255	636
25°	2084	2069	2099	2092	2092	959
35°	1833	1828	1861	1848	1848	1146
45°	1528	1523	1538	1519	1515	1176
55°	1168	1154	1153	1136	1136	1042
65°	757	740	742	736	736	749
75°	327	342	361	364	364	353
85°	48	73	86	89	86	65
90°	3	8	15	17	17	7
95°	72	256	770	394	272	75
105°	234	364	1400	2094	1965	246
115°	413	506	1165	2252	2547	407
125°	564	648	1046	1769	2081	504
135°	679	758	1017	1427	1616	524
145°	786	847	1004	1220	1310	493
155°	892	924	995	1094	1130	410
165°	967	978	999	1039	1044	273
175°	1006	1004	1000	1014	1012	96
180°	1004	1004	1004	1004	1004	

TEST NUMBER: P563079

CATALOG NUMBER: SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2336.8	2336.8	2336.8	2336.8	2336.8
2.5°	2350.6	2330.3	2336.8	2331.4	2322.9
5°	2345.4	2322.2	2330.3	2323.7	2321.6
7.5°	2328.6	2305.3	2316.0	2311.6	2309.5
10°	2313.0	2289.7	2302.2	2297.8	2295.7
12.5°	2292.2	2270.6	2284.8	2280.5	2280.1
15°	2256.7	2237.7	2256.7	2256.7	2254.6
17.5°	2212.1	2194.8	2215.2	2216.4	2215.2
20°	2181.0	2161.9	2187.5	2185.4	2187.5
22.5°	2142.9	2127.3	2154.6	2149.0	2151.1
25°	2083.6	2068.8	2098.8	2092.3	2092.3
27.5°	2013.5	2002.9	2035.6	2028.7	2028.7
30°	1966.8	1956.2	1990.6	1981.9	1981.9
32.5°	1914.9	1907.7	1940.4	1930.0	1930.0
35°	1832.6	1828.4	1860.8	1847.8	1847.8
37.5°	1747.8	1744.0	1773.4	1757.7	1752.6
40°	1685.5	1683.4	1709.3	1692.0	1692.0
42.5°	1623.2	1621.1	1643.5	1622.8	1622.8
45°	1527.6	1523.3	1538.4	1518.8	1514.6
47.5°	1423.3	1419.0	1428.5	1407.2	1405.1
50°	1352.3	1348.1	1352.3	1332.8	1330.7
52.5°	1279.6	1272.0	1272.7	1253.2	1252.8
55°	1168.4	1153.6	1153.2	1135.9	1135.9
57.5°	1050.7	1031.2	1032.9	1018.2	1016.1
60°	969.3	948.2	949.9	936.8	934.7
62.5°	889.7	865.2	870.2	855.5	855.1
65°	757.3	740.4	742.1	735.7	735.7
67.5°	630.1	614.4	625.7	620.5	620.1
70°	536.6	526.0	540.9	540.9	538.8
72.5°	450.0	449.6	468.2	468.2	469.5
75°	326.7	341.5	361.3	363.5	363.5
77.5°	218.1	244.3	266.1	267.0	266.6
80°	155.8	185.4	205.5	209.8	207.7
82.5°	105.6	136.9	153.6	157.9	155.8
85°	47.6	73.0	86.5	88.7	86.5
87.5°	14.4	30.6	37.7	37.9	34.5
90°	2.6	7.6	15.4	16.6	16.6
92.5°	31.2	110.3	218.0	104.9	72.9
95°	71.6	255.5	770.1	393.8	272.5
97.5°	114.4	292.5	1207.9	1009.1	760.9
100°	147.1	307.2	1347.0	1409.4	1169.2
102.5°	178.8	327.9	1393.1	1709.2	1512.1
105°	234.1	364.2	1399.5	2093.7	1964.9
107.5°	286.3	402.4	1339.9	2291.4	2324.6
110°	321.1	431.2	1285.6	2352.7	2474.1



TEST NUMBER: P563079

CATALOG NUMBER: SQ4-PC3-125U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.9	460.0	1233.4	2339.1	2538.5
115°	413.2	505.8	1165.4	2251.8	2547.0
117.5°	463.6	550.4	1112.7	2112.3	2441.0
120°	496.3	580.2	1086.1	2012.2	2350.0
122.5°	525.0	607.8	1066.6	1909.9	2246.6
125°	564.1	648.0	1046.4	1768.6	2081.3
127.5°	601.8	684.3	1033.6	1644.0	1923.2
130°	624.3	706.8	1028.5	1572.6	1817.8
132.5°	646.8	728.3	1023.4	1509.8	1734.9
135°	679.3	758.1	1017.0	1426.8	1615.7
137.5°	710.2	785.8	1013.7	1356.5	1511.6
140°	731.7	804.3	1010.6	1313.1	1453.2
142.5°	754.2	821.8	1008.6	1272.7	1390.8
145°	785.5	846.7	1004.2	1219.9	1309.9
147.5°	819.2	872.5	999.9	1175.4	1246.2
150°	841.7	888.0	997.8	1147.5	1206.3
152.5°	862.2	902.5	996.8	1124.8	1172.6
155°	891.6	924.2	995.2	1094.5	1129.6
157.5°	917.5	942.7	995.5	1073.3	1096.8
160°	933.8	955.1	996.5	1060.9	1078.4
162.5°	948.2	965.4	997.6	1050.5	1063.0
165°	967.1	978.4	999.1	1038.9	1043.9
167.5°	982.5	989.0	1000.4	1029.8	1031.8
170°	992.7	995.2	1000.4	1024.7	1024.7
172.5°	998.8	999.3	1001.4	1019.6	1019.6
175°	1005.5	1004.2	1000.4	1014.4	1011.9
177.5°	1008.3	1006.3	1001.1	1009.3	1007.3
180°	1004.2	1004.2	1004.2	1004.2	1004.2

(END OF REPORT)