

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563223

Luminaire Tested: **SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563223
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4991.8 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563223
CATALOG NUMBER: SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563223

CATALOG NUMBER: SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75				
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	77	73	75	71	67	69	65	62	62	59	57	54				
3	86	77	69	63	82	73	67	61	67	61	57	61	56	53	55	52	49	46				
4	79	68	60	54	75	65	58	52	60	53	49	54	49	45	49	45	42	39				
5	73	61	53	46	69	58	51	45	53	47	42	49	44	39	45	40	37	34				
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30				
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	32	29	27				
8	58	45	37	32	55	43	36	31	40	34	29	37	32	28	34	29	26	24				
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	31	27	23	22				
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8932
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8572	8463
35°	8392	8334	8229
40°	8123	8072	7980
45°	7901	7846	7768
50°	7618	7569	7495
55°	7223	7128	7073
60°	6575	6387	6356
65°	5793	5551	5533
70°	5001	4794	4794
75°	4306	4244	4185
80°	3797	3840	3751
85°	2971	3239	3239



TEST NUMBER: P563223

CATALOG NUMBER: SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	2.8
10°-20°	393.0	7.9
20°-30°	588.7	11.8
30°-40°	690.5	13.8
40°-50°	692.7	13.9
50°-60°	590.9	11.8
60°-70°	385.4	7.7
70°-80°	193.3	3.9
80°-90°	54.5	1.1
90°-100°	95.1	1.9
100°-110°	250.1	5.0
110°-120°	259.3	5.2
120°-130°	208.0	4.2
130°-140°	163.2	3.3
140°-150°	125.3	2.5
150°-160°	90.2	1.8
160°-170°	55.2	1.1
170°-180°	18.6	0.4
0°-30°	1119.3	22.4
0°-40°	1809.9	36.3
0°-60°	3093.4	62.0
0°-90°	3726.7	74.7
90°-120°	604.6	12.1
90°-150°	1101.1	22.1
90°-180°	1265.0	25.3
0°-180°	4991.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1456	1456	1456	1456	1456	
5°	1461	1447	1452	1447	1447	139
15°	1405	1391	1397	1392	1389	396
25°	1294	1279	1285	1273	1272	595
35°	1118	1106	1110	1097	1096	698
45°	908	902	902	893	893	699
55°	674	671	665	661	660	599
65°	398	391	381	379	380	397
75°	181	181	179	177	176	197
85°	42	46	46	46	46	49
90°	1	4	10	5	5	3
95°	12	49	164	84	58	14
105°	45	68	276	420	392	48
115°	80	97	222	442	504	79
125°	111	125	201	340	402	99
135°	133	146	195	275	312	103
145°	154	164	193	234	253	96
155°	174	179	193	212	218	80
165°	188	190	193	200	203	53
175°	195	195	194	196	196	19
180°	195	195	195	195	195	

TEST NUMBER: P563223

CATALOG NUMBER: SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1455.6	1455.6	1455.6	1455.6	1455.6
2.5°	1464.8	1452.8	1455.6	1453.5	1447.5
5°	1460.7	1447.0	1451.8	1446.7	1446.7
7.5°	1450.8	1435.8	1440.6	1435.5	1435.2
10°	1441.6	1426.6	1431.4	1426.3	1425.0
12.5°	1428.3	1413.4	1419.1	1413.0	1412.8
15°	1404.6	1390.9	1396.9	1391.8	1389.3
17.5°	1377.8	1362.8	1370.2	1363.0	1362.0
20°	1357.4	1342.4	1349.7	1339.5	1339.5
22.5°	1332.9	1317.9	1326.3	1313.0	1313.0
25°	1293.6	1278.6	1284.7	1273.2	1271.9
27.5°	1246.9	1232.2	1238.5	1225.5	1225.2
30°	1213.2	1199.5	1206.9	1192.8	1191.6
32.5°	1176.5	1163.8	1169.1	1155.0	1153.8
35°	1117.6	1106.3	1109.9	1097.1	1095.9
37.5°	1055.6	1044.1	1048.2	1037.2	1036.7
40°	1011.7	1004.2	1005.3	996.3	993.8
42.5°	970.8	962.4	963.4	954.5	954.0
45°	908.3	902.1	902.0	893.0	893.0
47.5°	842.0	837.3	835.9	828.5	828.2
50°	796.1	792.3	791.0	784.6	783.3
52.5°	748.1	746.4	742.0	736.6	736.4
55°	673.6	671.1	664.7	660.8	659.6
57.5°	592.7	587.7	580.5	574.9	575.9
60°	534.5	529.6	519.2	516.7	516.7
62.5°	478.4	472.4	462.1	458.6	460.5
65°	398.0	390.6	381.4	378.9	380.2
67.5°	325.1	318.3	308.5	308.5	307.5
70°	278.1	274.4	266.6	266.6	266.6
72.5°	236.3	234.5	228.9	228.8	227.8
75°	181.2	181.2	178.6	177.3	176.1
77.5°	135.7	136.2	135.0	133.6	131.4
80°	107.2	109.7	108.4	107.1	105.9
82.5°	80.6	83.1	82.9	80.6	80.4
85°	42.1	45.8	45.9	45.9	45.9
87.5°	11.5	16.0	18.3	17.4	18.4
90°	1.3	3.7	10.0	5.0	5.0
92.5°	5.3	25.3	56.1	24.8	16.0
95°	12.5	49.2	163.9	84.5	57.6
97.5°	21.8	54.1	245.2	195.0	143.6
100°	28.8	58.1	270.3	273.9	212.7
102.5°	34.8	62.2	277.3	341.1	288.8
105°	45.0	68.3	276.5	419.8	391.6
107.5°	55.6	77.1	260.8	460.6	467.5
110°	62.6	82.1	247.7	471.1	500.5



TEST NUMBER: P563223

CATALOG NUMBER: SQ4-PP3-025U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.6	88.2	235.7	464.5	509.5
115°	80.1	97.2	221.5	441.8	504.2
117.5°	90.3	106.0	211.7	410.5	479.7
120°	96.3	111.0	207.7	389.4	456.7
122.5°	102.3	117.0	204.7	368.4	434.7
125°	111.4	124.8	201.4	340.5	401.6
127.5°	118.6	132.3	198.7	318.0	369.6
130°	122.6	137.3	197.7	303.9	351.6
132.5°	126.6	141.3	196.7	291.8	334.6
135°	132.6	146.1	195.2	274.8	311.6
137.5°	138.9	152.1	194.9	262.2	292.3
140°	143.9	156.1	193.9	252.1	280.3
142.5°	147.9	159.1	193.9	245.0	269.3
145°	153.9	163.7	192.7	234.4	252.7
147.5°	159.9	169.4	192.7	225.6	240.7
150°	163.9	172.5	192.7	220.5	232.7
152.5°	167.9	174.5	192.7	216.4	225.7
155°	173.9	178.8	192.7	211.6	217.7
157.5°	178.4	183.1	192.7	207.3	211.7
160°	181.4	185.1	192.7	205.3	207.7
162.5°	184.4	187.1	192.7	203.3	205.7
165°	187.7	190.1	192.7	200.2	202.7
167.5°	190.7	191.9	193.9	199.0	199.9
170°	192.7	193.9	193.9	198.9	198.9
172.5°	193.7	193.9	193.9	197.9	196.9
175°	195.2	195.2	193.9	196.4	196.4
177.5°	195.2	195.2	194.2	196.2	195.2
180°	195.2	195.2	195.2	195.2	195.2

(END OF REPORT)