

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564760

Luminaire Tested: **SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564760
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10091.4 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 91
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564760
CATALOG NUMBER: SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P564760

CATALOG NUMBER: SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	39	35
3	81	72	64	59	74	66	60	55	56	51	48	47	43	40	38	36	34	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	36	30	37	31	27	31	26	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8908	8908	8908
5°	8966	8895	8856
10°	8894	8823	8775
15°	8800	8703	8670
20°	8695	8561	8544
25°	8574	8418	8392
30°	8392	8266	8211
35°	8154	8039	7991
40°	7900	7777	7746
45°	7593	7492	7459
50°	7277	7216	7167
55°	6938	6938	6828
60°	6515	6640	6405
65°	5962	6259	5813
70°	5255	5761	5117
75°	4488	5155	4367
80°	3480	4338	3525
85°	2249	3335	2969



TEST NUMBER: P564760

CATALOG NUMBER: SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.8	1.8
10°-20°	513.4	5.1
20°-30°	761.5	7.5
30°-40°	891.1	8.8
40°-50°	887.1	8.8
50°-60°	766.0	7.6
60°-70°	551.4	5.5
70°-80°	289.2	2.9
80°-90°	73.7	0.7
90°-100°	374.7	3.7
100°-110°	1031.0	10.2
110°-120°	1064.2	10.5
120°-130°	852.6	8.4
130°-140°	669.7	6.6
140°-150°	513.2	5.1
150°-160°	369.0	3.7
160°-170°	225.6	2.2
170°-180°	76.1	0.8
0°-30°	1456.8	14.4
0°-40°	2347.8	23.3
0°-60°	4001.0	39.6
0°-90°	4915.2	48.7
90°-120°	2470.0	24.5
90°-150°	4505.5	44.6
90°-180°	5176.0	51.3
0°-180°	10091.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1931	1931	1931	1931	1931	
5°	1936	1915	1921	1916	1912	183
15°	1843	1819	1822	1819	1815	519
25°	1684	1656	1654	1644	1649	775
35°	1448	1428	1428	1414	1419	905
45°	1164	1154	1148	1145	1143	898
55°	863	861	863	851	849	770
65°	546	563	573	551	532	541
75°	252	275	289	270	245	270
85°	42	56	63	60	56	56
90°	2	7	12	15	15	5
95°	56	205	663	283	181	59
105°	184	283	1136	1730	1614	194
115°	326	397	911	1814	2059	322
125°	450	512	827	1398	1638	401
135°	543	602	803	1131	1280	419
145°	627	670	791	964	1038	393
155°	710	733	786	866	891	326
165°	768	777	790	822	827	216
175°	794	796	791	801	800	75
180°	794	794	794	794	794	



TEST NUMBER: P564760

CATALOG NUMBER: SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1931.1	1931.1	1931.1	1931.1	1931.1
2.5°	1942.0	1926.0	1931.1	1926.8	1917.5
5°	1936.2	1914.6	1920.9	1915.7	1912.4
7.5°	1916.5	1896.5	1901.2	1895.7	1893.7
10°	1898.8	1878.8	1883.5	1876.6	1873.2
12.5°	1878.4	1857.1	1861.7	1854.8	1852.8
15°	1842.6	1819.3	1822.2	1818.7	1815.4
17.5°	1801.1	1777.5	1778.0	1772.5	1771.8
20°	1771.2	1746.2	1743.9	1737.2	1740.5
22.5°	1738.5	1712.2	1709.9	1700.5	1705.1
25°	1684.4	1656.1	1653.8	1643.7	1648.7
27.5°	1621.8	1593.8	1593.9	1579.7	1585.0
30°	1575.5	1548.9	1551.7	1534.8	1541.5
32.5°	1526.5	1502.5	1504.0	1487.2	1493.8
35°	1447.9	1427.9	1427.5	1414.0	1419.0
37.5°	1367.6	1350.0	1347.2	1339.4	1340.7
40°	1311.8	1296.8	1291.4	1286.3	1286.3
42.5°	1253.3	1239.6	1234.2	1230.4	1229.1
45°	1163.8	1153.8	1148.4	1145.0	1143.3
47.5°	1075.3	1066.0	1061.3	1058.9	1057.3
50°	1014.0	1007.4	1005.5	1000.4	998.7
52.5°	952.8	948.8	947.0	940.5	938.8
55°	862.6	860.9	862.6	850.7	849.0
57.5°	768.7	771.4	776.9	760.8	756.8
60°	706.1	712.7	719.7	700.8	694.2
62.5°	642.1	652.8	662.5	640.9	631.6
65°	546.2	562.8	573.4	550.8	532.5
67.5°	453.6	474.2	486.9	462.7	442.0
70°	389.6	412.9	427.1	402.7	379.4
72.5°	333.8	359.8	371.2	348.3	325.0
75°	251.8	275.1	289.2	270.0	245.0
77.5°	178.6	200.6	212.3	195.5	174.9
80°	131.0	154.3	163.3	149.3	132.7
82.5°	92.9	112.2	118.4	110.0	98.7
85°	42.5	55.8	63.0	59.5	56.1
87.5°	11.2	21.5	28.2	28.9	30.3
90°	1.7	6.6	11.8	15.2	15.2
92.5°	23.3	99.7	172.8	66.3	54.4
95°	55.8	204.6	662.7	283.4	180.9
97.5°	90.9	226.8	1011.3	779.2	549.8
100°	116.6	240.6	1120.8	1131.3	923.0
102.5°	141.0	257.0	1149.2	1403.5	1212.4
105°	184.3	283.4	1136.0	1730.2	1614.4
107.5°	225.5	316.1	1071.5	1890.1	1924.5
110°	255.3	337.9	1022.8	1929.9	2048.9



TEST NUMBER: P564760

CATALOG NUMBER: SQ4-PW1-075U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.3	362.3	974.1	1904.3	2085.4
115°	326.3	397.3	911.2	1814.4	2059.1
117.5°	368.2	433.7	871.3	1688.4	1965.1
120°	393.9	456.7	853.7	1593.9	1879.9
122.5°	416.9	479.7	841.5	1511.1	1782.5
125°	449.7	512.5	826.7	1398.4	1638.1
127.5°	480.8	540.6	816.9	1304.4	1514.7
130°	497.0	558.2	811.4	1248.6	1440.3
132.5°	515.9	577.1	807.4	1199.5	1372.7
135°	542.7	602.2	803.0	1131.0	1279.7
137.5°	567.7	622.9	799.3	1075.6	1198.2
140°	586.6	637.9	797.9	1038.8	1149.6
142.5°	602.8	650.1	795.2	1006.0	1100.9
145°	627.2	670.2	791.2	963.6	1038.0
147.5°	653.2	690.2	789.1	926.1	985.6
150°	669.4	702.5	787.8	905.5	951.8
152.5°	684.3	714.7	786.4	887.7	926.1
155°	710.0	733.2	786.1	866.1	890.9
157.5°	728.6	747.5	786.1	848.4	865.5
160°	742.1	757.0	786.1	838.8	852.0
162.5°	753.0	765.2	787.4	830.6	841.2
165°	767.5	777.4	789.5	821.7	826.7
167.5°	777.6	785.2	791.2	814.2	815.5
170°	784.4	789.4	791.2	811.4	811.4
172.5°	789.8	792.1	791.2	807.4	806.0
175°	794.5	796.2	791.2	801.3	799.6
177.5°	795.9	795.9	790.5	798.5	795.9
180°	794.5	794.5	794.5	794.5	794.5

(END OF REPORT)