

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563775

Luminaire Tested: **SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563775
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10341.7 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563775
CATALOG NUMBER: SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563775

CATALOG NUMBER: SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	26	24	23	18
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6061
10°	6109	6066	6038
15°	6068	6035	6002
20°	6028	5994	5949
25°	5957	5915	5857
30°	5847	5815	5742
35°	5693	5654	5583
40°	5511	5477	5414
45°	5361	5324	5270
50°	5168	5136	5086
55°	4901	4836	4799
60°	4462	4334	4313
65°	3931	3767	3753
70°	3394	3253	3253
75°	2921	2880	2838
80°	2575	2607	2543
85°	2018	2202	2202



TEST NUMBER: P563775

CATALOG NUMBER: SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.4	0.9
10°-20°	266.7	2.6
20°-30°	399.4	3.9
30°-40°	468.5	4.5
40°-50°	470.0	4.5
50°-60°	400.9	3.9
60°-70°	261.5	2.5
70°-80°	131.2	1.3
80°-90°	38.8	0.4
90°-100°	563.1	5.4
100°-110°	1522.4	14.7
110°-120°	1600.6	15.5
120°-130°	1300.1	12.6
130°-140°	1019.8	9.9
140°-150°	782.7	7.6
150°-160°	562.9	5.4
160°-170°	343.9	3.3
170°-180°	115.9	1.1
0°-30°	759.5	7.3
0°-40°	1227.9	11.9
0°-60°	2098.8	20.3
0°-90°	2530.3	24.5
90°-120°	3686.0	35.6
90°-150°	6788.7	65.6
90°-180°	7811.0	75.5
0°-180°	10341.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	988	988	988	988	988	
5°	991	982	985	982	982	94
15°	953	944	948	944	943	269
25°	878	868	872	864	863	404
35°	758	751	753	744	744	474
45°	616	612	612	606	606	475
55°	457	455	451	448	448	406
65°	270	265	259	257	258	270
75°	123	123	121	120	119	133
85°	29	31	31	31	31	34
90°	3	8	17	18	17	7
95°	87	307	936	485	288	91
105°	283	437	1689	2491	2389	298
115°	498	609	1401	2712	3061	492
125°	682	782	1262	2130	2503	608
135°	818	915	1228	1720	1947	632
145°	951	1022	1212	1472	1585	595
155°	1073	1115	1201	1321	1364	495
165°	1168	1180	1206	1253	1260	329
175°	1213	1212	1208	1223	1221	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P563775

CATALOG NUMBER: SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	987.6	987.6	987.6	987.6	987.6
2.5°	993.8	985.7	987.6	986.1	982.1
5°	991.1	981.8	985.0	981.6	981.6
7.5°	984.3	974.2	977.4	973.9	973.8
10°	978.1	967.9	971.2	967.7	966.8
12.5°	969.1	958.9	962.9	958.7	958.5
15°	953.0	943.7	947.8	944.3	942.6
17.5°	934.8	924.7	929.6	924.8	924.1
20°	921.0	910.8	915.8	908.9	908.9
22.5°	904.3	894.2	899.8	890.8	890.8
25°	877.7	867.5	871.6	863.8	863.0
27.5°	846.0	836.0	840.3	831.5	831.3
30°	823.2	813.8	818.8	809.3	808.4
32.5°	798.2	789.6	793.2	783.7	782.8
35°	758.2	750.6	753.0	744.4	743.5
37.5°	716.2	708.4	711.2	703.7	703.4
40°	686.4	681.3	682.1	676.0	674.3
42.5°	658.7	652.9	653.7	647.6	647.3
45°	616.3	612.1	612.0	605.9	605.9
47.5°	571.3	568.1	567.1	562.1	561.9
50°	540.1	537.6	536.7	532.3	531.5
52.5°	507.6	506.4	503.4	499.8	499.6
55°	457.0	455.3	451.0	448.3	447.5
57.5°	402.1	398.8	393.8	390.0	390.7
60°	362.7	359.3	352.3	350.6	350.6
62.5°	324.6	320.5	313.5	311.1	312.5
65°	270.1	265.0	258.8	257.1	257.9
67.5°	220.5	216.0	209.3	209.3	208.6
70°	188.7	186.2	180.9	180.9	180.9
72.5°	160.3	159.1	155.3	155.3	154.6
75°	122.9	122.9	121.2	120.3	119.4
77.5°	92.1	92.4	91.6	90.7	89.2
80°	72.7	74.4	73.6	72.7	71.8
82.5°	54.7	56.4	56.3	54.7	54.5
85°	28.6	31.1	31.2	31.2	31.2
87.5°	8.1	11.9	14.5	14.7	15.2
90°	2.6	7.7	17.0	18.2	17.0
92.5°	37.0	135.0	266.3	115.6	83.7
95°	87.4	306.7	936.4	484.6	288.2
97.5°	140.3	351.8	1459.6	1207.9	887.1
100°	180.0	370.0	1622.4	1692.0	1368.1
102.5°	216.5	395.3	1679.8	2059.0	1816.7
105°	283.0	437.3	1688.9	2491.2	2389.2
107.5°	344.6	485.3	1615.1	2760.9	2794.8
110°	392.6	520.1	1549.3	2833.3	2977.4



TEST NUMBER: P563775

CATALOG NUMBER: SQ4-PP3-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.3	554.7	1488.8	2818.8	3060.9
115°	498.2	609.1	1400.7	2711.5	3060.9
117.5°	559.7	663.8	1342.5	2547.4	2943.5
120°	597.3	699.3	1308.1	2429.7	2833.9
122.5°	632.8	732.8	1287.2	2303.5	2710.8
125°	682.1	781.5	1262.4	2130.3	2502.7
127.5°	727.5	825.1	1247.8	1989.0	2316.4
130°	752.5	853.2	1241.6	1901.7	2197.5
132.5°	778.6	878.3	1235.3	1822.9	2095.3
135°	817.7	914.6	1228.5	1720.1	1947.1
137.5°	857.1	948.6	1222.8	1636.7	1821.6
140°	884.2	969.7	1220.7	1583.1	1747.6
142.5°	910.3	990.6	1216.5	1534.6	1678.7
145°	950.7	1022.1	1211.6	1472.3	1584.6
147.5°	987.5	1050.8	1205.8	1415.9	1502.1
150°	1014.6	1070.7	1203.7	1385.3	1454.1
152.5°	1039.7	1088.6	1202.7	1356.8	1413.4
155°	1073.3	1115.4	1201.1	1320.8	1364.1
157.5°	1108.3	1137.6	1201.4	1295.7	1324.2
160°	1128.1	1152.3	1202.4	1279.8	1300.2
162.5°	1143.7	1163.9	1203.5	1267.2	1282.5
165°	1168.5	1180.0	1206.3	1253.4	1259.8
167.5°	1185.5	1193.4	1206.6	1241.6	1244.7
170°	1195.9	1199.7	1207.6	1236.3	1236.3
172.5°	1204.3	1205.0	1207.6	1230.1	1229.0
175°	1212.9	1211.6	1207.6	1223.2	1220.7
177.5°	1215.7	1212.7	1207.4	1217.8	1214.7
180°	1211.6	1211.6	1211.6	1211.6	1211.6

(END OF REPORT)