

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563823

Luminaire Tested: **SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563823
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12764.1 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 112.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563823
CATALOG NUMBER: SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563823

CATALOG NUMBER: SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	38	33	38	32	28	30	26	24	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11896	11896	11896
5°	11984	11910	11868
10°	11964	11879	11826
15°	11884	11819	11755
20°	11806	11739	11650
25°	11665	11585	11469
30°	11449	11389	11244
35°	11150	11073	10933
40°	10793	10725	10603
45°	10498	10424	10322
50°	10121	10057	9959
55°	9598	9470	9398
60°	8737	8487	8445
65°	7698	7376	7351
70°	6645	6372	6372
75°	5720	5639	5559
80°	5044	5104	4984
85°	3945	4305	4305



TEST NUMBER: P563823

CATALOG NUMBER: SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.9	1.4
10°-20°	522.2	4.1
20°-30°	782.2	6.1
30°-40°	917.5	7.2
40°-50°	920.3	7.2
50°-60°	785.1	6.2
60°-70°	512.0	4.0
70°-80°	256.9	2.0
80°-90°	73.6	0.6
90°-100°	563.1	4.4
100°-110°	1522.4	11.9
110°-120°	1600.6	12.5
120°-130°	1300.1	10.2
130°-140°	1019.8	8.0
140°-150°	782.7	6.1
150°-160°	562.9	4.4
160°-170°	343.9	2.7
170°-180°	115.9	0.9
0°-30°	1487.3	11.7
0°-40°	2404.8	18.8
0°-60°	4110.2	32.2
0°-90°	4952.8	38.8
90°-120°	3686.0	28.9
90°-150°	6788.7	53.2
90°-180°	7811.0	61.2
0°-180°	12764.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1934	1934	1934	1934	1934	
5°	1941	1923	1929	1922	1922	184
15°	1866	1848	1856	1849	1846	527
25°	1719	1699	1707	1692	1690	790
35°	1485	1470	1475	1458	1456	928
45°	1207	1199	1198	1187	1187	929
55°	895	892	883	878	876	795
65°	529	519	507	504	505	528
75°	241	241	237	236	234	261
85°	56	61	61	61	61	66
90°	3	8	17	18	17	8
95°	87	307	936	485	288	91
105°	283	437	1689	2491	2389	298
115°	498	609	1401	2712	3061	492
125°	682	782	1262	2130	2503	608
135°	818	915	1228	1720	1947	632
145°	951	1022	1212	1472	1585	595
155°	1073	1115	1201	1321	1364	495
165°	1168	1180	1206	1253	1260	329
175°	1213	1212	1208	1223	1221	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P563823

CATALOG NUMBER: SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1934.1	1934.1	1934.1	1934.1	1934.1
2.5°	1946.3	1930.4	1934.1	1931.2	1923.3
5°	1940.9	1922.7	1929.0	1922.2	1922.2
7.5°	1927.7	1907.8	1914.1	1907.3	1907.0
10°	1915.5	1895.6	1901.9	1895.1	1893.4
12.5°	1897.8	1877.9	1885.6	1877.5	1877.1
15°	1866.3	1848.1	1856.1	1849.3	1846.0
17.5°	1830.7	1810.8	1820.5	1811.0	1809.7
20°	1803.6	1783.7	1793.4	1779.8	1779.8
22.5°	1771.0	1751.1	1762.2	1744.6	1744.6
25°	1718.8	1698.9	1707.0	1691.7	1690.0
27.5°	1656.8	1637.2	1645.6	1628.3	1628.0
30°	1612.0	1593.8	1603.6	1584.9	1583.2
32.5°	1563.2	1546.3	1553.4	1534.7	1533.0
35°	1484.9	1470.0	1474.7	1457.7	1456.1
37.5°	1402.5	1387.3	1392.7	1378.1	1377.4
40°	1344.2	1334.3	1335.7	1323.8	1320.5
42.5°	1290.0	1278.7	1280.1	1268.3	1267.6
45°	1206.9	1198.6	1198.4	1186.6	1186.6
47.5°	1118.8	1112.5	1110.6	1100.8	1100.5
50°	1057.7	1052.8	1051.0	1042.4	1040.8
52.5°	994.0	991.7	985.9	978.7	978.4
55°	895.0	891.7	883.1	878.0	876.4
57.5°	787.5	780.9	771.3	763.8	765.2
60°	710.2	703.6	689.9	686.5	686.5
62.5°	635.7	627.7	614.0	609.3	611.9
65°	528.9	518.9	506.8	503.5	505.1
67.5°	431.9	423.0	409.9	409.8	408.5
70°	369.5	364.6	354.3	354.3	354.3
72.5°	313.9	311.6	304.1	304.1	302.7
75°	240.7	240.7	237.3	235.6	233.9
77.5°	180.4	181.0	179.3	177.6	174.6
80°	142.4	145.7	144.1	142.4	140.7
82.5°	107.1	110.4	110.2	107.1	106.8
85°	55.9	60.9	61.0	61.0	61.0
87.5°	15.4	21.8	25.1	25.4	26.4
90°	2.6	7.7	17.0	18.2	17.0
92.5°	37.0	135.0	266.3	115.6	83.7
95°	87.4	306.7	936.4	484.6	288.2
97.5°	140.3	351.8	1459.6	1207.9	887.1
100°	180.0	370.0	1622.4	1692.0	1368.1
102.5°	216.5	395.3	1679.8	2059.0	1816.7
105°	283.0	437.3	1688.9	2491.2	2389.2
107.5°	344.6	485.3	1615.1	2760.9	2794.8
110°	392.6	520.1	1549.3	2833.3	2977.4



TEST NUMBER: P563823

CATALOG NUMBER: SQ4-PP3-150U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.3	554.7	1488.8	2818.8	3060.9
115°	498.2	609.1	1400.7	2711.5	3060.9
117.5°	559.7	663.8	1342.5	2547.4	2943.5
120°	597.3	699.3	1308.1	2429.7	2833.9
122.5°	632.8	732.8	1287.2	2303.5	2710.8
125°	682.1	781.5	1262.4	2130.3	2502.7
127.5°	727.5	825.1	1247.8	1989.0	2316.4
130°	752.5	853.2	1241.6	1901.7	2197.5
132.5°	778.6	878.3	1235.3	1822.9	2095.3
135°	817.7	914.6	1228.5	1720.1	1947.1
137.5°	857.1	948.6	1222.8	1636.7	1821.6
140°	884.2	969.7	1220.7	1583.1	1747.6
142.5°	910.3	990.6	1216.5	1534.6	1678.7
145°	950.7	1022.1	1211.6	1472.3	1584.6
147.5°	987.5	1050.8	1205.8	1415.9	1502.1
150°	1014.6	1070.7	1203.7	1385.3	1454.1
152.5°	1039.7	1088.6	1202.7	1356.8	1413.4
155°	1073.3	1115.4	1201.1	1320.8	1364.1
157.5°	1108.3	1137.6	1201.4	1295.7	1324.2
160°	1128.1	1152.3	1202.4	1279.8	1300.2
162.5°	1143.7	1163.9	1203.5	1267.2	1282.5
165°	1168.5	1180.0	1206.3	1253.4	1259.8
167.5°	1185.5	1193.4	1206.6	1241.6	1244.7
170°	1195.9	1199.7	1207.6	1236.3	1236.3
172.5°	1204.3	1205.0	1207.6	1230.1	1229.0
175°	1212.9	1211.6	1207.6	1223.2	1220.7
177.5°	1215.7	1212.7	1207.4	1217.8	1214.7
180°	1211.6	1211.6	1211.6	1211.6	1211.6

(END OF REPORT)