

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564135

Luminaire Tested: **SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564135
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10163.4 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564135
CATALOG NUMBER: SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564135

CATALOG NUMBER: SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57	53
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	51	47	47	44	42	38
4	77	66	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20
9	53	40	33	28	49	38	31	27	34	29	24	31	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15451	15451	15451
5°	15590	15470	15390
10°	15541	15432	15351
15°	15472	15376	15293
20°	15394	15296	15182
25°	15286	15183	15007
30°	15122	15014	14798
35°	14898	14768	14557
40°	14559	14402	14141
45°	13965	13720	13438
50°	12919	12609	12360
55°	11276	11021	10789
60°	9502	9422	9236
65°	8219	8251	8188
70°	7550	7587	7587
75°	7251	7251	7301
80°	6822	6896	6822
85°	5498	6105	6105



TEST NUMBER: P564135

CATALOG NUMBER: SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.6	2.3
10°-20°	679.7	6.7
20°-30°	1025.1	10.1
30°-40°	1221.4	12.0
40°-50°	1204.2	11.8
50°-60°	920.3	9.1
60°-70°	569.5	5.6
70°-80°	323.5	3.2
80°-90°	99.9	1.0
90°-100°	281.1	2.8
100°-110°	773.3	7.6
110°-120°	798.1	7.9
120°-130°	639.5	6.3
130°-140°	502.3	4.9
140°-150°	384.9	3.8
150°-160°	276.7	2.7
160°-170°	169.2	1.7
170°-180°	57.0	0.6
0°-30°	1942.3	19.1
0°-40°	3163.8	31.1
0°-60°	5288.4	52.0
0°-90°	6281.3	61.8
90°-120°	1852.5	18.2
90°-150°	3379.1	33.2
90°-180°	3882.0	38.2
0°-180°	10163.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2512	2512	2512	2512	2512	
5°	2525	2498	2506	2497	2493	240
15°	2430	2404	2415	2406	2402	686
25°	2252	2225	2237	2213	2211	1037
35°	1984	1961	1967	1941	1939	1238
45°	1605	1584	1577	1549	1545	1230
55°	1052	1035	1028	1010	1006	942
65°	565	560	567	563	563	572
75°	305	305	305	307	307	322
85°	78	82	86	86	86	91
90°	1	5	9	11	11	6
95°	42	153	497	212	136	44
105°	138	213	852	1298	1211	146
115°	245	298	683	1361	1544	241
125°	337	384	620	1049	1229	301
135°	407	452	602	848	960	314
145°	470	503	593	723	778	295
155°	532	550	590	650	668	245
165°	576	583	592	616	620	162
175°	596	597	593	601	600	57
180°	596	596	596	596	596	

TEST NUMBER: P564135

CATALOG NUMBER: SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2512.0	2512.0	2512.0	2512.0	2512.0
2.5°	2527.6	2505.6	2512.0	2506.6	2494.7
5°	2525.0	2497.5	2505.5	2496.8	2492.6
7.5°	2505.5	2478.5	2486.5	2477.8	2475.2
10°	2488.2	2462.8	2470.9	2462.2	2457.9
12.5°	2469.2	2442.1	2451.9	2441.4	2437.2
15°	2429.8	2404.4	2414.7	2405.9	2401.7
17.5°	2386.5	2359.5	2369.7	2359.6	2354.1
20°	2351.9	2326.5	2336.8	2321.6	2319.5
22.5°	2313.8	2288.4	2298.7	2278.3	2277.9
25°	2252.4	2224.9	2237.2	2213.4	2211.3
27.5°	2179.3	2153.9	2164.1	2139.8	2137.3
30°	2129.1	2103.7	2113.9	2087.9	2083.6
32.5°	2071.9	2048.2	2056.8	2030.8	2028.2
35°	1984.1	1960.8	1966.8	1940.8	1938.7
37.5°	1884.1	1863.0	1866.4	1837.8	1835.7
40°	1813.2	1792.0	1793.7	1763.3	1761.2
42.5°	1735.3	1714.1	1712.3	1682.0	1679.9
45°	1605.4	1584.3	1577.3	1549.1	1544.9
47.5°	1457.5	1436.3	1423.3	1400.3	1397.3
50°	1350.1	1329.0	1317.7	1298.1	1291.7
52.5°	1234.2	1213.0	1203.4	1185.6	1179.2
55°	1051.5	1034.6	1027.7	1010.3	1006.1
57.5°	878.0	866.6	864.6	847.7	846.0
60°	772.4	766.1	765.9	750.8	750.8
62.5°	682.4	677.8	681.1	671.1	669.4
65°	564.7	560.5	566.9	562.6	562.6
67.5°	471.7	471.7	475.6	473.8	473.8
70°	419.8	419.8	421.9	421.9	421.9
72.5°	373.0	371.3	376.9	376.9	375.2
75°	305.1	305.1	305.1	307.2	307.2
77.5°	237.6	238.0	239.7	239.3	237.6
80°	192.6	194.7	194.7	192.6	192.6
82.5°	147.6	149.7	149.7	149.3	147.6
85°	77.9	82.1	86.5	86.5	86.5
87.5°	22.8	30.3	36.4	36.9	35.2
90°	1.3	5.0	8.9	11.4	11.4
92.5°	17.5	74.8	129.6	49.8	40.8
95°	41.8	153.4	497.0	212.5	135.7
97.5°	68.2	170.1	758.5	584.4	412.3
100°	87.5	180.5	840.6	848.5	692.3
102.5°	105.7	192.8	861.9	1052.6	909.3
105°	138.2	212.6	852.0	1297.6	1210.8
107.5°	169.1	237.1	803.6	1417.6	1443.4
110°	191.5	253.4	767.1	1447.4	1536.7



TEST NUMBER: P564135

CATALOG NUMBER: SQ4-PR1-075U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.7	271.7	730.6	1428.2	1564.1
115°	244.7	298.0	683.4	1360.8	1544.3
117.5°	276.1	325.2	653.5	1266.3	1473.8
120°	295.4	342.5	640.3	1195.4	1409.9
122.5°	312.7	359.8	631.2	1133.3	1336.9
125°	337.3	384.4	620.0	1048.8	1228.6
127.5°	360.6	405.5	612.6	978.3	1136.0
130°	372.8	418.6	608.6	936.4	1080.2
132.5°	387.0	432.8	605.5	899.6	1029.5
135°	407.0	451.6	602.2	848.2	959.8
137.5°	425.8	467.2	599.5	806.7	898.7
140°	440.0	478.4	598.4	779.1	862.2
142.5°	452.1	487.6	596.4	754.5	825.6
145°	470.4	502.6	593.4	722.7	778.5
147.5°	489.9	517.7	591.9	694.5	739.2
150°	502.1	526.9	590.8	679.1	713.8
152.5°	513.2	536.1	589.8	665.8	694.5
155°	532.5	549.9	589.6	649.6	668.2
157.5°	546.5	560.6	589.6	636.3	649.2
160°	556.6	567.8	589.6	629.1	639.0
162.5°	564.7	573.9	590.6	623.0	630.9
165°	575.6	583.1	592.1	616.3	620.0
167.5°	583.2	588.9	593.4	610.6	611.6
170°	588.3	592.0	593.4	608.6	608.6
172.5°	592.4	594.1	593.4	605.5	604.5
175°	595.9	597.1	593.4	601.0	599.7
177.5°	596.9	596.9	592.9	598.9	596.9
180°	595.9	595.9	595.9	595.9	595.9

(END OF REPORT)