

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564303

Luminaire Tested: **SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564303
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10130.7 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 92.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564303
CATALOG NUMBER: SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564303

CATALOG NUMBER: SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	53	47	51	45	41	42	39	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	28	34	28	25	29	24	21	24	21	18	16
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12108	12108	12108
5°	12216	12123	12060
10°	12178	12094	12030
15°	12124	12049	11984
20°	12063	11986	11897
25°	11978	11898	11760
30°	11850	11765	11597
35°	11675	11572	11407
40°	11408	11286	11081
45°	10944	10751	10530
50°	10124	9881	9686
55°	8836	8637	8454
60°	7446	7383	7237
65°	6440	6465	6415
70°	5915	5945	5945
75°	5682	5682	5723
80°	5345	5405	5345
85°	4305	4785	4785



TEST NUMBER: P564303

CATALOG NUMBER: SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.1	1.8
10°-20°	532.6	5.3
20°-30°	803.3	7.9
30°-40°	957.1	9.4
40°-50°	943.7	9.3
50°-60°	721.2	7.1
60°-70°	446.3	4.4
70°-80°	253.5	2.5
80°-90°	78.8	0.8
90°-100°	375.4	3.7
100°-110°	1036.3	10.2
110°-120°	1068.7	10.5
120°-130°	858.8	8.5
130°-140°	674.9	6.7
140°-150°	517.7	5.1
150°-160°	372.0	3.7
160°-170°	227.5	2.2
170°-180°	76.7	0.8
0°-30°	1522.0	15.0
0°-40°	2479.2	24.5
0°-60°	4144.0	40.9
0°-90°	4922.6	48.6
90°-120°	2480.4	24.5
90°-150°	4531.8	44.7
90°-180°	5208.0	51.4
0°-180°	10130.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1968	1968	1968	1968	1968	
5°	1979	1957	1963	1956	1953	188
15°	1904	1884	1892	1885	1882	537
25°	1765	1744	1753	1734	1733	812
35°	1555	1536	1541	1521	1519	970
45°	1258	1242	1236	1214	1211	964
55°	824	811	805	792	788	738
65°	442	439	444	441	441	448
75°	239	239	239	241	241	252
85°	61	64	68	68	68	71
90°	3	5	10	12	13	6
95°	55	203	681	280	182	59
105°	185	285	1140	1741	1639	196
115°	331	400	918	1818	2067	325
125°	454	517	832	1409	1653	404
135°	546	605	809	1141	1286	423
145°	634	677	799	971	1045	397
155°	714	738	793	871	899	329
165°	773	783	796	827	834	218
175°	802	803	798	809	807	76
180°	802	802	802	802	802	

TEST NUMBER: P564303

CATALOG NUMBER: SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1968.5	1968.5	1968.5	1968.5	1968.5
2.5°	1980.7	1963.4	1968.5	1964.2	1954.9
5°	1978.6	1957.1	1963.4	1956.5	1953.2
7.5°	1963.4	1942.2	1948.5	1941.6	1939.6
10°	1949.8	1929.9	1936.3	1929.4	1926.1
12.5°	1934.9	1913.7	1921.3	1913.1	1909.8
15°	1904.0	1884.1	1892.2	1885.3	1882.0
17.5°	1870.1	1848.9	1856.9	1849.0	1844.7
20°	1843.0	1823.1	1831.1	1819.2	1817.6
22.5°	1813.2	1793.3	1801.3	1785.3	1785.0
25°	1765.0	1743.5	1753.1	1734.5	1732.8
27.5°	1707.7	1687.8	1695.8	1676.8	1674.8
30°	1668.4	1648.5	1656.5	1636.1	1632.8
32.5°	1623.6	1605.0	1611.7	1591.3	1589.4
35°	1554.8	1536.5	1541.2	1520.8	1519.2
37.5°	1476.4	1459.9	1462.5	1440.1	1438.5
40°	1420.8	1404.2	1405.6	1381.8	1380.1
42.5°	1359.8	1343.2	1341.8	1318.0	1316.4
45°	1258.1	1241.5	1236.0	1213.9	1210.6
47.5°	1142.1	1125.5	1115.3	1097.3	1094.9
50°	1058.0	1041.4	1032.6	1017.2	1012.2
52.5°	967.1	950.5	943.0	929.0	924.0
55°	824.0	810.7	805.4	791.7	788.4
57.5°	688.0	679.1	677.5	664.3	662.9
60°	605.3	600.3	600.2	588.3	588.3
62.5°	534.8	531.1	533.7	525.9	524.6
65°	442.5	439.2	444.2	440.8	440.8
67.5°	369.6	369.6	372.7	371.3	371.3
70°	328.9	328.9	330.6	330.6	330.6
72.5°	292.3	291.0	295.4	295.3	294.0
75°	239.1	239.1	239.1	240.8	240.8
77.5°	186.2	186.5	187.9	187.5	186.2
80°	150.9	152.6	152.6	150.9	150.9
82.5°	115.6	117.3	117.3	117.0	115.6
85°	61.0	64.4	67.8	67.8	67.8
87.5°	18.1	24.0	29.2	29.4	28.3
90°	2.6	5.1	10.3	11.6	12.8
92.5°	23.1	95.8	171.3	62.5	48.7
95°	55.1	203.1	681.0	279.9	182.1
97.5°	91.3	227.5	1008.8	776.7	562.5
100°	118.0	242.1	1129.9	1137.8	924.7
102.5°	143.6	258.8	1153.5	1405.9	1203.7
105°	184.7	285.0	1140.1	1740.6	1639.0
107.5°	228.3	317.6	1076.5	1902.0	1939.1
110°	259.1	339.3	1027.3	1936.7	2057.1



TEST NUMBER: P564303

CATALOG NUMBER: SQ4-PR1-100U-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	286.8	364.0	981.1	1909.3	2086.8
115°	330.9	399.8	918.3	1817.8	2067.4
117.5°	369.4	438.1	877.0	1689.1	1973.0
120°	395.0	462.7	860.5	1601.9	1887.8
122.5°	419.6	484.3	847.2	1520.5	1791.4
125°	454.0	516.7	832.3	1408.6	1653.1
127.5°	483.2	545.9	823.6	1313.9	1524.9
130°	502.7	565.4	819.5	1256.1	1447.9
132.5°	521.2	580.9	815.4	1207.4	1381.2
135°	546.3	605.3	809.2	1140.9	1286.3
137.5°	574.6	628.2	806.2	1085.0	1209.1
140°	589.9	642.6	804.1	1047.7	1156.8
142.5°	607.4	656.0	802.1	1014.6	1110.6
145°	633.5	677.4	799.0	971.2	1045.2
147.5°	658.7	697.1	796.2	934.7	992.1
150°	677.1	708.5	795.1	912.9	959.3
152.5°	691.5	720.9	794.1	894.2	932.6
155°	714.3	738.2	792.6	871.4	899.0
157.5°	735.4	753.7	792.8	854.8	873.6
160°	747.7	764.0	793.9	845.5	859.3
162.5°	757.9	772.2	794.9	837.2	848.0
165°	773.3	783.4	796.4	827.3	833.6
167.5°	785.1	791.2	797.7	821.3	823.4
170°	791.3	796.3	797.7	818.2	818.2
172.5°	796.4	799.4	797.7	814.1	813.1
175°	801.5	802.8	797.7	809.2	806.7
177.5°	803.6	802.6	797.4	804.6	802.6
180°	801.5	801.5	801.5	801.5	801.5

(END OF REPORT)