

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564423

Luminaire Tested: **SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564423
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12764.9 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564423
CATALOG NUMBER: SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564423

CATALOG NUMBER: SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35	31
4	75	64	56	51	69	60	53	47	51	46	41	43	39	36	35	32	30	26
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15451	15451	15451
5°	15590	15470	15390
10°	15541	15432	15351
15°	15472	15376	15293
20°	15394	15296	15182
25°	15286	15183	15007
30°	15122	15014	14798
35°	14898	14768	14557
40°	14559	14402	14141
45°	13965	13720	13438
50°	12919	12609	12360
55°	11276	11021	10789
60°	9502	9422	9236
65°	8219	8251	8188
70°	7550	7587	7587
75°	7251	7251	7301
80°	6822	6896	6822
85°	5498	6105	6105



TEST NUMBER: P564423

CATALOG NUMBER: SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.6	1.9
10°-20°	679.7	5.3
20°-30°	1025.1	8.0
30°-40°	1221.4	9.6
40°-50°	1204.2	9.4
50°-60°	920.3	7.2
60°-70°	569.5	4.5
70°-80°	323.5	2.5
80°-90°	100.8	0.8
90°-100°	469.8	3.7
100°-110°	1265.4	9.9
110°-120°	1328.0	10.4
120°-130°	1077.7	8.4
130°-140°	845.2	6.6
140°-150°	648.9	5.1
150°-160°	466.6	3.7
160°-170°	285.0	2.2
170°-180°	96.1	0.8
0°-30°	1942.3	15.2
0°-40°	3163.8	24.8
0°-60°	5288.4	41.4
0°-90°	6282.2	49.2
90°-120°	3063.3	24.0
90°-150°	5635.0	44.1
90°-180°	6483.0	50.8
0°-180°	12764.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2512	2512	2512	2512	2512	
5°	2525	2498	2506	2497	2493	240
15°	2430	2404	2415	2406	2402	686
25°	2252	2225	2237	2213	2211	1037
35°	1984	1961	1967	1941	1939	1238
45°	1605	1584	1577	1549	1545	1230
55°	1052	1035	1028	1010	1006	942
65°	565	560	567	563	563	572
75°	305	305	305	307	307	322
85°	78	82	86	86	86	91
90°	3	8	15	17	17	8
95°	72	256	770	394	272	75
105°	234	364	1400	2094	1965	246
115°	413	506	1165	2252	2547	407
125°	564	648	1046	1769	2081	504
135°	679	758	1017	1427	1616	524
145°	786	847	1004	1220	1310	493
155°	892	924	995	1094	1130	410
165°	967	978	999	1039	1044	273
175°	1006	1004	1000	1014	1012	96
180°	1004	1004	1004	1004	1004	



TEST NUMBER: P564423

CATALOG NUMBER: SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2512.0	2512.0	2512.0	2512.0	2512.0
2.5°	2527.6	2505.6	2512.0	2506.6	2494.7
5°	2525.0	2497.5	2505.5	2496.8	2492.6
7.5°	2505.5	2478.5	2486.5	2477.8	2475.2
10°	2488.2	2462.8	2470.9	2462.2	2457.9
12.5°	2469.2	2442.1	2451.9	2441.4	2437.2
15°	2429.8	2404.4	2414.7	2405.9	2401.7
17.5°	2386.5	2359.5	2369.7	2359.6	2354.1
20°	2351.9	2326.5	2336.8	2321.6	2319.5
22.5°	2313.8	2288.4	2298.7	2278.3	2277.9
25°	2252.4	2224.9	2237.2	2213.4	2211.3
27.5°	2179.3	2153.9	2164.1	2139.8	2137.3
30°	2129.1	2103.7	2113.9	2087.9	2083.6
32.5°	2071.9	2048.2	2056.8	2030.8	2028.2
35°	1984.1	1960.8	1966.8	1940.8	1938.7
37.5°	1884.1	1863.0	1866.4	1837.8	1835.7
40°	1813.2	1792.0	1793.7	1763.3	1761.2
42.5°	1735.3	1714.1	1712.3	1682.0	1679.9
45°	1605.4	1584.3	1577.3	1549.1	1544.9
47.5°	1457.5	1436.3	1423.3	1400.3	1397.3
50°	1350.1	1329.0	1317.7	1298.1	1291.7
52.5°	1234.2	1213.0	1203.4	1185.6	1179.2
55°	1051.5	1034.6	1027.7	1010.3	1006.1
57.5°	878.0	866.6	864.6	847.7	846.0
60°	772.4	766.1	765.9	750.8	750.8
62.5°	682.4	677.8	681.1	671.1	669.4
65°	564.7	560.5	566.9	562.6	562.6
67.5°	471.7	471.7	475.6	473.8	473.8
70°	419.8	419.8	421.9	421.9	421.9
72.5°	373.0	371.3	376.9	376.9	375.2
75°	305.1	305.1	305.1	307.2	307.2
77.5°	237.6	238.0	239.7	239.3	237.6
80°	192.6	194.7	194.7	192.6	192.6
82.5°	147.6	149.7	149.7	149.3	147.6
85°	77.9	82.1	86.5	86.5	86.5
87.5°	23.0	30.8	37.7	37.9	36.2
90°	2.6	7.6	15.4	16.6	16.6
92.5°	31.2	110.3	218.0	104.9	72.9
95°	71.6	255.5	770.1	393.8	272.5
97.5°	114.4	292.5	1207.9	1009.1	760.9
100°	147.1	307.2	1347.0	1409.4	1169.2
102.5°	178.8	327.9	1393.1	1709.2	1512.1
105°	234.1	364.2	1399.5	2093.7	1964.9
107.5°	286.3	402.4	1339.9	2291.4	2324.6
110°	321.1	431.2	1285.6	2352.7	2474.1



TEST NUMBER: P564423

CATALOG NUMBER: SQ4-PR1-125U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.9	460.0	1233.4	2339.1	2538.5
115°	413.2	505.8	1165.4	2251.8	2547.0
117.5°	463.6	550.4	1112.7	2112.3	2441.0
120°	496.3	580.2	1086.1	2012.2	2350.0
122.5°	525.0	607.8	1066.6	1909.9	2246.6
125°	564.1	648.0	1046.4	1768.6	2081.3
127.5°	601.8	684.3	1033.6	1644.0	1923.2
130°	624.3	706.8	1028.5	1572.6	1817.8
132.5°	646.8	728.3	1023.4	1509.8	1734.9
135°	679.3	758.1	1017.0	1426.8	1615.7
137.5°	710.2	785.8	1013.7	1356.5	1511.6
140°	731.7	804.3	1010.6	1313.1	1453.2
142.5°	754.2	821.8	1008.6	1272.7	1390.8
145°	785.5	846.7	1004.2	1219.9	1309.9
147.5°	819.2	872.5	999.9	1175.4	1246.2
150°	841.7	888.0	997.8	1147.5	1206.3
152.5°	862.2	902.5	996.8	1124.8	1172.6
155°	891.6	924.2	995.2	1094.5	1129.6
157.5°	917.5	942.7	995.5	1073.3	1096.8
160°	933.8	955.1	996.5	1060.9	1078.4
162.5°	948.2	965.4	997.6	1050.5	1063.0
165°	967.1	978.4	999.1	1038.9	1043.9
167.5°	982.5	989.0	1000.4	1029.8	1031.8
170°	992.7	995.2	1000.4	1024.7	1024.7
172.5°	998.8	999.3	1001.4	1019.6	1019.6
175°	1005.5	1004.2	1000.4	1014.4	1011.9
177.5°	1008.3	1006.3	1001.1	1009.3	1007.3
180°	1004.2	1004.2	1004.2	1004.2	1004.2

(END OF REPORT)