

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P564447

Luminaire Tested: **SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564447
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10326.7 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564447
CATALOG NUMBER: SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564447

CATALOG NUMBER: SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	28	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6183	6183	6183
5°	6239	6190	6158
10°	6218	6175	6143
15°	6191	6153	6119
20°	6160	6120	6075
25°	6117	6075	6005
30°	6050	6008	5921
35°	5961	5909	5825
40°	5825	5763	5658
45°	5588	5490	5377
50°	5169	5046	4946
55°	4512	4410	4317
60°	3802	3770	3695
65°	3289	3301	3276
70°	3021	3036	3036
75°	2902	2902	2921
80°	2731	2759	2731
85°	2202	2442	2442



TEST NUMBER: P564447

CATALOG NUMBER: SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.1	0.9
10°-20°	272.0	2.6
20°-30°	410.2	4.0
30°-40°	488.8	4.7
40°-50°	481.9	4.7
50°-60°	368.3	3.6
60°-70°	227.9	2.2
70°-80°	129.4	1.3
80°-90°	41.9	0.4
90°-100°	563.1	5.5
100°-110°	1522.4	14.7
110°-120°	1600.6	15.5
120°-130°	1300.1	12.6
130°-140°	1019.8	9.9
140°-150°	782.7	7.6
150°-160°	562.9	5.5
160°-170°	343.9	3.3
170°-180°	115.9	1.1
0°-30°	777.2	7.5
0°-40°	1266.0	12.3
0°-60°	2116.1	20.5
0°-90°	2515.3	24.4
90°-120°	3686.0	35.7
90°-150°	6788.7	65.7
90°-180°	7811.0	75.6
0°-180°	10326.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	1010	999	1003	999	997	96
15°	972	962	966	963	961	274
25°	901	890	895	886	885	415
35°	794	785	787	777	776	495
45°	642	634	631	620	618	492
55°	421	414	411	404	403	377
65°	226	224	227	225	225	229
75°	122	122	122	123	123	129
85°	31	33	35	35	35	36
90°	3	8	17	18	17	7
95°	87	307	936	485	288	91
105°	283	437	1689	2491	2389	298
115°	498	609	1401	2712	3061	492
125°	682	782	1262	2130	2503	608
135°	818	915	1228	1720	1947	632
145°	951	1022	1212	1472	1585	595
155°	1073	1115	1201	1321	1364	495
165°	1168	1180	1206	1253	1260	329
175°	1213	1212	1208	1223	1221	115
180°	1212	1212	1212	1212	1212	



TEST NUMBER: P564447

CATALOG NUMBER: SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1005.2	1005.2	1005.2	1005.2	1005.2
2.5°	1011.4	1002.6	1005.2	1003.0	998.2
5°	1010.4	999.4	1002.6	999.1	997.4
7.5°	1002.6	991.7	994.9	991.5	990.4
10°	995.6	985.5	988.7	985.2	983.5
12.5°	988.0	977.2	981.1	976.9	975.2
15°	972.3	962.1	966.2	962.7	961.0
17.5°	954.9	944.1	948.2	944.2	942.0
20°	941.1	930.9	935.0	929.0	928.1
22.5°	925.9	915.7	919.8	911.7	911.5
25°	901.3	890.3	895.2	885.7	884.8
27.5°	872.0	861.8	865.9	856.2	855.2
30°	851.9	841.8	845.9	835.4	833.7
32.5°	829.1	819.6	823.0	812.6	811.6
35°	793.9	784.6	787.0	776.6	775.7
37.5°	753.9	745.5	746.8	735.4	734.5
40°	725.5	717.1	717.7	705.6	704.7
42.5°	694.4	685.9	685.2	673.0	672.2
45°	642.4	633.9	631.1	619.9	618.2
47.5°	583.2	574.7	569.5	560.3	559.1
50°	540.2	531.8	527.3	519.4	516.9
52.5°	493.8	485.4	481.5	474.4	471.8
55°	420.8	414.0	411.2	404.3	402.6
57.5°	351.3	346.8	346.0	339.2	338.5
60°	309.1	306.5	306.5	300.4	300.4
62.5°	273.1	271.2	272.5	268.5	267.9
65°	226.0	224.3	226.8	225.1	225.1
67.5°	188.7	188.7	190.3	189.6	189.6
70°	168.0	168.0	168.8	168.8	168.8
72.5°	149.3	148.6	150.8	150.8	150.1
75°	122.1	122.1	122.1	122.9	122.9
77.5°	95.1	95.2	95.9	95.7	95.1
80°	77.1	77.9	77.9	77.1	77.1
82.5°	59.0	59.9	59.9	59.7	59.0
85°	31.2	32.9	34.6	34.6	34.6
87.5°	9.5	13.3	17.2	17.5	16.6
90°	2.6	7.7	17.0	18.2	17.0
92.5°	37.0	135.0	266.3	115.6	83.7
95°	87.4	306.7	936.4	484.6	288.2
97.5°	140.3	351.8	1459.6	1207.9	887.1
100°	180.0	370.0	1622.4	1692.0	1368.1
102.5°	216.5	395.3	1679.8	2059.0	1816.7
105°	283.0	437.3	1688.9	2491.2	2389.2
107.5°	344.6	485.3	1615.1	2760.9	2794.8
110°	392.6	520.1	1549.3	2833.3	2977.4



TEST NUMBER: P564447

CATALOG NUMBER: SQ4-PR1-150U-050D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.3	554.7	1488.8	2818.8	3060.9
115°	498.2	609.1	1400.7	2711.5	3060.9
117.5°	559.7	663.8	1342.5	2547.4	2943.5
120°	597.3	699.3	1308.1	2429.7	2833.9
122.5°	632.8	732.8	1287.2	2303.5	2710.8
125°	682.1	781.5	1262.4	2130.3	2502.7
127.5°	727.5	825.1	1247.8	1989.0	2316.4
130°	752.5	853.2	1241.6	1901.7	2197.5
132.5°	778.6	878.3	1235.3	1822.9	2095.3
135°	817.7	914.6	1228.5	1720.1	1947.1
137.5°	857.1	948.6	1222.8	1636.7	1821.6
140°	884.2	969.7	1220.7	1583.1	1747.6
142.5°	910.3	990.6	1216.5	1534.6	1678.7
145°	950.7	1022.1	1211.6	1472.3	1584.6
147.5°	987.5	1050.8	1205.8	1415.9	1502.1
150°	1014.6	1070.7	1203.7	1385.3	1454.1
152.5°	1039.7	1088.6	1202.7	1356.8	1413.4
155°	1073.3	1115.4	1201.1	1320.8	1364.1
157.5°	1108.3	1137.6	1201.4	1295.7	1324.2
160°	1128.1	1152.3	1202.4	1279.8	1300.2
162.5°	1143.7	1163.9	1203.5	1267.2	1282.5
165°	1168.5	1180.0	1206.3	1253.4	1259.8
167.5°	1185.5	1193.4	1206.6	1241.6	1244.7
170°	1195.9	1199.7	1207.6	1236.3	1236.3
172.5°	1204.3	1205.0	1207.6	1230.1	1229.0
175°	1212.9	1211.6	1207.6	1223.2	1220.7
177.5°	1215.7	1212.7	1207.4	1217.8	1214.7
180°	1211.6	1211.6	1211.6	1211.6	1211.6

(END OF REPORT)