

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519687

Luminaire Tested: **SQ4-050U-0D-940-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519687
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-050U-0D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5165.9 lumens
Efficiency: N/A
Efficacy: 197.2 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 26.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519687
CATALOG NUMBER: SQ4-050U-0D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519687

CATALOG NUMBER: SQ4-050U-0D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	1976	23338	6821
100°	2072	19869	16265
105°	2177	13482	19316
110°	2310	9174	18414
115°	2369	6609	14977
120°	2410	5226	11501
125°	2400	4406	8757
130°	2374	3871	6853
135°	2346	3474	5532
140°	2339	3186	4586
145°	2340	2961	3868
150°	2376	2792	3361
155°	2391	2659	3004
160°	2415	2565	2781
165°	2430	2503	2616
170°	2439	2463	2519
175°	2443	2435	2458



TEST NUMBER: P519687

CATALOG NUMBER: SQ4-050U-0D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	379.8	7.4
100°-110°	1031.8	20.0
110°-120°	1060.8	20.5
120°-130°	848.2	16.4
130°-140°	666.4	12.9
140°-150°	511.0	9.9
150°-160°	367.5	7.1
160°-170°	224.7	4.4
170°-180°	75.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2472.4	47.9
90°-150°	4498.0	87.1
90°-180°	5166.0	100.0
0°-180°	5165.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	10	18	23	23	
95°	56	208	661	288	193	63
105°	183	285	1135	1728	1626	195
115°	326	395	908	1807	2058	321
125°	448	510	822	1384	1633	399
135°	539	599	799	1128	1272	417
145°	623	668	789	958	1030	391
155°	705	730	784	860	885	325
165°	763	773	786	819	822	215
175°	791	794	789	799	796	75
180°	791	791	791	791	791	



TEST NUMBER: P519687

CATALOG NUMBER: SQ4-050U-0D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.5	10.0	17.8	22.9	22.9
92.5°	22.9	104.0	180.6	77.6	65.6
95°	56.0	207.7	661.4	287.9	193.3
97.5°	92.6	229.4	1014.0	788.9	554.1
100°	117.0	243.9	1121.9	1137.3	918.4
102.5°	141.4	258.4	1150.4	1406.5	1213.5
105°	183.2	285.2	1134.6	1727.6	1625.6
107.5°	226.4	316.5	1069.0	1893.4	1921.8
110°	256.9	339.0	1020.2	1926.1	2047.9
112.5°	283.4	361.5	971.3	1899.0	2082.5
115°	325.6	395.3	908.2	1806.9	2058.1
117.5°	365.3	432.0	868.0	1676.3	1959.4
120°	391.8	456.5	849.7	1588.8	1869.9
122.5°	414.2	478.8	837.5	1501.0	1772.2
125°	447.7	509.9	821.7	1384.5	1633.3
127.5°	477.8	539.5	813.1	1296.2	1509.6
130°	496.1	555.8	809.0	1240.8	1432.3
132.5°	514.4	574.1	804.9	1193.4	1363.1
135°	539.3	599.0	798.8	1127.7	1272.0
137.5°	566.3	620.5	795.8	1069.7	1191.1
140°	582.6	634.8	793.7	1032.8	1142.3
142.5°	598.9	647.1	791.7	1003.9	1095.5
145°	623.3	668.1	788.6	958.2	1030.3
147.5°	650.8	689.1	786.1	922.2	978.9
150°	669.1	701.4	786.1	901.6	946.4
152.5°	683.3	711.7	784.1	883.1	919.9
155°	704.7	729.6	783.6	860.4	885.3
157.5°	725.6	745.0	783.6	845.0	864.0
160°	737.8	755.2	783.6	834.8	849.7
162.5°	750.0	763.4	785.6	826.5	837.5
165°	763.2	773.2	786.1	819.2	821.7
167.5°	776.9	781.9	788.6	810.6	812.6
170°	781.0	786.0	788.6	806.5	806.5
172.5°	785.1	788.1	788.6	802.4	802.4
175°	791.2	793.7	788.6	798.8	796.3
177.5°	793.2	793.2	787.1	795.2	791.2
180°	791.2	791.2	791.2	791.2	791.2

(END OF REPORT)