

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519711

Luminaire Tested: **SQ4-075U-0D-940-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519711
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7764.2 lumens
Efficiency: N/A
Efficacy: 143.8 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519711
CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519711

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2953	35075	9573
100°	3099	29775	24520
105°	3284	20248	28776
110°	3443	13794	27636
115°	3561	9946	22476
120°	3634	7877	17344
125°	3617	6649	13175
130°	3567	5824	10337
135°	3540	5239	8349
140°	3532	4805	6922
145°	3532	4455	5846
150°	3566	4196	5070
155°	3614	4001	4535
160°	3643	3859	4183
165°	3665	3770	3948
170°	3674	3706	3801
175°	3679	3664	3703



TEST NUMBER: P519711

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	562.1	7.2
100°-110°	1546.5	19.9
110°-120°	1596.3	20.6
120°-130°	1279.0	16.5
130°-140°	1004.5	12.9
140°-150°	769.8	9.9
150°-160°	553.5	7.1
160°-170°	338.4	4.4
170°-180°	114.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3704.9	47.7
90°-150°	6758.2	87.0
90°-180°	7764.0	100.0
0°-180°	7764.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	10	18	23	23	
95°	84	307	994	425	271	94
105°	276	425	1704	2595	2422	291
115°	489	596	1367	2722	3089	483
125°	674	769	1240	2098	2457	602
135°	814	903	1204	1696	1920	628
145°	941	1005	1187	1445	1557	590
155°	1065	1100	1179	1299	1336	489
165°	1151	1166	1184	1233	1240	324
175°	1192	1194	1187	1202	1199	113
180°	1192	1192	1192	1192	1192	



TEST NUMBER: P519711

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.5	10.0	17.8	22.8	22.8
92.5°	35.0	149.5	259.2	99.5	81.7
95°	83.7	306.8	994.0	425.1	271.3
97.5°	136.4	340.2	1516.9	1168.8	824.6
100°	175.0	360.9	1681.2	1696.9	1384.5
102.5°	211.5	385.5	1723.8	2105.3	1818.7
105°	276.4	425.2	1704.0	2595.2	2421.7
107.5°	338.3	474.1	1607.2	2835.2	2886.7
110°	382.9	506.9	1534.1	2894.8	3073.4
112.5°	423.5	543.5	1461.1	2856.4	3128.1
115°	489.4	596.0	1366.8	2721.6	3088.6
117.5°	552.3	650.5	1306.9	2532.5	2947.6
120°	590.8	685.1	1280.6	2390.8	2819.8
122.5°	625.3	719.5	1262.3	2266.6	2673.7
125°	674.5	768.7	1240.0	2097.7	2457.2
127.5°	721.2	810.9	1225.3	1956.7	2272.1
130°	745.5	837.3	1217.2	1872.9	2160.5
132.5°	773.9	865.7	1211.1	1799.2	2059.1
135°	814.0	903.2	1204.5	1696.4	1919.6
137.5°	851.5	934.3	1198.9	1613.4	1797.4
140°	879.9	956.8	1196.9	1558.2	1724.3
142.5°	904.3	975.2	1192.8	1509.0	1651.3
145°	940.8	1005.2	1186.7	1445.4	1557.0
147.5°	979.8	1035.4	1183.7	1389.1	1478.4
150°	1004.2	1053.8	1181.7	1358.2	1427.6
152.5°	1026.5	1072.1	1179.6	1331.6	1389.1
155°	1065.0	1099.7	1179.1	1299.2	1336.4
157.5°	1092.9	1121.2	1179.1	1272.5	1298.3
160°	1113.2	1135.5	1179.1	1258.2	1278.0
162.5°	1129.4	1147.8	1181.2	1245.9	1261.8
165°	1151.2	1166.1	1184.2	1232.6	1240.0
167.5°	1166.5	1177.9	1186.7	1221.3	1223.3
170°	1176.6	1184.0	1186.7	1217.2	1217.2
172.5°	1184.7	1188.2	1186.7	1211.0	1209.1
175°	1191.8	1194.3	1186.7	1201.9	1199.4
177.5°	1193.8	1193.8	1185.7	1197.8	1193.8
180°	1191.8	1191.8	1191.8	1191.8	1191.8

(END OF REPORT)