

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564567

Luminaire Tested: **SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564567
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4951.1 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564567
CATALOG NUMBER: SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564567

CATALOG NUMBER: SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	74
1	103	99	95	91	98	94	91	88	85	83	80	77	75	73	70	68	67	63
2	94	87	80	75	89	83	77	72	75	71	67	68	64	61	62	59	56	53
3	86	76	69	63	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	60	52	46	69	58	50	44	53	47	42	48	43	39	44	40	36	34
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	30
7	62	49	41	35	59	47	40	34	43	37	32	40	34	30	37	32	28	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	23
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	26	23	21
10	50	38	30	25	48	36	29	25	34	28	24	31	26	22	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8908	8908	8908
5°	8966	8895	8856
10°	8894	8823	8775
15°	8800	8703	8670
20°	8695	8562	8545
25°	8574	8417	8392
30°	8392	8266	8211
35°	8154	8039	7991
40°	7899	7776	7746
45°	7592	7492	7459
50°	7277	7216	7167
55°	6938	6938	6829
60°	6515	6640	6404
65°	5961	6258	5813
70°	5255	5760	5118
75°	4489	5155	4368
80°	3482	4339	3524
85°	2251	3331	2971



TEST NUMBER: P564567

CATALOG NUMBER: SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	2.8
10°-20°	385.0	7.8
20°-30°	571.2	11.5
30°-40°	668.3	13.5
40°-50°	665.3	13.4
50°-60°	574.5	11.6
60°-70°	413.6	8.4
70°-80°	216.9	4.4
80°-90°	54.8	1.1
90°-100°	95.1	1.9
100°-110°	250.1	5.1
110°-120°	259.3	5.2
120°-130°	208.0	4.2
130°-140°	163.2	3.3
140°-150°	125.3	2.5
150°-160°	90.2	1.8
160°-170°	55.2	1.1
170°-180°	18.6	0.4
0°-30°	1092.6	22.1
0°-40°	1760.9	35.6
0°-60°	3000.7	60.6
0°-90°	3686.0	74.4
90°-120°	604.6	12.2
90°-150°	1101.1	22.2
90°-180°	1265.0	25.5
0°-180°	4951.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1452	1436	1441	1437	1434	138
15°	1382	1364	1367	1364	1362	390
25°	1263	1242	1240	1233	1236	581
35°	1086	1071	1071	1060	1064	679
45°	873	865	861	859	858	673
55°	647	646	647	638	637	577
65°	410	422	430	413	399	406
75°	189	206	217	202	184	202
85°	32	42	47	45	42	42
90°	1	4	10	5	5	2
95°	12	49	164	84	58	14
105°	45	68	276	420	392	48
115°	80	97	222	442	504	79
125°	111	125	201	340	402	99
135°	133	146	195	275	312	103
145°	154	164	193	234	253	96
155°	174	179	193	212	218	80
165°	188	190	193	200	203	53
175°	195	195	194	196	196	19
180°	195	195	195	195	195	

TEST NUMBER: P564567

CATALOG NUMBER: SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1448.3	1448.3	1448.3	1448.3	1448.3
2.5°	1456.5	1444.5	1448.3	1445.1	1438.1
5°	1452.2	1435.9	1440.7	1436.8	1434.3
7.5°	1437.3	1422.4	1425.9	1421.7	1420.2
10°	1424.1	1409.1	1412.6	1407.4	1404.9
12.5°	1408.8	1392.8	1396.3	1391.1	1389.6
15°	1382.0	1364.5	1366.7	1364.0	1361.6
17.5°	1350.8	1333.1	1333.5	1329.4	1328.9
20°	1328.4	1309.7	1308.0	1302.9	1305.4
22.5°	1303.9	1284.2	1282.4	1275.4	1278.9
25°	1263.3	1242.1	1240.3	1232.8	1236.5
27.5°	1216.3	1195.4	1195.4	1184.8	1188.8
30°	1181.6	1161.7	1163.8	1151.1	1156.1
32.5°	1144.9	1126.9	1128.0	1115.4	1120.4
35°	1085.9	1071.0	1070.6	1060.5	1064.2
37.5°	1025.7	1012.5	1010.4	1004.5	1005.5
40°	983.8	972.6	968.5	964.7	964.7
42.5°	939.9	929.7	925.7	922.8	921.8
45°	872.8	865.3	861.3	858.8	857.5
47.5°	806.5	799.5	796.0	794.2	792.9
50°	760.5	755.5	754.1	750.3	749.0
52.5°	714.6	711.6	710.3	705.4	704.1
55°	647.0	645.7	647.0	638.0	636.8
57.5°	576.5	578.5	582.6	570.6	567.6
60°	529.6	534.6	539.8	525.6	520.6
62.5°	481.6	489.6	496.9	480.7	473.7
65°	409.6	422.1	430.0	413.1	399.4
67.5°	340.2	355.7	365.2	347.0	331.5
70°	292.2	309.7	320.3	302.0	284.6
72.5°	250.4	269.8	278.4	261.2	243.7
75°	188.9	206.3	216.9	202.5	183.8
77.5°	134.0	150.5	159.3	146.6	131.2
80°	98.3	115.7	122.5	112.0	99.5
82.5°	69.7	84.1	88.8	82.5	74.0
85°	31.9	41.9	47.2	44.6	42.1
87.5°	8.4	15.9	21.4	20.4	21.4
90°	1.3	3.7	10.0	5.0	5.0
92.5°	5.3	25.3	56.1	24.8	16.0
95°	12.5	49.2	163.9	84.5	57.6
97.5°	21.8	54.1	245.2	195.0	143.6
100°	28.8	58.1	270.3	273.9	212.7
102.5°	34.8	62.2	277.3	341.1	288.8
105°	45.0	68.3	276.5	419.8	391.6
107.5°	55.6	77.1	260.8	460.6	467.5
110°	62.6	82.1	247.7	471.1	500.5



TEST NUMBER: P564567

CATALOG NUMBER: SQ4-PW1-025U-075D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	69.6	88.2	235.7	464.5	509.5
115°	80.1	97.2	221.5	441.8	504.2
117.5°	90.3	106.0	211.7	410.5	479.7
120°	96.3	111.0	207.7	389.4	456.7
122.5°	102.3	117.0	204.7	368.4	434.7
125°	111.4	124.8	201.4	340.5	401.6
127.5°	118.6	132.3	198.7	318.0	369.6
130°	122.6	137.3	197.7	303.9	351.6
132.5°	126.6	141.3	196.7	291.8	334.6
135°	132.6	146.1	195.2	274.8	311.6
137.5°	138.9	152.1	194.9	262.2	292.3
140°	143.9	156.1	193.9	252.1	280.3
142.5°	147.9	159.1	193.9	245.0	269.3
145°	153.9	163.7	192.7	234.4	252.7
147.5°	159.9	169.4	192.7	225.6	240.7
150°	163.9	172.5	192.7	220.5	232.7
152.5°	167.9	174.5	192.7	216.4	225.7
155°	173.9	178.8	192.7	211.6	217.7
157.5°	178.4	183.1	192.7	207.3	211.7
160°	181.4	185.1	192.7	205.3	207.7
162.5°	184.4	187.1	192.7	203.3	205.7
165°	187.7	190.1	192.7	200.2	202.7
167.5°	190.7	191.9	193.9	199.0	199.9
170°	192.7	193.9	193.9	198.9	198.9
172.5°	193.7	193.9	193.9	197.9	196.9
175°	195.2	195.2	193.9	196.4	196.4
177.5°	195.2	195.2	194.2	196.2	195.2
180°	195.2	195.2	195.2	195.2	195.2

(END OF REPORT)