

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519735

Luminaire Tested: **SQ4-100U-0D-940-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519735
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10416.1 lumens
Efficiency: N/A
Efficacy: 140.8 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 74
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519735
CATALOG NUMBER: SQ4-100U-0D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519735

CATALOG NUMBER: SQ4-100U-0D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3892	48060	12851
100°	4180	40020	32752
105°	4389	27094	38951
110°	4659	18474	36994
115°	4816	13364	30088
120°	4859	10586	23223
125°	4869	8926	17727
130°	4811	7842	13855
135°	4752	7039	11189
140°	4737	6456	9288
145°	4757	5999	7848
150°	4809	5647	6813
155°	4848	5379	6101
160°	4894	5196	5624
165°	4925	5071	5308
170°	4942	4982	5110
175°	4949	4925	4981



TEST NUMBER: P519735

CATALOG NUMBER: SQ4-100U-0D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	750.7	7.2
100°-110°	2072.5	19.9
110°-120°	2137.5	20.5
120°-130°	1717.6	16.5
130°-140°	1349.9	13.0
140°-150°	1035.3	9.9
150°-160°	744.1	7.1
160°-170°	455.0	4.4
170°-180°	153.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4960.7	47.6
90°-150°	9063.6	87.0
90°-180°	10416.0	100.0
0°-180°	10416.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	10	20	23	26	
95°	110	406	1362	560	364	125
105°	369	570	2280	3481	3278	393
115°	662	800	1836	3636	4135	650
125°	908	1033	1665	2817	3306	808
135°	1093	1210	1618	2282	2573	845
145°	1267	1355	1598	1942	2090	793
155°	1429	1476	1585	1743	1798	658
165°	1547	1567	1593	1655	1667	436
175°	1603	1606	1595	1618	1613	152
180°	1603	1603	1603	1603	1603	



TEST NUMBER: P519735

CATALOG NUMBER: SQ4-100U-OD-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	5.1	10.1	20.5	23.1	25.6
92.5°	46.2	191.6	342.7	125.1	97.5
95°	110.3	406.2	1362.0	559.8	364.2
97.5°	182.6	455.0	2017.6	1553.3	1125.0
100°	236.0	484.3	2259.7	2275.7	1849.3
102.5°	287.3	517.5	2306.9	2811.8	2407.5
105°	369.4	570.0	2280.2	3481.2	3278.0
107.5°	456.6	635.1	2153.0	3804.0	3878.2
110°	518.1	678.6	2054.5	3873.4	4114.2
112.5°	573.5	728.0	1962.2	3818.6	4173.7
115°	661.8	799.7	1836.5	3635.6	4134.7
117.5°	738.7	876.1	1753.9	3378.1	3945.9
120°	790.0	925.4	1721.1	3203.8	3775.6
122.5°	839.3	968.7	1694.4	3041.0	3582.7
125°	908.0	1033.4	1664.7	2817.2	3306.2
127.5°	966.5	1091.9	1647.2	2627.9	3049.7
130°	1005.5	1130.9	1639.0	2512.1	2895.8
132.5°	1042.4	1161.8	1630.8	2414.9	2762.5
135°	1092.7	1210.5	1618.5	2281.7	2572.7
137.5°	1149.1	1256.4	1612.3	2170.0	2418.2
140°	1179.9	1285.2	1608.2	2095.4	2313.6
142.5°	1214.8	1312.1	1604.1	2029.1	2221.3
145°	1267.1	1354.9	1598.0	1942.5	2090.4
147.5°	1317.4	1394.1	1592.3	1869.4	1984.2
150°	1354.3	1417.0	1590.3	1825.8	1918.6
152.5°	1383.0	1441.7	1588.2	1788.5	1865.2
155°	1428.7	1476.3	1585.1	1742.9	1798.0
157.5°	1470.7	1507.4	1585.7	1709.6	1747.2
160°	1495.4	1528.0	1587.7	1690.9	1718.5
162.5°	1515.9	1544.5	1589.8	1674.4	1695.9
165°	1546.7	1566.7	1592.8	1654.7	1667.2
167.5°	1570.3	1582.3	1595.4	1642.7	1646.7
170°	1582.6	1592.6	1595.4	1636.4	1636.4
172.5°	1592.8	1598.9	1595.4	1628.2	1626.2
175°	1603.1	1605.6	1595.4	1618.4	1613.4
177.5°	1607.2	1605.2	1594.9	1609.2	1605.1
180°	1603.1	1603.1	1603.1	1603.1	1603.1

(END OF REPORT)