

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564903

Luminaire Tested: **SQ4-PW1-0U-125D-940-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564903
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6248.1 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564903
CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564903

CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15105	15105	15105
5°	15203	15083	15016
10°	15081	14960	14878
15°	14922	14756	14701
20°	14743	14517	14488
25°	14537	14273	14229
30°	14230	14015	13923
35°	13826	13631	13550
40°	13394	13186	13134
45°	12874	12704	12648
50°	12340	12236	12154
55°	11764	11764	11578
60°	11046	11258	10860
65°	10108	10613	9856
70°	8911	9767	8677
75°	7610	8741	7405
80°	5901	7357	5979
85°	3818	5653	5039



TEST NUMBER: P564903

CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.3	3.7
10°-20°	652.9	10.4
20°-30°	968.4	15.5
30°-40°	1133.2	18.1
40°-50°	1128.1	18.1
50°-60°	974.2	15.6
60°-70°	701.2	11.2
70°-80°	367.7	5.9
80°-90°	91.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1852.6	29.6
0°-40°	2985.7	47.8
0°-60°	5088.0	81.4
0°-90°	6248.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6248.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2456	2456	2456	2456	2456	
5°	2462	2435	2443	2436	2432	233
15°	2343	2314	2317	2313	2309	660
25°	2142	2106	2103	2090	2097	985
35°	1841	1816	1815	1798	1804	1151
45°	1480	1467	1460	1456	1454	1142
55°	1097	1095	1097	1082	1080	979
65°	694	716	729	700	677	688
75°	320	350	368	343	312	343
85°	54	71	80	76	71	73
90°	0	0	0	0	0	



TEST NUMBER: P564903

CATALOG NUMBER: SQ4-PW1-0U-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2455.8	2455.8	2455.8	2455.8	2455.8
2.5°	2469.6	2449.3	2455.8	2450.3	2438.5
5°	2462.3	2434.8	2442.8	2436.2	2432.0
7.5°	2437.2	2411.8	2417.7	2410.7	2408.2
10°	2414.7	2389.3	2395.2	2386.4	2382.2
12.5°	2388.7	2361.6	2367.5	2358.8	2356.2
15°	2343.3	2313.6	2317.3	2312.9	2308.6
17.5°	2290.5	2260.4	2261.0	2254.1	2253.3
20°	2252.4	2220.7	2217.8	2209.2	2213.4
22.5°	2210.9	2177.4	2174.5	2162.5	2168.4
25°	2142.0	2106.1	2103.1	2090.3	2096.6
27.5°	2062.4	2026.9	2026.9	2008.9	2015.7
30°	2003.6	1969.7	1973.3	1951.8	1960.3
32.5°	1941.3	1910.8	1912.7	1891.3	1899.7
35°	1841.3	1815.9	1815.3	1798.2	1804.5
37.5°	1739.2	1716.7	1713.2	1703.3	1705.0
40°	1668.2	1649.2	1642.2	1635.7	1635.7
42.5°	1593.8	1576.4	1569.5	1564.7	1563.0
45°	1480.0	1467.3	1460.5	1456.1	1454.0
47.5°	1367.4	1355.6	1349.7	1346.6	1344.5
50°	1289.6	1281.1	1278.7	1272.2	1270.1
52.5°	1211.7	1206.6	1204.3	1196.0	1193.9
55°	1097.0	1094.9	1097.0	1081.8	1079.7
57.5°	977.6	980.9	987.9	967.5	962.4
60°	897.9	906.4	915.2	891.2	882.8
62.5°	816.6	830.1	842.5	815.0	803.2
65°	694.5	715.7	729.2	700.5	677.2
67.5°	576.8	603.1	619.2	588.4	562.1
70°	495.5	525.1	543.1	512.1	482.5
72.5°	424.5	457.5	472.1	442.9	413.3
75°	320.2	349.8	367.8	343.3	311.6
77.5°	227.2	255.1	270.0	248.7	222.4
80°	166.6	196.2	207.7	189.9	168.8
82.5°	118.1	142.7	150.6	139.9	125.5
85°	54.1	71.0	80.1	75.6	71.4
87.5°	13.8	25.7	32.9	32.9	34.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)