

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519329

Luminaire Tested: **SQ4-WB-0U-100D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519329
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-100D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4266.7 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 55.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519329
CATALOG NUMBER: SQ4-WB-0U-100D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519329

CATALOG NUMBER: SQ4-WB-OU-100D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65		74	68	64		71	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	78	66	59	53	76	65	58	53	64	57	53		62	56	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		58	52	47		56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40		50	44	40		49	44	40	38
10	61	49	42	37	60	48	42	37	48	41	37		47	41	37		46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18010	18010	18010
5°	17785	17721	17825
10°	16803	16956	17349
15°	15512	15872	16584
20°	14086	14616	15583
25°	12635	13324	14518
30°	11297	12036	13414
35°	9879	10593	12107
40°	8314	8975	10481
45°	6862	7455	8751
50°	5729	6246	7291
55°	4863	5360	6021
60°	4157	4646	4805
65°	3310	3908	3104
70°	2935	3050	1895
75°	2716	2474	1160
80°	2504	2274	1002
85°	2265	2089	819



TEST NUMBER: P519329

CATALOG NUMBER: SQ4-WB-OU-100D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.6	6.3
10°-20°	698.6	16.4
20°-30°	904.9	21.2
30°-40°	886.1	20.8
40°-50°	678.2	15.9
50°-60°	451.9	10.6
60°-70°	246.6	5.8
70°-80°	102.8	2.4
80°-90°	29.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1872.0	43.9
0°-40°	2758.1	64.6
0°-60°	3888.2	91.1
0°-90°	4266.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4266.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2928	2928	2928	2928	2928	
5°	2880	2852	2870	2877	2887	268
15°	2436	2427	2492	2560	2604	680
25°	1862	1867	1963	2049	2139	856
35°	1316	1322	1411	1506	1612	818
45°	789	804	857	922	1006	615
55°	454	472	500	519	562	411
65°	227	246	268	235	213	236
75°	114	114	104	71	49	122
85°	32	32	30	19	12	36
90°	0	0	0	0	0	



TEST NUMBER: P519329

CATALOG NUMBER: SQ4-WB-OU-100D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2928.1	2928.1	2928.1	2928.1	2928.1
2.5°	2935.3	2909.1	2915.7	2915.5	2907.5
5°	2880.5	2851.6	2870.2	2876.9	2886.9
7.5°	2773.6	2751.8	2785.7	2810.8	2831.2
10°	2690.4	2671.5	2714.8	2751.4	2777.7
12.5°	2593.8	2577.9	2631.5	2680.6	2715.0
15°	2436.0	2427.2	2492.5	2560.3	2604.3
17.5°	2267.2	2262.9	2337.8	2417.0	2473.2
20°	2152.0	2150.8	2233.0	2315.4	2380.7
22.5°	2035.9	2038.7	2125.1	2210.8	2285.1
25°	1861.7	1866.7	1963.2	2048.7	2139.2
27.5°	1700.6	1702.8	1802.6	1892.9	1989.4
30°	1590.6	1596.9	1694.7	1788.2	1888.7
32.5°	1480.6	1487.9	1583.6	1680.3	1782.8
35°	1315.6	1321.9	1410.7	1505.6	1612.4
37.5°	1145.5	1154.1	1232.9	1322.6	1427.7
40°	1035.5	1048.1	1117.8	1202.3	1305.4
42.5°	929.7	945.3	1009.9	1090.1	1183.0
45°	788.9	803.9	857.0	921.8	1006.0
47.5°	667.6	684.9	725.7	781.5	853.4
50°	598.7	615.0	652.7	694.0	761.9
52.5°	538.1	554.4	587.9	619.8	677.6
55°	453.5	472.4	499.8	518.7	561.5
57.5°	384.2	402.2	424.0	432.5	458.4
60°	337.9	358.0	377.7	376.8	390.6
62.5°	295.8	312.8	332.5	318.9	319.7
65°	227.4	246.3	268.5	234.6	213.3
67.5°	183.7	187.7	210.7	163.6	138.2
70°	163.2	163.2	169.6	126.7	105.4
72.5°	143.6	143.6	137.7	103.0	80.7
75°	114.3	114.3	104.1	71.4	48.8
77.5°	88.1	87.1	79.7	53.3	35.5
80°	70.7	70.7	64.2	42.1	28.3
82.5°	55.2	55.2	49.9	32.9	21.1
85°	32.1	32.1	29.6	19.1	11.6
87.5°	11.3	11.3	10.3	6.1	5.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)