

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937073

Luminaire Tested: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937073
REPORT IS A COMBINATION OF REPORTS P933493 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12280.2 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937073
CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35	29				29
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	23				23
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24	19				19
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20	16				16
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14				14
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15	12				12
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10				10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12	9				9
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10	8				8
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1719	1719	1719
5°	1680	1987	2310
10°	1524	2897	3830
15°	1296	3786	4625
20°	1055	4389	4713
25°	881	4594	4618
30°	743	4624	4609
35°	657	4548	4728
40°	573	4450	4851
45°	519	4378	4870
50°	477	4314	4790
55°	457	4219	4577
60°	468	4035	4242
65°	488	3756	3781
70°	522	3278	3195
75°	580	2675	2493
80°	640	1857	1680
85°	577	987	860

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 4870 cd/sqm



TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	0.6
10°-20°	318.6	2.6
20°-30°	557.2	4.5
30°-40°	717.3	5.8
40°-50°	801.2	6.5
50°-60°	767.4	6.2
60°-70°	608.2	5.0
70°-80°	357.6	2.9
80°-90°	104.0	0.8
90°-100°	599.8	4.9
100°-110°	1576.9	12.8
110°-120°	1635.1	13.3
120°-130°	1311.5	10.7
130°-140°	1029.1	8.4
140°-150°	789.9	6.4
150°-160°	568.8	4.6
160°-170°	348.0	2.8
170°-180°	117.6	1.0
0°-30°	947.7	7.7
0°-40°	1665.0	13.6
0°-60°	3233.7	26.3
0°-90°	4303.5	35.0
90°-120°	3811.7	31.0
90°-150°	6942.2	56.5
90°-180°	7977.0	65.0
0°-180°	12280.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	541	581	654	740	766	50
15°	406	749	1262	1530	1578	113
25°	259	849	1503	1569	1571	119
35°	175	811	1415	1496	1554	109
45°	120	647	1251	1433	1497	93
55°	86	411	1061	1233	1267	78
65°	68	218	788	886	899	67
75°	50	134	432	475	477	52
85°	18	41	107	118	120	19
90°	8	23	63	31	31	8
95°	79	310	1033	533	363	88
105°	284	430	1743	2647	2469	301
115°	505	613	1396	2786	3179	498
125°	702	787	1270	2146	2532	623
135°	837	921	1230	1733	1965	647
145°	970	1032	1215	1478	1594	608
155°	1097	1127	1215	1334	1372	504
165°	1183	1199	1215	1263	1278	334
175°	1230	1230	1223	1239	1239	117
180°	1230	1230	1230	1230	1230	



TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7
2.5°	555.7	555.7	559.3	561.0	564.6	566.4	570.0	573.6	584.3	586.1	589.6
5°	541.4	548.5	571.8	580.7	605.7	639.6	653.9	677.2	725.4	739.7	748.7
7.5°	519.9	536.0	593.2	607.5	670.1	759.4	796.9	847.0	923.8	961.3	991.6
10°	486.0	519.9	621.8	655.8	757.6	893.4	963.0	1032.7	1148.9	1200.8	1220.4
12.5°	448.4	503.9	652.1	698.6	845.1	1043.5	1127.5	1204.3	1336.5	1406.2	1416.9
15°	405.6	480.7	680.7	748.7	938.1	1168.5	1261.5	1356.2	1479.5	1529.5	1542.0
17.5°	368.1	462.7	707.6	779.0	1009.6	1281.1	1375.8	1454.5	1554.5	1588.5	1597.4
20°	321.6	434.2	725.4	818.4	1084.6	1363.3	1454.5	1515.2	1583.1	1604.5	1608.1
22.5°	287.7	403.8	736.2	832.7	1134.6	1413.3	1490.2	1538.5	1584.9	1592.0	1593.8
25°	259.1	369.9	734.4	848.8	1177.5	1443.7	1502.7	1538.5	1565.2	1568.8	1568.8
27.5°	232.3	332.4	727.2	852.3	1209.6	1450.9	1497.3	1522.3	1534.8	1542.0	1542.0
30°	209.0	296.6	709.3	845.1	1223.9	1443.7	1481.3	1493.8	1506.2	1517.0	1522.3
32.5°	191.2	262.7	682.5	830.8	1225.7	1425.9	1452.7	1459.8	1477.6	1502.7	1511.6
35°	175.1	228.7	652.1	811.2	1215.1	1397.3	1415.1	1422.3	1458.0	1495.6	1508.0
37.5°	159.0	203.7	612.9	777.3	1198.9	1363.3	1375.8	1388.3	1443.7	1488.4	1502.7
40°	143.0	182.2	566.4	739.7	1173.9	1322.2	1333.0	1352.6	1425.9	1477.6	1491.9
42.5°	130.4	164.4	516.4	700.5	1141.8	1275.8	1291.9	1320.5	1404.4	1459.8	1475.9
45°	119.7	146.5	462.7	646.8	1100.7	1227.5	1250.7	1290.1	1379.4	1433.0	1447.3
47.5°	109.0	134.0	407.4	591.4	1056.0	1179.3	1209.6	1254.3	1345.4	1397.3	1409.8
50°	100.1	121.5	352.0	532.4	1007.7	1127.5	1163.2	1209.6	1302.6	1350.8	1366.9
52.5°	92.9	110.8	300.1	473.5	952.4	1073.9	1115.0	1163.2	1250.7	1297.2	1307.9
55°	85.8	101.9	255.5	411.0	895.2	1016.7	1061.3	1107.8	1193.6	1232.9	1240.0
57.5°	82.2	94.7	218.0	352.0	834.5	952.4	1002.4	1045.3	1125.6	1156.1	1163.2
60°	76.8	89.3	189.4	302.0	768.3	891.6	934.5	977.3	1045.3	1070.3	1075.6
62.5°	71.5	85.8	167.9	253.7	700.5	820.2	863.0	902.3	959.5	977.3	984.5
65°	67.9	82.2	151.8	218.0	630.7	745.1	788.0	821.9	868.4	886.2	889.8
67.5°	64.3	78.6	139.3	187.6	561.0	670.1	702.2	734.4	770.1	788.0	789.8
70°	59.0	75.0	128.7	166.1	489.6	584.3	611.1	645.0	673.6	682.5	687.9
72.5°	55.4	69.7	121.5	150.1	416.3	502.1	527.1	546.7	571.8	580.7	580.7
75°	50.0	62.5	114.4	134.0	341.3	411.0	432.4	452.1	471.7	475.3	469.9
77.5°	44.7	55.4	98.3	112.6	266.2	325.2	343.0	353.8	369.9	373.4	375.2
80°	37.6	48.2	76.8	87.6	193.0	239.4	251.9	260.9	275.2	275.2	278.7
82.5°	28.6	37.6	55.4	62.5	130.4	164.4	175.1	180.4	189.4	189.4	189.4
85°	17.8	23.3	35.7	41.1	78.6	100.1	107.2	109.0	116.2	117.9	117.9
87.5°	9.0	12.5	23.3	25.0	41.1	51.9	51.9	55.4	55.4	53.6	51.9
90°	8.3	14.8	21.4	23.1	36.3	54.0	62.8	55.8	41.8	31.3	31.3
92.5°	33.0	89.2	145.4	159.4	224.0	310.3	353.4	309.7	222.4	156.9	150.7
95°	79.3	182.0	284.9	310.5	551.4	872.5	1033.1	921.9	699.5	532.6	513.7
97.5°	137.1	227.8	318.4	341.1	742.7	1278.2	1545.9	1475.6	1335.0	1229.6	1193.6
100°	181.7	263.9	346.1	366.7	812.3	1406.5	1703.6	1708.8	1719.1	1726.8	1683.9
102.5°	219.7	296.4	373.0	392.2	844.2	1446.9	1748.3	1837.8	2016.9	2151.3	2114.6
105°	284.1	349.1	414.0	430.2	867.9	1451.5	1743.3	1944.1	2345.7	2646.8	2627.1
107.5°	350.1	410.7	471.3	486.4	872.4	1387.0	1644.2	1924.3	2484.4	2904.4	2909.2
110°	394.7	449.4	504.1	517.8	865.7	1329.7	1561.6	1874.7	2500.9	2970.4	2991.0



TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	438.5	490.6	542.7	555.8	866.1	1279.7	1486.5	1806.9	2447.8	2928.4	2959.9
115°	504.6	552.6	600.7	612.7	874.0	1222.3	1396.5	1705.1	2322.5	2785.5	2829.3
117.5°	569.8	613.5	657.1	668.0	890.2	1186.4	1334.5	1613.1	2170.2	2588.1	2636.6
120°	607.8	649.0	690.0	700.3	903.5	1174.3	1309.7	1564.2	2073.3	2455.1	2502.3
122.5°	645.0	686.4	727.9	738.3	922.5	1168.0	1290.7	1519.9	1978.4	2322.2	2368.7
125°	702.0	739.8	777.6	787.0	948.0	1162.7	1270.1	1464.8	1854.2	2146.3	2189.2
127.5°	748.2	786.4	824.6	834.1	973.7	1159.7	1252.8	1420.0	1754.3	2005.1	2041.2
130°	773.0	814.1	855.1	865.4	992.3	1161.5	1246.1	1395.0	1692.6	1915.9	1949.2
132.5°	798.6	839.7	880.7	891.0	1007.4	1162.7	1240.4	1373.6	1640.0	1839.9	1869.9
135°	836.6	874.0	911.4	920.8	1024.0	1161.7	1230.5	1342.0	1565.2	1732.6	1758.3
137.5°	875.4	912.4	949.5	958.8	1048.8	1168.8	1228.8	1323.1	1511.8	1653.3	1674.4
140°	907.5	941.6	975.8	984.3	1063.9	1170.0	1223.0	1304.6	1467.5	1589.7	1609.4
142.5°	932.3	963.9	995.4	1003.4	1076.6	1174.2	1223.0	1294.6	1437.8	1545.1	1562.1
145°	970.3	997.8	1025.4	1032.3	1093.1	1174.2	1214.8	1273.3	1390.4	1478.3	1491.1
147.5°	1008.3	1035.1	1062.0	1068.6	1117.4	1182.3	1214.8	1260.9	1353.0	1422.0	1432.7
150°	1033.1	1057.3	1081.6	1087.6	1130.0	1186.5	1214.8	1253.7	1331.5	1389.8	1398.4
152.5°	1058.7	1077.1	1095.3	1100.0	1138.2	1189.3	1214.8	1248.0	1314.4	1364.2	1370.7
155°	1096.7	1110.3	1123.9	1127.2	1156.4	1195.3	1214.8	1241.2	1294.1	1333.7	1338.0
157.5°	1124.7	1138.0	1151.2	1154.5	1174.6	1201.4	1214.8	1235.3	1276.4	1307.2	1310.2
160°	1143.7	1154.0	1164.3	1166.9	1182.9	1204.1	1214.8	1232.4	1267.6	1294.1	1295.9
162.5°	1162.7	1170.5	1178.1	1180.1	1191.6	1207.1	1214.8	1229.6	1259.4	1281.7	1283.3
165°	1183.4	1190.4	1197.3	1199.1	1204.3	1211.3	1214.8	1225.4	1246.7	1262.6	1264.4
167.5°	1202.4	1205.6	1209.0	1209.8	1214.3	1220.1	1223.0	1230.0	1243.9	1254.4	1255.1
170°	1214.8	1218.1	1221.4	1222.2	1222.5	1222.9	1223.0	1230.0	1243.9	1254.4	1254.4
172.5°	1221.4	1222.1	1222.9	1223.0	1223.0	1223.0	1223.0	1228.5	1239.6	1247.8	1247.2
175°	1230.5	1230.5	1230.5	1230.5	1228.0	1224.7	1223.0	1226.5	1233.5	1238.8	1238.8
177.5°	1230.5	1230.5	1230.5	1230.5	1228.5	1226.0	1224.7	1227.5	1233.0	1237.1	1236.4
180°	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5



TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	555.7	555.7
2.5°	593.2	589.6
5°	763.0	766.5
7.5°	1027.4	1025.6
10°	1277.6	1293.6
12.5°	1459.8	1463.3
15°	1570.6	1577.7
17.5°	1613.5	1615.3
20°	1615.3	1611.7
22.5°	1595.6	1592.0
25°	1572.4	1570.6
27.5°	1550.9	1552.8
30°	1542.0	1547.3
32.5°	1542.0	1550.9
35°	1545.6	1554.5
37.5°	1543.8	1554.5
40°	1536.6	1549.1
42.5°	1517.0	1525.9
45°	1486.6	1497.3
47.5°	1447.3	1454.5
50°	1397.3	1404.4
52.5°	1334.8	1336.5
55°	1259.7	1266.8
57.5°	1179.3	1181.0
60°	1089.9	1095.3
62.5°	995.3	995.3
65°	895.2	898.7
67.5°	791.6	800.4
70°	686.2	687.9
72.5°	582.5	582.5
75°	475.3	477.0
77.5°	373.4	373.4
80°	277.0	278.7
82.5°	191.2	194.7
85°	119.7	119.7
87.5°	55.4	50.0
90°	31.3	31.3
92.5°	125.7	100.8
95°	438.1	362.6
97.5°	1049.8	905.9
100°	1512.5	1341.1
102.5°	1967.7	1820.9
105°	2548.1	2469.2
107.5°	2928.3	2947.4
110°	3073.2	3155.4



TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3086.2	3212.4
115°	3004.3	3179.4
117.5°	2830.8	3025.0
120°	2691.0	2879.6
122.5°	2554.8	2740.9
125°	2360.6	2532.0
127.5°	2185.9	2330.5
130°	2082.9	2216.5
132.5°	1989.5	2109.2
135°	1861.5	1964.6
137.5°	1758.8	1843.2
140°	1688.4	1767.2
142.5°	1630.0	1697.9
145°	1542.5	1593.8
147.5°	1475.2	1517.9
150°	1433.0	1467.5
152.5°	1396.8	1422.8
155°	1355.3	1372.5
157.5°	1322.4	1334.5
160°	1302.8	1309.7
162.5°	1289.9	1296.6
165°	1271.3	1278.4
167.5°	1258.1	1261.0
170°	1254.4	1254.4
172.5°	1244.6	1242.0
175°	1238.8	1238.8
177.5°	1233.4	1230.5
180°	1230.5	1230.5



TEST NUMBER: P937073

CATALOG NUMBER: SQ4-FB-075U-050D-940-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.34	2.11	2.41	3.18	4.65	14.53	15.30	15.60	16.37	17.84
	3H	2.04	2.73	3.12	3.81	5.30	16.37	17.06	17.45	18.14	19.63
	4H	2.33	2.99	3.42	4.07	5.56	17.02	17.67	18.10	18.75	20.24
	6H	2.58	3.18	3.68	4.27	5.77	17.44	18.05	18.54	19.13	20.64
	8H	2.64	3.22	3.75	4.32	5.82	17.57	18.14	18.67	19.24	20.74
	12H	2.66	3.20	3.77	4.30	5.82	17.63	18.18	18.74	19.28	20.80
4H	2H	8.55	9.21	9.65	10.29	11.78	14.80	15.45	15.89	16.53	18.02
	3H	10.11	10.66	11.21	11.77	13.27	16.84	17.38	17.94	18.50	20.00
	4H	10.20	10.70	11.31	11.80	13.33	17.60	18.11	18.71	19.21	20.73
	6H	10.21	10.64	11.32	11.76	13.28	18.14	18.57	19.26	19.70	21.21
	8H	10.18	10.58	11.30	11.70	13.23	18.30	18.71	19.42	19.82	21.36
	12H	10.13	10.50	11.27	11.63	13.17	18.39	18.76	19.53	19.89	21.43
8H	4H	11.64	12.04	12.76	13.16	14.70	17.66	18.06	18.77	19.17	20.71
	6H	11.88	12.21	13.02	13.37	14.90	18.28	18.62	19.42	19.78	21.31
	8H	11.90	12.19	13.04	13.33	14.88	18.51	18.80	19.65	19.94	21.49
	12H	11.86	12.12	13.01	13.25	14.84	18.65	18.91	19.80	20.04	21.63
12H	4H	11.78	12.15	12.91	13.28	14.81	17.60	17.97	18.74	19.10	20.64
	6H	12.14	12.43	13.28	13.57	15.12	18.27	18.56	19.41	19.70	21.25
	8H	12.20	12.46	13.35	13.59	15.18	18.49	18.75	19.64	19.89	21.47