

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519353

Luminaire Tested: **SQ4-WB-0U-125D-940-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519353
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-0U-125D-940-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5323.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519353
CATALOG NUMBER: SQ4-WB-0U-125D-940-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519353

CATALOG NUMBER: SQ4-WB-0U-125D-940-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89				89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62				62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55				55
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50				50
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45				45
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41				41
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38				38
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35				35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22468	22468	22468
5°	22188	22109	22237
10°	20963	21153	21644
15°	19352	19801	20689
20°	17573	18235	19441
25°	15762	16622	18112
30°	14093	15016	16735
35°	12324	13215	15105
40°	10373	11197	13076
45°	8561	9300	10917
50°	7147	7792	9095
55°	6067	6686	7512
60°	5186	5797	5995
65°	4129	4876	3873
70°	3661	3805	2363
75°	3391	3085	1447
80°	3124	2837	1250
85°	2830	2604	1016



TEST NUMBER: P519353

CATALOG NUMBER: SQ4-WB-OU-125D-940-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.1	6.3
10°-20°	871.5	16.4
20°-30°	1128.8	21.2
30°-40°	1105.4	20.8
40°-50°	846.1	15.9
50°-60°	563.8	10.6
60°-70°	307.7	5.8
70°-80°	128.2	2.4
80°-90°	36.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2335.4	43.9
0°-40°	3440.8	64.6
0°-60°	4850.8	91.1
0°-90°	5323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5323.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3653	3653	3653	3653	3653	
5°	3594	3558	3581	3589	3602	334
15°	3039	3028	3110	3194	3249	849
25°	2322	2329	2449	2556	2669	1068
35°	1641	1649	1760	1878	2012	1020
45°	984	1003	1069	1150	1255	767
55°	566	589	624	647	700	513
65°	284	307	335	293	266	295
75°	143	143	130	89	61	152
85°	40	40	37	24	14	45
90°	0	0	0	0	0	



TEST NUMBER: P519353

CATALOG NUMBER: SQ4-WB-OU-125D-940-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3652.9	3652.9	3652.9	3652.9	3652.9
2.5°	3661.9	3629.3	3637.5	3637.3	3627.3
5°	3593.6	3557.6	3580.8	3589.1	3601.6
7.5°	3460.3	3433.0	3475.3	3506.7	3532.1
10°	3356.4	3332.9	3386.8	3432.5	3465.4
12.5°	3235.9	3216.1	3283.0	3344.2	3387.2
15°	3039.0	3028.1	3109.6	3194.1	3249.0
17.5°	2828.4	2823.1	2916.6	3015.3	3085.5
20°	2684.8	2683.2	2785.8	2888.6	2970.1
22.5°	2539.9	2543.3	2651.1	2758.1	2850.9
25°	2322.5	2328.8	2449.2	2555.9	2668.8
27.5°	2121.5	2124.4	2248.8	2361.5	2481.9
30°	1984.3	1992.2	2114.2	2230.8	2356.2
32.5°	1847.1	1856.2	1975.7	2096.2	2224.1
35°	1641.3	1649.2	1759.9	1878.4	2011.6
37.5°	1429.1	1439.8	1538.1	1650.1	1781.1
40°	1291.9	1307.6	1394.5	1500.0	1628.5
42.5°	1159.8	1179.3	1259.8	1359.9	1475.9
45°	984.2	1003.0	1069.1	1150.0	1255.0
47.5°	832.8	854.5	905.3	975.0	1064.6
50°	746.9	767.3	814.3	865.9	950.5
52.5°	671.3	691.7	733.5	773.3	845.3
55°	565.8	589.3	623.5	647.2	700.5
57.5°	479.3	501.8	528.9	539.6	571.9
60°	421.6	446.6	471.2	470.0	487.3
62.5°	369.0	390.3	414.8	397.9	398.8
65°	283.7	307.2	335.0	292.7	266.1
67.5°	229.2	234.2	262.9	204.1	172.5
70°	203.6	203.6	211.6	158.1	131.4
72.5°	179.2	179.2	171.8	128.6	100.7
75°	142.7	142.7	129.8	89.1	60.9
77.5°	110.0	108.7	99.4	66.5	44.2
80°	88.2	88.2	80.1	52.5	35.3
82.5°	68.9	68.9	62.2	41.0	26.3
85°	40.1	40.1	36.9	23.8	14.4
87.5°	14.1	14.1	12.8	7.7	6.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)