

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937373

Luminaire Tested: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937373
REPORT IS A COMBINATION OF REPORTS P933496 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18827.4 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937373
CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937373

CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58			58
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52	47			47
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43	38			38
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36	32			32
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30	27			27
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26	23			23
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22	19			19
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19	17			17
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17	15			15
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15	13			13
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14	12			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4337	4337	4337
5°	4238	5014	5829
10°	3846	7310	9663
15°	3270	9552	11669
20°	2663	11072	11892
25°	2222	11590	11650
30°	1875	11666	11628
35°	1659	11475	11929
40°	1446	11226	12240
45°	1310	11046	12288
50°	1203	10883	12085
55°	1153	10645	11549
60°	1182	10181	10703
65°	1232	9476	9541
70°	1315	8269	8060
75°	1463	6749	6290
80°	1611	4686	4239
85°	1461	2491	2169

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12288 cd/sqm



TEST NUMBER: P937373

CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.4	1.0
10°-20°	803.8	4.3
20°-30°	1405.9	7.5
30°-40°	1809.9	9.6
40°-50°	2021.6	10.7
50°-60°	1936.2	10.3
60°-70°	1534.4	8.1
70°-80°	902.3	4.8
80°-90°	255.4	1.4
90°-100°	599.8	3.2
100°-110°	1576.9	8.4
110°-120°	1635.1	8.7
120°-130°	1311.5	7.0
130°-140°	1029.1	5.5
140°-150°	789.9	4.2
150°-160°	568.8	3.0
160°-170°	348.0	1.8
170°-180°	117.6	0.6
0°-30°	2391.1	12.7
0°-40°	4200.9	22.3
0°-60°	8158.7	43.3
0°-90°	10850.7	57.6
90°-120°	3811.7	20.2
90°-150°	6942.2	36.9
90°-180°	7977.0	42.4
0°-180°	18827.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1402	1402	1402	1402	1402	
5°	1366	1465	1650	1866	1934	126
15°	1023	1889	3183	3859	3981	285
25°	654	2141	3791	3958	3963	301
35°	442	2047	3570	3773	3922	276
45°	302	1632	3156	3616	3778	234
55°	216	1037	2678	3111	3196	197
65°	171	550	1988	2236	2268	170
75°	126	338	1091	1199	1204	132
85°	45	104	270	298	302	48
90°	8	23	63	31	31	10
95°	79	310	1033	533	363	88
105°	284	430	1743	2647	2469	301
115°	505	613	1396	2786	3179	498
125°	702	787	1270	2146	2532	623
135°	837	921	1230	1733	1965	647
145°	970	1032	1215	1478	1594	608
155°	1097	1127	1215	1334	1372	504
165°	1183	1199	1215	1263	1278	334
175°	1230	1230	1223	1239	1239	117
180°	1230	1230	1230	1230	1230	



TEST NUMBER: P937373

CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1402.1	1402.1	1402.1	1402.1	1402.1	1402.1	1402.1	1402.1	1402.1	1402.1	1402.1
2.5°	1402.1	1402.1	1411.0	1415.6	1424.5	1429.1	1438.1	1447.1	1474.2	1478.7	1487.7
5°	1365.9	1383.9	1442.6	1465.1	1528.2	1613.9	1650.0	1708.6	1830.3	1866.4	1888.9
7.5°	1311.8	1352.4	1496.7	1532.8	1690.6	1915.9	2010.6	2136.9	2330.7	2425.4	2502.0
10°	1226.2	1311.8	1568.8	1654.4	1911.4	2254.0	2429.8	2605.7	2898.7	3029.4	3079.1
12.5°	1131.6	1271.3	1645.5	1762.7	2132.4	2632.7	2844.6	3038.5	3372.1	3547.9	3574.9
15°	1023.3	1212.7	1717.6	1888.9	2366.8	2948.3	3182.7	3421.6	3732.7	3859.0	3890.5
17.5°	928.7	1167.6	1785.2	1965.5	2547.1	3232.3	3471.3	3669.6	3922.0	4007.7	4030.3
20°	811.5	1095.4	1830.3	2064.7	2736.5	3439.7	3669.6	3822.8	3994.2	4048.3	4057.3
22.5°	725.8	1018.8	1857.3	2100.7	2862.6	3565.9	3759.8	3881.4	3998.7	4016.7	4021.2
25°	653.7	933.2	1852.8	2141.3	2970.8	3642.6	3791.3	3881.4	3949.1	3958.1	3958.1
27.5°	586.1	838.5	1834.8	2150.4	3052.0	3660.6	3777.8	3840.9	3872.5	3890.5	3890.5
30°	527.5	748.3	1789.7	2132.4	3088.0	3642.6	3737.2	3768.8	3800.4	3827.4	3840.9
32.5°	482.4	662.7	1722.1	2096.3	3092.5	3597.5	3665.1	3683.2	3728.2	3791.3	3813.9
35°	441.8	577.0	1645.5	2046.7	3065.6	3525.4	3570.4	3588.5	3678.6	3773.3	3804.8
37.5°	401.2	513.9	1546.3	1961.1	3025.0	3439.7	3471.3	3502.8	3642.6	3755.3	3791.3
40°	360.6	459.8	1429.1	1866.4	2961.8	3336.0	3363.0	3412.7	3597.5	3728.2	3764.2
42.5°	329.1	414.8	1302.9	1767.2	2880.7	3218.8	3259.4	3331.5	3543.4	3683.2	3723.7
45°	302.0	369.7	1167.6	1632.0	2777.0	3097.1	3155.7	3254.9	3480.2	3615.5	3651.5
47.5°	275.0	338.2	1027.9	1492.2	2664.3	2975.3	3052.0	3164.7	3394.6	3525.4	3556.9
50°	252.5	306.5	888.1	1343.5	2542.6	2844.6	2934.8	3052.0	3286.4	3408.1	3448.7
52.5°	234.4	279.5	757.4	1194.6	2402.8	2709.4	2813.1	2934.8	3155.7	3272.9	3299.9
55°	216.4	257.0	644.7	1036.8	2258.5	2565.1	2677.9	2795.1	3011.4	3110.6	3128.6
57.5°	207.3	239.0	550.0	888.1	2105.3	2402.8	2529.0	2637.3	2840.1	2916.7	2934.8
60°	193.9	225.4	477.8	761.9	1938.5	2249.6	2357.7	2466.0	2637.3	2700.3	2713.9
62.5°	180.4	216.4	423.8	640.2	1767.2	2069.2	2177.4	2276.6	2420.9	2466.0	2484.0
65°	171.3	207.3	383.2	550.0	1591.4	1879.9	1988.1	2073.7	2191.0	2236.0	2245.0
67.5°	162.3	198.4	351.6	473.4	1415.6	1690.6	1771.6	1852.8	1943.0	1988.1	1992.6
70°	148.7	189.3	324.6	419.2	1235.2	1474.2	1541.7	1627.4	1699.5	1722.1	1735.6
72.5°	139.8	175.8	306.5	378.6	1050.4	1266.8	1329.9	1379.5	1442.6	1465.1	1465.1
75°	126.2	157.8	288.5	338.2	861.0	1036.8	1091.0	1140.5	1190.1	1199.2	1185.7
77.5°	112.7	139.8	247.9	284.0	671.7	820.5	865.5	892.6	933.2	942.2	946.7
80°	94.7	121.7	193.9	220.9	486.9	604.1	635.6	658.2	694.2	694.2	703.3
82.5°	72.1	94.7	139.8	157.8	329.1	414.8	441.8	455.3	477.8	477.8	477.8
85°	45.1	58.6	90.1	103.7	198.4	252.5	270.5	275.0	293.0	297.6	297.6
87.5°	22.6	31.5	58.6	63.1	103.7	130.7	130.7	139.8	139.8	135.2	130.7
90°	8.3	14.8	21.4	23.1	36.3	54.0	62.8	55.8	41.8	31.3	31.3
92.5°	33.0	89.2	145.4	159.4	224.0	310.3	353.4	309.7	222.4	156.9	150.7
95°	79.3	182.0	284.9	310.5	551.4	872.5	1033.1	921.9	699.5	532.6	513.7
97.5°	137.1	227.8	318.4	341.1	742.7	1278.2	1545.9	1475.6	1335.0	1229.6	1193.6
100°	181.7	263.9	346.1	366.7	812.3	1406.5	1703.6	1708.8	1719.1	1726.8	1683.9
102.5°	219.7	296.4	373.0	392.2	844.2	1446.9	1748.3	1837.8	2016.9	2151.3	2114.6
105°	284.1	349.1	414.0	430.2	867.9	1451.5	1743.3	1944.1	2345.7	2646.8	2627.1
107.5°	350.1	410.7	471.3	486.4	872.4	1387.0	1644.2	1924.3	2484.4	2904.4	2909.2
110°	394.7	449.4	504.1	517.8	865.7	1329.7	1561.6	1874.7	2500.9	2970.4	2991.0



TEST NUMBER: P937373

CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	438.5	490.6	542.7	555.8	866.1	1279.7	1486.5	1806.9	2447.8	2928.4	2959.9
115°	504.6	552.6	600.7	612.7	874.0	1222.3	1396.5	1705.1	2322.5	2785.5	2829.3
117.5°	569.8	613.5	657.1	668.0	890.2	1186.4	1334.5	1613.1	2170.2	2588.1	2636.6
120°	607.8	649.0	690.0	700.3	903.5	1174.3	1309.7	1564.2	2073.3	2455.1	2502.3
122.5°	645.0	686.4	727.9	738.3	922.5	1168.0	1290.7	1519.9	1978.4	2322.2	2368.7
125°	702.0	739.8	777.6	787.0	948.0	1162.7	1270.1	1464.8	1854.2	2146.3	2189.2
127.5°	748.2	786.4	824.6	834.1	973.7	1159.7	1252.8	1420.0	1754.3	2005.1	2041.2
130°	773.0	814.1	855.1	865.4	992.3	1161.5	1246.1	1395.0	1692.6	1915.9	1949.2
132.5°	798.6	839.7	880.7	891.0	1007.4	1162.7	1240.4	1373.6	1640.0	1839.9	1869.9
135°	836.6	874.0	911.4	920.8	1024.0	1161.7	1230.5	1342.0	1565.2	1732.6	1758.3
137.5°	875.4	912.4	949.5	958.8	1048.8	1168.8	1228.8	1323.1	1511.8	1653.3	1674.4
140°	907.5	941.6	975.8	984.3	1063.9	1170.0	1223.0	1304.6	1467.5	1589.7	1609.4
142.5°	932.3	963.9	995.4	1003.4	1076.6	1174.2	1223.0	1294.6	1437.8	1545.1	1562.1
145°	970.3	997.8	1025.4	1032.3	1093.1	1174.2	1214.8	1273.3	1390.4	1478.3	1491.1
147.5°	1008.3	1035.1	1062.0	1068.6	1117.4	1182.3	1214.8	1260.9	1353.0	1422.0	1432.7
150°	1033.1	1057.3	1081.6	1087.6	1130.0	1186.5	1214.8	1253.7	1331.5	1389.8	1398.4
152.5°	1058.7	1077.1	1095.3	1100.0	1138.2	1189.3	1214.8	1248.0	1314.4	1364.2	1370.7
155°	1096.7	1110.3	1123.9	1127.2	1156.4	1195.3	1214.8	1241.2	1294.1	1333.7	1338.0
157.5°	1124.7	1138.0	1151.2	1154.5	1174.6	1201.4	1214.8	1235.3	1276.4	1307.2	1310.2
160°	1143.7	1154.0	1164.3	1166.9	1182.9	1204.1	1214.8	1232.4	1267.6	1294.1	1295.9
162.5°	1162.7	1170.5	1178.1	1180.1	1191.6	1207.1	1214.8	1229.6	1259.4	1281.7	1283.3
165°	1183.4	1190.4	1197.3	1199.1	1204.3	1211.3	1214.8	1225.4	1246.7	1262.6	1264.4
167.5°	1202.4	1205.6	1209.0	1209.8	1214.3	1220.1	1223.0	1230.0	1243.9	1254.4	1255.1
170°	1214.8	1218.1	1221.4	1222.2	1222.5	1222.9	1223.0	1230.0	1243.9	1254.4	1254.4
172.5°	1221.4	1222.1	1222.9	1223.0	1223.0	1223.0	1223.0	1228.5	1239.6	1247.8	1247.2
175°	1230.5	1230.5	1230.5	1230.5	1228.0	1224.7	1223.0	1226.5	1233.5	1238.8	1238.8
177.5°	1230.5	1230.5	1230.5	1230.5	1228.5	1226.0	1224.7	1227.5	1233.0	1237.1	1236.4
180°	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5	1230.5



TEST NUMBER: P937373

CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1402.1	1402.1
2.5°	1496.7	1487.7
5°	1925.0	1934.0
7.5°	2592.2	2587.6
10°	3223.3	3263.8
12.5°	3683.2	3692.1
15°	3962.6	3980.6
17.5°	4070.9	4075.3
20°	4075.3	4066.3
22.5°	4025.7	4016.7
25°	3967.1	3962.6
27.5°	3913.1	3917.6
30°	3890.5	3904.0
32.5°	3890.5	3913.1
35°	3899.5	3922.0
37.5°	3895.0	3922.0
40°	3877.0	3908.5
42.5°	3827.4	3849.9
45°	3750.7	3777.8
47.5°	3651.5	3669.6
50°	3525.4	3543.4
52.5°	3367.6	3372.1
55°	3178.2	3196.3
57.5°	2975.3	2979.9
60°	2750.0	2763.5
62.5°	2511.0	2511.0
65°	2258.5	2267.6
67.5°	1997.1	2019.7
70°	1731.2	1735.6
72.5°	1469.6	1469.6
75°	1199.2	1203.7
77.5°	942.2	942.2
80°	698.8	703.3
82.5°	482.4	491.4
85°	302.0	302.0
87.5°	139.8	126.2
90°	31.3	31.3
92.5°	125.7	100.8
95°	438.1	362.6
97.5°	1049.8	905.9
100°	1512.5	1341.1
102.5°	1967.7	1820.9
105°	2548.1	2469.2
107.5°	2928.3	2947.4
110°	3073.2	3155.4



TEST NUMBER: P937373

CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3086.2	3212.4
115°	3004.3	3179.4
117.5°	2830.8	3025.0
120°	2691.0	2879.6
122.5°	2554.8	2740.9
125°	2360.6	2532.0
127.5°	2185.9	2330.5
130°	2082.9	2216.5
132.5°	1989.5	2109.2
135°	1861.5	1964.6
137.5°	1758.8	1843.2
140°	1688.4	1767.2
142.5°	1630.0	1697.9
145°	1542.5	1593.8
147.5°	1475.2	1517.9
150°	1433.0	1467.5
152.5°	1396.8	1422.8
155°	1355.3	1372.5
157.5°	1322.4	1334.5
160°	1302.8	1309.7
162.5°	1289.9	1296.6
165°	1271.3	1278.4
167.5°	1258.1	1261.0
170°	1254.4	1254.4
172.5°	1244.6	1242.0
175°	1238.8	1238.8
177.5°	1233.4	1230.5
180°	1230.5	1230.5



TEST NUMBER: P937373
 CATALOG NUMBER: SQ4-FB-075U-125D-940-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.77	7.75	7.65	8.66	9.82	19.97	20.95	20.85	21.85	23.01
	3H	7.49	8.37	8.38	9.29	10.47	21.82	22.70	22.71	23.62	24.80
	4H	7.79	8.63	8.70	9.55	10.74	22.47	23.31	23.38	24.23	25.42
	6H	8.05	8.82	8.97	9.75	10.95	22.92	23.69	23.83	24.61	25.82
	8H	8.12	8.86	9.05	9.80	11.00	23.04	23.78	23.97	24.72	25.93
	12H	8.14	8.84	9.08	9.78	11.01	23.12	23.82	24.05	24.76	25.99
4H	2H	14.01	14.85	14.92	15.77	16.96	20.25	21.09	21.17	22.01	23.20
	3H	15.59	16.29	16.51	17.24	18.45	22.32	23.02	23.24	23.97	25.17
	4H	15.69	16.33	16.62	17.28	18.51	23.09	23.73	24.03	24.68	25.91
	6H	15.71	16.26	16.66	17.23	18.46	23.64	24.20	24.59	25.17	26.40
	8H	15.69	16.21	16.64	17.17	18.41	23.81	24.33	24.76	25.29	26.54
	12H	15.65	16.12	16.62	17.10	18.35	23.91	24.38	24.88	25.36	26.61
8H	4H	17.15	17.67	18.10	18.63	19.88	23.16	23.68	24.11	24.65	25.89
	6H	17.40	17.83	18.37	18.83	20.07	23.80	24.23	24.78	25.24	26.48
	8H	17.42	17.80	18.40	18.79	20.05	24.03	24.41	25.01	25.40	26.66
	12H	17.39	17.72	18.38	18.71	20.02	24.18	24.51	25.17	25.50	26.81
12H	4H	17.30	17.77	18.27	18.75	20.00	23.12	23.59	24.09	24.57	25.82
	6H	17.66	18.04	18.64	19.03	20.29	23.79	24.17	24.77	25.16	26.42
	8H	17.73	18.07	18.72	19.06	20.36	24.02	24.36	25.02	25.35	26.66