

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519714

Luminaire Tested: **SQ4-075U-0D-940-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519714
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5176.1 lumens
Efficiency: N/A
Efficacy: 141.4 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 36.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519714
CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519714

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	2953	35076	9575
100°	3098	29775	24520
105°	3285	20248	28775
110°	3443	13795	27635
115°	3562	9946	22476
120°	3634	7876	17344
125°	3617	6649	13175
130°	3567	5823	10337
135°	3541	5239	8349
140°	3532	4805	6923
145°	3532	4456	5846
150°	3566	4196	5070
155°	3614	4001	4535
160°	3643	3859	4183
165°	3665	3771	3948
170°	3674	3706	3801
175°	3679	3664	3703



TEST NUMBER: P519714

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	374.7	7.2
100°-110°	1031.0	19.9
110°-120°	1064.2	20.6
120°-130°	852.6	16.5
130°-140°	669.7	12.9
140°-150°	513.2	9.9
150°-160°	369.0	7.1
160°-170°	225.6	4.4
170°-180°	76.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2470.0	47.7
90°-150°	4505.5	87.0
90°-180°	5176.0	100.0
0°-180°	5176.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	7	12	15	15	
95°	56	205	663	283	181	62
105°	184	283	1136	1730	1614	194
115°	326	397	911	1814	2059	322
125°	450	512	827	1398	1638	401
135°	543	602	803	1131	1280	419
145°	627	670	791	964	1038	393
155°	710	733	786	866	891	326
165°	768	777	790	822	827	216
175°	794	796	791	801	800	75
180°	794	794	794	794	794	



TEST NUMBER: P519714

CATALOG NUMBER: SQ4-075U-0D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.7	6.6	11.8	15.2	15.2
92.5°	23.3	99.7	172.8	66.3	54.4
95°	55.8	204.6	662.7	283.4	180.9
97.5°	90.9	226.8	1011.3	779.2	549.8
100°	116.6	240.6	1120.8	1131.3	923.0
102.5°	141.0	257.0	1149.2	1403.5	1212.4
105°	184.3	283.4	1136.0	1730.2	1614.4
107.5°	225.5	316.1	1071.5	1890.1	1924.5
110°	255.3	337.9	1022.8	1929.9	2048.9
112.5°	282.3	362.3	974.1	1904.3	2085.4
115°	326.3	397.3	911.2	1814.4	2059.1
117.5°	368.2	433.7	871.3	1688.4	1965.1
120°	393.9	456.7	853.7	1593.9	1879.9
122.5°	416.9	479.7	841.5	1511.1	1782.5
125°	449.7	512.5	826.7	1398.4	1638.1
127.5°	480.8	540.6	816.9	1304.4	1514.7
130°	497.0	558.2	811.4	1248.6	1440.3
132.5°	515.9	577.1	807.4	1199.5	1372.7
135°	542.7	602.2	803.0	1131.0	1279.7
137.5°	567.7	622.9	799.3	1075.6	1198.2
140°	586.6	637.9	797.9	1038.8	1149.6
142.5°	602.8	650.1	795.2	1006.0	1100.9
145°	627.2	670.2	791.2	963.6	1038.0
147.5°	653.2	690.2	789.1	926.1	985.6
150°	669.4	702.5	787.8	905.5	951.8
152.5°	684.3	714.7	786.4	887.7	926.1
155°	710.0	733.2	786.1	866.1	890.9
157.5°	728.6	747.5	786.1	848.4	865.5
160°	742.1	757.0	786.1	838.8	852.0
162.5°	753.0	765.2	787.4	830.6	841.2
165°	767.5	777.4	789.5	821.7	826.7
167.5°	777.6	785.2	791.2	814.2	815.5
170°	784.4	789.4	791.2	811.4	811.4
172.5°	789.8	792.1	791.2	807.4	806.0
175°	794.5	796.2	791.2	801.3	799.6
177.5°	795.9	795.9	790.5	798.5	795.9
180°	794.5	794.5	794.5	794.5	794.5

(END OF REPORT)