

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519762

Luminaire Tested: **SQ4-125U-0D-940-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519762
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8643.6 lumens
Efficiency: N/A
Efficacy: 140.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Indirect

Input Watts (W): 61.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519762
CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P519762

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20			
RC	80								50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5055	54348	19229
100°	5212	47715	41416
105°	5563	33259	46696
110°	5774	23121	44492
115°	6013	16962	37069
120°	6106	13360	28908
125°	6050	11221	22319
130°	5974	9841	17394
135°	5909	8846	14054
140°	5875	8115	11668
145°	5898	7540	9836
150°	5978	7087	8568
155°	6051	6754	7666
160°	6112	6523	7059
165°	6158	6362	6647
170°	6200	6248	6400
175°	6208	6176	6248



TEST NUMBER: P519762

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	626.4	7.2
100°-110°	1687.3	19.5
110°-120°	1770.7	20.5
120°-130°	1436.9	16.6
130°-140°	1126.9	13.0
140°-150°	865.2	10.0
150°-160°	622.1	7.2
160°-170°	380.0	4.4
170°-180°	128.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4084.4	47.3
90°-150°	7513.4	86.9
90°-180°	8644.0	100.0
0°-180°	8643.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	10	20	22	22	
95°	96	341	1027	525	363	106
105°	312	486	1866	2792	2620	328
115°	551	674	1554	3002	3396	542
125°	752	864	1395	2358	2775	672
135°	906	1011	1356	1902	2154	699
145°	1047	1129	1339	1626	1747	657
155°	1189	1232	1327	1459	1506	547
165°	1290	1304	1332	1385	1392	364
175°	1341	1339	1334	1352	1349	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P519762

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	3.4	10.1	20.5	22.2	22.2
92.5°	41.6	147.0	290.6	139.9	97.2
95°	95.5	340.7	1026.8	525.1	363.3
97.5°	152.5	390.0	1610.5	1345.4	1014.5
100°	196.2	409.6	1796.1	1879.2	1559.0
102.5°	238.5	437.2	1857.5	2278.9	2016.1
105°	312.1	485.6	1866.0	2791.7	2619.9
107.5°	381.7	536.5	1786.5	3055.2	3099.5
110°	428.1	574.9	1714.2	3137.0	3298.7
112.5°	477.2	613.3	1644.6	3118.9	3384.7
115°	550.9	674.3	1553.9	3002.4	3396.0
117.5°	618.1	733.9	1483.6	2816.4	3254.7
120°	661.8	773.5	1448.1	2683.0	3133.3
122.5°	700.0	810.4	1422.2	2546.5	2995.5
125°	752.2	863.9	1395.2	2358.2	2775.1
127.5°	802.3	912.4	1378.2	2192.0	2564.3
130°	832.4	942.4	1371.3	2096.9	2423.7
132.5°	862.4	971.1	1364.5	2013.0	2313.2
135°	905.7	1010.8	1356.0	1902.4	2154.2
137.5°	947.0	1047.7	1351.6	1808.6	2015.4
140°	975.6	1072.4	1347.5	1750.8	1937.6
142.5°	1005.7	1095.7	1344.7	1697.0	1854.4
145°	1047.3	1129.0	1338.9	1626.5	1746.6
147.5°	1092.3	1163.3	1333.1	1567.3	1661.6
150°	1122.3	1184.0	1330.4	1530.0	1608.4
152.5°	1149.6	1203.3	1329.0	1499.7	1563.4
155°	1188.8	1232.2	1327.0	1459.4	1506.1
157.5°	1223.3	1257.0	1327.3	1431.1	1462.4
160°	1245.1	1273.5	1328.7	1414.5	1437.9
162.5°	1264.2	1287.2	1330.1	1400.7	1417.4
165°	1289.5	1304.5	1332.1	1385.1	1391.8
167.5°	1309.9	1318.6	1333.8	1373.1	1375.8
170°	1323.6	1326.9	1333.8	1366.2	1366.2
172.5°	1331.8	1332.4	1335.2	1359.4	1359.4
175°	1340.6	1339.0	1333.8	1352.5	1349.2
177.5°	1344.4	1341.7	1334.8	1345.7	1343.0
180°	1338.9	1338.9	1338.9	1338.9	1338.9

(END OF REPORT)