

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518418

Luminaire Tested: **SQ4-BB-050U-050D-940-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518418
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-050U-050D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.1 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 58.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518418
CATALOG NUMBER: SQ4-BB-050U-050D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P518418

CATALOG NUMBER: SQ4-BB-050U-050D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	97	93	90	87	88	85	82	79	69	68	66	55	54	53	42	42	41	35
2	89	83	77	73	81	76	71	67	63	59	57	50	48	47	39	38	37	32
3	82	74	68	63	75	68	62	58	56	53	49	46	43	41	36	34	33	29
4	76	66	60	54	69	61	55	51	51	47	43	42	39	37	33	31	30	26
5	70	60	53	47	64	55	49	44	46	42	38	38	35	33	31	29	27	24
6	65	54	47	42	59	50	44	39	42	38	34	35	32	29	28	26	25	22
7	61	50	42	37	55	46	40	35	39	34	31	32	29	27	26	24	22	20
8	56	45	38	33	52	42	36	32	36	31	28	30	27	24	25	22	21	18
9	53	42	35	30	48	39	33	29	33	29	25	28	25	22	23	21	19	17
10	49	38	32	27	45	36	30	26	31	26	23	26	23	20	22	19	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8381	8381	8381
5°	8245	8226	8286
10°	7715	7818	8036
15°	7014	7236	7639
20°	6226	6550	7124
25°	5422	5851	6545
30°	4644	5155	5997
35°	3851	4375	5336
40°	2959	3499	4547
45°	2139	2649	3658
50°	1457	1974	2902
55°	947	1428	2255
60°	543	1006	1630
65°	144	613	825
70°	71	190	237
75°	32	16	0
80°	24	0	0
85°	0	0	0



TEST NUMBER: P518418

CATALOG NUMBER: SQ4-BB-050U-050D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	3.0
10°-20°	424.0	7.6
20°-30°	530.8	9.5
30°-40°	490.3	8.7
40°-50°	329.4	5.9
50°-60°	170.2	3.0
60°-70°	53.3	0.9
70°-80°	3.4	0.1
80°-90°	2.1	0.0
90°-100°	253.2	4.5
100°-110°	687.8	12.3
110°-120°	707.2	12.6
120°-130°	565.4	10.1
130°-140°	444.3	7.9
140°-150°	340.7	6.1
150°-160°	245.0	4.4
160°-170°	149.8	2.7
170°-180°	50.5	0.9
0°-30°	1120.6	20.0
0°-40°	1610.8	28.7
0°-60°	2110.4	37.6
0°-90°	2169.2	38.6
90°-120°	1648.3	29.4
90°-150°	2998.6	53.4
90°-180°	3444.0	61.4
0°-180°	5613.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1817	1817	1817	1817	1817	
5°	1781	1763	1776	1783	1789	165
15°	1469	1464	1515	1566	1600	409
25°	1065	1074	1150	1228	1286	488
35°	684	701	777	868	948	424
45°	328	348	406	485	561	257
55°	118	138	178	228	280	110
65°	13	25	56	68	76	22
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	2	7	12	15	15	3
95°	37	138	441	192	129	40
105°	122	190	756	1152	1084	130
115°	217	264	606	1205	1372	214
125°	298	340	548	923	1089	266
135°	360	399	532	752	848	278
145°	416	445	526	639	687	261
155°	470	486	522	574	590	217
165°	509	515	524	546	548	144
175°	528	529	526	532	531	50
180°	528	528	528	528	528	



TEST NUMBER: P518418

CATALOG NUMBER: SQ4-BB-050U-050D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1816.7	1816.7	1816.7	1816.7	1816.7
2.5°	1820.9	1803.7	1808.2	1808.1	1803.3
5°	1780.6	1762.6	1776.3	1782.6	1789.4
7.5°	1705.4	1691.3	1717.5	1737.2	1751.5
10°	1647.1	1635.0	1669.0	1695.8	1715.6
12.5°	1579.6	1570.3	1611.4	1648.2	1673.4
15°	1468.6	1463.5	1515.2	1566.1	1599.6
17.5°	1349.8	1349.6	1408.7	1471.8	1512.2
20°	1268.3	1270.8	1334.2	1403.8	1451.1
22.5°	1186.7	1192.7	1260.3	1332.9	1387.1
25°	1065.2	1073.8	1149.6	1228.3	1285.8
27.5°	948.5	961.1	1040.8	1122.5	1192.7
30°	871.9	886.5	967.7	1053.7	1125.9
32.5°	796.6	814.0	893.1	984.1	1057.7
35°	683.8	701.0	776.9	868.4	947.5
37.5°	567.2	584.1	658.3	748.3	833.7
40°	491.3	510.2	581.0	668.2	755.0
42.5°	422.4	441.3	507.8	593.5	675.5
45°	327.8	347.6	406.1	485.1	560.7
47.5°	249.4	270.9	322.2	393.7	462.7
50°	203.0	224.5	275.1	338.1	404.3
52.5°	165.8	186.6	232.2	291.6	352.3
55°	117.8	137.5	177.5	227.9	280.4
57.5°	81.4	98.4	134.3	176.4	217.4
60°	58.9	75.2	109.0	143.1	176.7
62.5°	39.2	54.2	87.2	113.4	135.9
65°	13.2	25.2	56.2	67.9	75.6
67.5°	6.7	8.1	29.5	31.2	33.7
70°	5.3	5.3	14.1	15.0	17.6
72.5°	3.9	3.9	5.6	7.2	7.7
75°	1.8	1.8	0.9	0.0	0.0
77.5°	0.9	0.9	0.7	0.0	0.0
80°	0.9	0.9	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.3	1.3	2.4	3.1	3.1
90°	1.7	6.7	11.9	15.3	15.3
92.5°	15.3	69.3	120.4	51.7	43.8
95°	37.3	138.5	441.0	191.9	128.9
97.5°	61.7	152.9	676.0	525.9	369.4
100°	78.0	162.6	747.9	758.2	612.3
102.5°	94.3	172.2	766.9	937.7	809.0
105°	122.1	190.1	756.4	1151.7	1083.8
107.5°	150.9	211.0	712.7	1262.3	1281.2
110°	171.3	226.0	680.1	1284.0	1365.3



TEST NUMBER: P518418

CATALOG NUMBER: SQ4-BB-050U-050D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.9	241.0	647.5	1266.0	1388.4
115°	217.1	263.5	605.5	1204.6	1372.1
117.5°	243.5	288.0	578.7	1117.6	1306.3
120°	261.2	304.3	566.5	1059.2	1246.6
122.5°	276.1	319.2	558.3	1000.7	1181.4
125°	298.5	340.0	547.8	923.0	1088.8
127.5°	318.5	359.6	542.0	864.1	1006.4
130°	330.7	370.5	539.3	827.2	954.9
132.5°	342.9	382.7	536.6	795.6	908.7
135°	359.6	399.4	532.5	751.8	848.0
137.5°	377.5	413.7	530.5	713.1	794.1
140°	388.4	423.2	529.2	688.5	761.5
142.5°	399.2	431.4	527.8	669.3	730.3
145°	415.5	445.4	525.8	638.8	686.9
147.5°	433.8	459.4	524.1	614.8	652.6
150°	446.1	467.6	524.1	601.1	630.9
152.5°	455.6	474.5	522.7	588.7	613.3
155°	469.8	486.4	522.4	573.6	590.2
157.5°	483.7	496.6	522.4	563.4	576.0
160°	491.8	503.5	522.4	556.5	566.5
162.5°	500.0	508.9	523.7	551.0	558.3
165°	508.8	515.4	524.1	546.2	547.8
167.5°	518.0	521.3	525.8	540.4	541.7
170°	520.7	524.0	525.8	537.6	537.6
172.5°	523.4	525.4	525.8	534.9	534.9
175°	527.5	529.1	525.8	532.5	530.9
177.5°	528.8	528.8	524.7	530.1	527.5
180°	527.5	527.5	527.5	527.5	527.5

(END OF REPORT)